



PRODUCT DATASHEET

TUBE READY T8 WRAP 2 LAMP 4FT

TUBE READY WRAP | Tube Ready Wrap Fixture for LED T8 Type B - Ballast-Free Lamps

Areas of application

- Retail
- Manufacturing
- Warehouses
- Offices
- Low Bay locations

Product features

- 4-foot fixture
- Prismatic lens
- White powder coated metal body
- Wired to operate two UL Type-B (ballast-free) double ended LED T8 lamps
- Lamps are not included
- Toolless lens removal

TECHNICAL DATA

Additional product data

Ordering Abbreviation	TUBEREADY/T8BFWRAP/2LAMP/48/WH
Abbrev. With Packaging Info.	TUBEREADYT8BFWRAP2LAMP48WH 6/CS 1/SKU
SKU UPC	0046135656552
NAED	65655
General Description	LED T8 Lamp-ready 4-foot Wrap fixture. Fixture does NOT include lamps. Designed to operate two 48" LED T8 Type B lamps. White metal body, PMMA lens. 48.7" long by 6.5" wide.
Warranty	5 years

Electrical data

Nominal voltage	120.00...277.00 V
Power factor	≥0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Luminaire Type	Wrap
----------------	------

Dimensions & Weight

Length	48.72 in
Width	6.54 in
Height	2.75 in
Product weight	5.51 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Metal
Mercury content	0.0 mg

Application & Mounting

Dimming	No
Mounting	Surface
Indoor/Outdoor	Indoor
Replaceable light source	No

Logistical data

SKU Qty	1
Case Qty	6
Case Length (in)	50.354

Case Width (in)	15.315
Case Depth (in)	9.843
Case Cube (ft)	4.393
Case Weight (lbs)	42.874
SKU UPC	0046135656552
Pallet Qty	48

Certificates & Standards

Certification Listing	RoHS / cULus
-----------------------	--------------

Safety advice

- Fixture is wired to operate two UL Type B (ballast bypass) double end LED T8 lamps
- Fixture is recommended for surface mounting

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Product Family Spec Sheet	LED TUBE READY WRAP

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.