




LED recessed luminaire for machines



Product-Nr.	153110-11
EAN:	4260556625478
Model:	FIELDLED EVO Integrated, M12 front-end

Order number:	153110-11
Model:	FIELDLED EVO Integrated, M12 front-end

Type:	LED recessed luminaire for machines
Illuminant:	SMD LED
Power consumption:	~39 W
Lamp luminous flux:	6000 lm
Lamp luminous efficiency:	155 lm/W
Light distribution:	Direct

Light colour:	5700K 3-step MacAdam
Colour rendering (Ra):	>85

Supply voltage:	24V DC $\pm$ 10%
Connection (connector):	M12 A-coded, end face

Degree of protection:	IP67/IP69K
Class of protection:	III

Glare control:	Microprisms
Beam angle (optics):	100°

Operating temperature:	-30 °C - +60 °C (-22 °F - 140 °F)
Storage temperature:	-30 °C - +80 °C (-22 °F - 176 °F)

Lamps lifetime:	> 100,000 h (L80/B10)
Vibration resistance:	At 10 to 55 Hz (amplitude 0.35 mm (~0,01"))

Shock resistance:	Up to 50 g (~2 oz)
Housing material:	aluminium

Cover material:	ESG (toughened tempered glass), shatterproof
Height [B] x Width [C]:	30 mm x 96 mm (~1.18" x ~3.78"), frame: 5.6 mm x 132 mm (~0.22" x ~5.2")

Length [A]:	540 mm (~21,26")
Weight (net):	2200 g (~78 oz)

Gross weight:	2550 g (~90 oz)
Risk group (DIN EN 62471):	Free group

Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	Optional via accessories

Made in:	Germany
-----------------	---------