


JOB NAME:

DATE:

TYPE:

COMMENTS:



LIGHT INFORMATION

Light Type	Integrated LED
CRI	90
Delivered Lumens	1516
Color Temperature	3000K-6400K
LED Lifespan (L70)	50000
Light Direction	Ambient
Dimming Method	Touch Switch
Current Type	DC
Input Voltage	120-240
Total Wattage	40

DIMENSIONS & WEIGHT

Width (In)	24
Height (In)	48
Min Height (In)	48
Max Height (In)	48
Ext (In)	5.5
Weight (Lbs)	33.22

INSTALLATION

Mounting Type	J-Box
Rating	Damp
Hanging Support Type	Z-Bar

PRODUCT FINISH

Tendril Green

PRODUCT FEATURES

Built-in USB-A and USB-C charging ports

CERTIFICATIONS & COMPLIANCE

