

BIRK

B7912-PBR/BRZ

Combining the classic with the cool, the Birk family blends sleek architectural lines with an understated RLM shade to create a convenient exterior lighting solution. Featuring two wall-mounted sconces and a portable, battery-powered table lamp, the designs reflect LED light downward after it bounces off the shallow dome shade. The integrated handle of the table lamp encourages portability, making it perfect to carry both indoors and outdoors. Birk is finished in Bronze with Patina Brass accents.

FINISHES

PATINA BRASS w/ BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12"

Width/Diameter: 11"

Canopy/Backplate: 4.75"

Product Weight: 3.92lb

Extension: 11.5"

Top to Center: 5"

Canopy/Backplate Shape: Square

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear Inside Etched

Shade 1 Top Width: 2.5"

Shade 2: Aluminum

Shade 2 Finish: Bronze

Shade 2 Top Width: 11"

Shade 2 Height: 1.75"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: GU10

Bulb Type: MR16

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"):

Dark Sky: Yes

SHIPPING

Carton 1: 13" x 13" x 11"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

REVISED 3.11.2022