

ValueLED™ Strip Retrofit



Erich Bockley

ValueLED™ Strip Retrofit

Key Features and Benefits



- Offers a cost-effective and energy efficient retrofit for fluorescent strip fixtures
- Attaches to standard 4.25" to 5.25" wide fluorescent strip fixture bodies
- Available in 4ft or 8ft kits
- DLC Premium listing for all models maximizes rebate opportunities

Applications

- Warehouse
- Office
- Education
- Low-bay applications

Wattage	CCT (K)	Voltage	Length	Warranty
25W	3500K, 4000K, 5000K	120-277	4'	5 years
30W	3500K, 4000K, 5000K	120-277	4'	5 years
46W	3500K, 4000K, 5000K	120-277	8'	5 years
54W	3500K, 4000K, 5000K	120-277	8'	5 years



ValueLED™ Strip Retrofit

Product Offering (base models)

Item Number	Ordering Description (click for PIB)	Wattage	Voltage	Dimming	CRI/CCT	Lumens	LPW	DLC
61471	RSTRIP1A025UNVD83548UWH	25	120-277	0-10	835	3250	130	Premium
61472	RSTRIP1A/025UNVD840/48U/WH	25	120-277	0-10	840	3300	132	Premium
61473	RSTRIP1A/025UNVD850/48U/WH	25	120-277	0-10	850	3325	133	Premium
61474	RSTRIP1A/030UNVD835/48U/WH	30	120-277	0-10	835	3960	132	Premium
61475	RSTRIP1A/030UNVD840/48U/WH	30	120-277	0-10	840	4020	134	Premium
61476	RSTRIP1A/030UNVD850/48U/WH	30	120-277	0-10	850	4080	136	Premium
61477	RSTRIP1A/046UNVD835/96U/WH	46	120-277	0-10	835	5980	130	Premium
61478	RSTRIP1A/046UNVD840/96U/WH	46	120-277	0-10	840	6070	132	Premium
61479	RSTRIP1A/046UNVD850/96U/WH	46	120-277	0-10	850	6115	133	Premium
61480	RSTRIP1A/054UNVD850/96U/WH	54	120-277	0-10	835	7125	132	Premium
61481	RSTRIP1A/054UNVD850/96U/WH	54	120-277	0-10	840	7230	134	Premium
61482	RSTRIP1A/054UNVD850/96U/WH	54	120-277	0-10	850	7340	136	Premium



ValueLED™ Strip Retrofit Product Offering (EM models)

Item Number	Ordering Description (click for PIB)	Wattage	Voltage	Dimming	CRI/CCT	Lumens	LPW	DLC
61483	RSTRIP1A/025UNVD835/48U/WH/E	25	120-277	0-10	835	3250	130	Premium
61484	RSTRIP1A/025UNVD840/48U/WH/E	25	120-277	0-10	840	3300	132	Premium
61485	RSTRIP1A/025UNVD850/48U/WH/E	25	120-277	0-10	850	3325	132	Premium
61486	RSTRIP1A/030UNVD835/48U/WH/E	30	120-277	0-10	835	3960	132	Premium
61487	RSTRIP1A/030UNVD840/48U/WH/E	30	120-277	0-10	840	4020	134	Premium
61488	RSTRIP1A/030UNVD850/48U/WH/E	30	120-277	0-10	850	4080	136	Premium
61489	RSTRIP1A/046UNVD835/96U/WH/E	46	120-277	0-10	835	5980	130	Premium
61490	RSTRIP1A/046UNVD840/96U/WH/E	46	120-277	0-10	840	6070	132	Premium
61491	RSTRIP1A/046UNVD850/96U/WH/E	46	120-277	0-10	850	6115	133	Premium
61492	RSTRIP1A/054UNVD835/96U/WH/E	54	120-277	0-10	835	7125	132	Premium
61493	RSTRIP1A/054UNVD840/96U/WH/E	54	120-277	0-10	840	7230	134	Premium
61494	RSTRIP1A/054UNVD850/96U/WH/E	54	120-277	0-10	850	7340	136	Premium

ValueLED™ Strip Retrofit

Nomenclature Review

Ordering Guide

RSTRIP	1A	/	XX	UNV	D	8	XX	/	XX	U	/	WH
Product Name	Generation		Wattage	Voltage	Dimming	CRI	Color Temp (CCT)		Length	Mounting		Color/Finish
RSTRIP =	1A		25 = 25 Watts	UNV = 120-277V	D = 0-10V	8 = >80	35 = 3500K		48 = 48 inches	U = Universal		WH = White
Retrofit Strip			30 = 30 Watts				40 = 4000K		96 = 96 inches	Mounting		
			46 = 46 Watts				50 = 5000K					
			54 = 54 Watts									



ValueLED™ Strip Retrofit

Key Takeaways

- Offers a cost-effective and energy efficient retrofit for fluorescent strip fixtures
- Attaches to standard 4.25" to 5.25" wide fluorescent strip fixtures
- Available in 4ft or 8ft kits
- DLC Premium listing for all models maximizes rebate opportunities