


JOB NAME:DATE:TYPE:

COMMENTS:



LIGHT INFORMATION

Light Type	Integrated LED
CRI	90
Delivered Lumens	658
Color Temperature	3000K-6400K
LED Lifespan (L70)	50000
Light Direction	Ambient
Dimming Method	Touch Switch
Current Type	DC
Input Voltage	120-240
Total Wattage	30

DIMENSIONS & WEIGHT

Width (In)	20
Height (In)	36
Min Height (In)	36
Max Height (In)	36
Ext (In)	5.5
Weight (Lbs)	23.76

INSTALLATION

Mounting Type	J-Box
Rating	Damp
Hanging Support Type	Z-Bar

PRODUCT FINISH

Onyx White

PRODUCT FEATURES

Built-in USB-A and USB-C charging ports

CERTIFICATIONS & COMPLIANCE

