

LED FILAMENT LAMP

Model No. VG25-3020ad

LED **VG25-3020ad** delivers superior brightness, valuable energy savings and long lasting performance. LED Filaments along with heat-sink absence unmistakably mimic traditional bulb styles while providing greater light distribution. This G25 Class LED bulb comes in 2200K CCT (Warm White) for charming and hospitable environments.



Globe / Amber Glass

N/A

REPLACEMENT

4.5W

4.5 Watts

2200K
CCT

Warm White



Energy Efficient



Dimmable



Wet Rated



Enclosed
Fixture Suitable

Electrical Specifications


Model No.	Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	CCT
VG25-3020ad	4.5 W	120 V	250 lm	320°	N/A	2200 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan	Estimated Yearly Cost
80	55 lm/W	0.7	0.05 A	E26	15,000 Hrs.	\$ 0.54

Mechanical Specifications

Rating	Operational Temperature	Inner Box QTY.	Master Box QTY.	Dimensions(in.)	UPC Code
Wet Rated	-4°F - 104°F	N/A	50 pcs	3.14"(Ø) x 4.56"(H)	811174032304

Product Dimensions



Product Photometric Data

