

LEDVANCE DESIGN BUILD GUIDE

DOWNLIGHTS

RT66AS2000UNHD9SC3WHSS


NAED: 62923

12/16/21W
1100/1500/2000lm
2700/3000/3500/4000/5000K
120-347V
>90

SUPERIOR CLASS 6" downlight. IC rated, EMBB (field installable). White trim with semi specular reflector. Specular reflector, white reflector, and trim extender available.



RT85AS3300UNVD9SC8WHTAA


NAED: 62810

25/29/35W
2400/2800/3300lm
3000/3500/4000/5000K
120-277V
>90

PERFORMANCE CLASS 8" downlight. Hardwired; ideal for New Construction but can be used in retrofit projects. 0-10V Dimming, Non-IC Rated, EMBB (field installable). Uniform, glare free illumination. White trim. Bronze, satin, black trim; trim extender and rough-in available



RT45AS700UNVD9SC8WHTAA


NAED: 62805

7/8/9W
500/600/700lm
3000/3500/4000/5000K
120-277V
>90

PERFORMANCE CLASS 4" downlight. Hardwired; ideal for New Construction but can be used in retrofit projects. 0-10V Dimming, Non-IC Rated, EMBB (field installable). Uniform, glare free illumination. White trim. Bronze, satin, black trim; trim extender and rough-in available



PANEL

PANELF3BS045UNVD8SC724GWH



NAED: 62699

30/35/45W

3300/3850/5000lm

3500/4000/5000K

120-277V

>90

VALUE CLASS 2x4. Recessed, surface or suspended mount. Flange kit, surface mount kit and suspension kit available. Earthquake clips. PMMA lens. Uniform light. Aluminum frame for increased rigidity. Steel back. Field installed EMBB. 0-10V Dimming.



PANELF4BS050UNHD8SC724GWH



NAED: 62705

30/40/50W

3750/5000/6250lm

3500/4000/5000K

120-347V

>90

PERFORMANCE CLASS 2x4. Recessed, surface or suspended mount. Flange kit, surface mount kit and suspension kit available. Earthquake clips. PMMA lens. Uniform light. Aluminum frame for increased rigidity. Steel back. 6 knockouts. Field installed EMBB. 0-10V Dimming.



TROFFER

VOLUME6A/S044UNHD8SC724UWH



NAED: 62534

24/32/39/44W

3000/4000/4875/5500lm

3500/4000/5000K

120-347V

>80

VALUE CLASS 2x4. Controls ready for field installable push-in standalone PIR sensor. PIR sensor programmable via RF remote. 0-10V Dimming. Surface mount and flange kit available.



VOLUME6A/S044UNHD8SC724UWHE



NAED: 62829

MTO

24/32/39/44W

3000/4000/4875/5500lm

3500/4000/5000K

120-347V


>80

VALUE CLASS 2x4. MTO with EMBB. Controls ready for field installable push-in standalone PIR sensor. PIR sensor programmable via RF remote. 0-10V Dimming. Surface mount and flange kit available.



RETROFIT DOOR KIT

RDORKIT6AS032UNHD8SC722UWH



NAED: 62528

20/24/28/32W

2500/3000/3500/4000lm

3500/4000/5000K

120-347V

>80

VALUE CLASS 2x2. Controls ready for field installable push-in standalone PIR sensor. PIR sensor programmable via RF remote. 5 piece design. 0-10V Dimming



RDORKIT6AS044UNHD8SC724UWH



NAED: 62529

24/32/39/44W

3000/4000/4875/5500lm

3500/4000/5000K

120-347V

>80


VALUE CLASS 2x4. Controls ready for field installable push-in standalone PIR sensor. PIR sensor programmable via RF remote. 5 piece design. 0-10V Dimming



WRAP



WRAPHNGS060UNHD8SC748WH



NAED: 64118

30/40/50/60W

4290/5680/7050/8400lm

3500/4000/5000K

120-347V


>80

PERFORMANCE CLASS 4', 10.4" width. New optical design for maximum edge-to-edge uniformity. Controls ready for standalone or NLC. Toolless lens/light engine. Pre-wired with factory installed polarized wiring system for single circuit continuous row mounting. Ships with V-hooks. Optional Joiner Brackets and aircraft cable mounts.



STRIPS AND STAIRWELL

LNSLOT1A34UNHD8SC148CWH



NAED: 62453

34W

3400lm

3000/3500/4000K

120-347V

>80

VALUE CLASS 4' white architectural strip designed to be suspended/surface/recessed or wall mount. Linkable up to 20 units. 100% downward light (direct). White housing. L, T, and X connectors available. 0-10V dimming.



STAIR1AS45UNVD8SC748SWH



NAED: 65584

30/35/45W

3750/4340/5445lm

3500/4000/5000K


120-277V

>80

Built in high resolution ultrasonic bi-level sensor for stairwells. Specialized optics optimize the lighting in stairwells. Can be mounted on walls or at the intersection of walls and ceilings. Can be set to on-to-dim or on-to-off operation. 0-10V Dimming.



STRIP3AS055UNHD8SC748WH



NAED: 63786

22/35/45/55W

2860/4500/5850/7150lm

3500/4000/5000K

120-347V

>80

PERFORMANCE CLASS 4' strip; 2.8"W. Controls ready. Includes end-to-end mounting bracket, j-box cover & v-hooks. Factory pre-wired for continuous row mounting. Wire guard & adjustable aircraft cable mount (10 feet, 1 Pair).



VAPOR TIGHTS

VAPOR3AS050UNHD8SC748GRD



NAED: 62489

30/40/50W

4320/5760/7200lm

3500/4000/5000K

120-347V

>80

4'; 3.31"W Vapor tight with stainless steel mounting bracket, clips, and v-hooks included for surface or suspended mount. NSF Splash Zone. Aircraft cable attached to lens, lens and board are separate. 0-10V Dimming. MTO: daylight/motion sensor.



VAPOR3AS050UNHD8SC748GR



NAED: 65700

30/40/50W

4320/5760/7200lm

3500/4000/5000K


120-347V

>80

4'; 3.31"W Vapor tight with stainless steel mounting bracket, clips, and v-hooks included for surface or suspended mount. NSF Splash Zone. Aircraft cable attached to lens, lens and board are separate. 0-10V dimming.



VAPORILTS050UNHD8SC748



NAED: 65906

20/30/40/50W

2860/4260/5640/7000lm

3500/4000/5000K

120-347V

>80

PERFORMANCE CLASS 4', 4.3" wide. Polycarbonate lenses. 6kV surge protection. NSF Splash Zone. Controls ready for behind the lens microwave sensor. Integrated LED board and lens. Stainless Steel Clips. 0-10V dimming.



CANOPY

CANOPYS4AS020UNVD8SC2C5WH



NAED: 62539

10/15/20W

1250/1875/2500lm

3000/4000/5000K

120-277V

>80

PERFORMANCE CLASS white canopy. Slim, lightweight design. Mounting plate included. 0-10V dimming. Luminaire mounts to recessed outlet box (3" or 4") or can be pendant mounted (accessories not included). 12.5" and 16" mounting plate available.



CANOPYS4BS075UNVD8SC2C5BZ



NAED: 62542

40/60/75W

5000/7500/9375lm

3000/4000/5000K

120-277V

>80

PERFORMANCE CLASS bronze canopy. Slim, lightweight design. Mounting plate included. 0-10V dimming. Luminaire mounts to recessed outlet box (3" or 4") or can be pendant mounted (accessories not included). 12.5" and 16" mounting plate available.



CANOPYS4BS060UNVD8SC2G5BZ



NAED: 62549

MTO

40/50/60W

5000/6250/7500lm

3000/4000/5000K

120-277V


>80

MTO for garage lens. PERFORMANCE CLASS bronze garage. Slim, lightweight design. Mounting plate included. 0-10V dimming. Luminaire mounts to recessed outlet box (3" or 4") or can be pendant mounted (accessories not included). 12.5" and 16" mounting plate available.



JELLY JAR

JELLYJAR2AS020UNHD8SC2GR



NAED: 62448

10/20W
1000/2000lm
3000/4000/5000K
120-347V
>80

VALUE CLASS Ceiling, wall or pendant mount. Frosted glass lens. 180° adjustable mounting. Red or blue lens accessory available. Die cast Aluminum grey housing. Type V distribution. 0-10V Dimming.



FLEXMOUNT



HIGH BAYS

UFOHIBA3AS150UNVD8SC7WH



NAED: 62693

100/120/150W
15,000/18,000/22,500lm
3500/4000/5000K
120-277V
>80

VALUE CLASS. White housing. Controls ready for standalone or NLC via screw-in receptacle. Includes hook & 6' power & 3' dimming cord. NSF Splash zone. Accessories: refractor, reflector, lens, wire guard. Optional Surface or pendant mount bracket. EMBB Field installed.



UFO5AS320UNHD8SC7WH



NAED: 62300

240/280/320W
36,000/42,000/48,000lm
3500/4000/5000K
120-347V
>80

VALUE CLASS. White housing. Controls ready for standalone or NLC via screw-in receptacle. Includes hook & 6' power & 3' dimming cord. NSF Splash zone. Accessories: refractor, reflector, lens, wire guard. Optional Surface or pendant mount bracket. EMBB Field installed.



LNHIBA5AS300UNVD8SC1412WH



NAED: 62877

255/275/300W
36,700/38,700/41,100lm
4000/5000K
120-277V
>80

VALUE CLASS. Controls ready for standalone or Networked Lighting Controls via screw-in receptacle. Polycarbonate lens; no aisle lens. Comes with V-hook and 3' mounting chains. Accessories: wire guard, surface mount or pendant mount bracket. 0-10V Dimming.



AREA LIGHT

AREAFLD5AS300UNHD850T3BZ



NAED: 63312

180/240/300W
28,000/35,000/40,500lm
5000K
120-347V
>80

VALUE CLASS Type III Area Light. Controls Ready featuring screw-in receptacle for standalone or NLC controls. Ships with 3-pin NEMA receptacle + shorting cap optional photocell available. FLEXMOUNT: Universal mounting bracket included. Visor available for 4 sides: only use up to 3.



AREAFLD6AS080UNHDSC2ADJBZ



NAED: 64012

COMING SOON

40/60/80W
6,000/9,000/12,000lm
3000/4000/5000K
120-347V
>80

PERFORMANCE CLASS featuring OPTI-SELECT: Field Adjustable Type III, IV, V distribution no lens swap and opening the luminaire. 10kV Surge Protection: FLEXMOUNT: Universal mounting bracket included. Controls ready for standalone or networked lighting controls via screw-in receptacle. Visor available for 4 sides only use up to 3. Bird spikes available.



AREAFLD6AS150UNHDSC2ADJBZ



NAED: 64013

COMING SOON

90/120/150W
13,500/18,000/22,500lm
3000/4000/5000K
120-347V
>80

PERFORMANCE CLASS featuring OPTI-SELECT: Field Adjustable Type III, IV, V distribution no lens swap and opening the luminaire. 10kV Surge Protection: FLEXMOUNT: Universal mounting bracket included. Controls ready for standalone or networked lighting controls via screw-in receptacle. Visor available for 4 sides only use up to 3. Bird spikes available.



AREAFLD6AS300UNHDSC2ADJBZ



NAED: 64014

COMING SOON

180/240/300W
27,000/36,000/45,000lm
3000/4000/5000K
120-347V
>80

PERFORMANCE CLASS featuring OPTI-SELECT: Field Adjustable Type III, IV, V distribution no lens swap and opening the luminaire. 10kV Surge Protection: FLEXMOUNT: Universal mounting bracket included. Controls ready for standalone or networked lighting controls via screw-in receptacle. Visor available for 4 sides only use up to 3. Bird spikes available.



WALL PACKS

WALPAKN9AS080UNHD8SC2BZP



NAED: 63766

50/65/80W

7500/9750/12000lm

3000/4000/5000K

120-347V

>80

PERFORMANCE CLASS. Bronze housing. Integrated photocell can be disabled in the field. Glass lens. Accessories: visor; wire guard. Field installable standalone or networked lighting controls via screw-in receptable.



WALPAKC9AS035UNHD8SC2BZP



NAED: 65856

20/30/35W

3000/4500/5250lm

3000/4000/5000K

120-347V

>80

PERFORMANCE CLASS. Dark Sky compliant. Bronze housing. Integrated photocell can be disabled in the field. Polycarbonate lens. Field installable standalone or networked lighting controls via screw-in receptable. Hinged door housing and internal level. 0-10V Dimming. Bug Rating: B2U0G1



LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone: 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com

LEDVANCE is a registered trademark. The Bluetooth word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by LEDVANCE LLC is under license. All other trademarks are those of their respective owners. Specifications subject to change without notice.



SCAN TO FOLLOW US
ON SOCIAL MEDIA

