

# PRODUCT DATASHEET

## TROFFER 5A 1x4 (20, 25 or 30W) 4000K EMBB

SYLVANIA Volumetric Troffer Lumen Selectable | Troffer with selectable wattage



---

### Areas of application

- Offices
- Retail
- Hallways
- Multipurpose Rooms
- Hospitality

---

### Product features

- Lumen selectability increases the versatility of this product
- All models are DLC Standard
- Ideal for retrofits, delivering major energy savings vs. traditional lighting
- Standard 0–10V driver enables added energy savings via dimming
- Up to 125 LPW
- 3500K, 4000K, or 5000K color temperature
- 0–10V Dimmable
- CRI > 80



## TECHNICAL DATA

### Additional product data

|                              |                                                                                                                             |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Ordering Abbreviation        | VOLUME5AS030UNVD84014UWHE                                                                                                   |
| Abbrev. With Packaging Info. | VOLUME5AS030UNVD84014UWHE 1/CS 1/SKU                                                                                        |
| NAED                         | 61694                                                                                                                       |
| General Description          | ValueLED Volumetric 5A, 20/25/30 Watts, 125 LPW, 120-277V, 0-10V Dimmable, 80+ CRI, 4000K, 1x4, For lay in grid ceiling, EM |
| Warranty                     | 5 years                                                                                                                     |

### Electrical data

|                           |                     |
|---------------------------|---------------------|
| Nominal Wattage           | 20.00/25.00/30.00 W |
| Nominal voltage           | 120.00...277.00 V   |
| Power factor              | ≥0.90               |
| Total Harmonic Distortion | < 20 %              |

### Photometrical data

|                             |                   |
|-----------------------------|-------------------|
| Lumens                      | 2500/3125/3750 lm |
| Efficacy                    | 125 lm/W          |
| Color Temperature/CCT       | 4000 K            |
| Color Rendering Index (CRI) | > 80              |
| Luminaire Type              | Troffer           |

### Dimensions & Weight

|                |          |
|----------------|----------|
| Length         | 47.76 in |
| Width          | 11.97 in |
| Height         | 3.62 in  |
| Product weight | 10.32 lb |

### Materials & Colors

|                  |        |
|------------------|--------|
| Luminaire Finish | White  |
| Housing color    | White  |
| Housing          | Steel  |
| Mercury content  | 0.0 mg |

### Application & Mounting

|            |                        |
|------------|------------------------|
| Connectors | Plug, quick disconnect |
| Dimming    | Yes                    |

|                          |          |
|--------------------------|----------|
| Type of Dimming          | 0-10V    |
| Mounting                 | Recessed |
| Indoor/Outdoor           | Indoor   |
| Replaceable light source | No       |

### Lifespan

|                         |       |
|-------------------------|-------|
| Average Rated Life (hr) | 50000 |
|-------------------------|-------|

### BATTERY

|                     |                |
|---------------------|----------------|
| Type of Battery     | Lithium ion    |
| Lithium Ion Battery | Li ion battery |
| Battery size [GMS]  | Others         |

### Logistical data

|                   |        |
|-------------------|--------|
| Case Qty          | 1      |
| Case Length (in)  | 48.622 |
| Case Width (in)   | 12.756 |
| Case Depth (in)   | 3.150  |
| Case Cube (ft)    | 1.131  |
| Case Weight (lbs) | 12.967 |
| Pallet Qty        | 45     |

### Certificates & Standards

|                       |                    |
|-----------------------|--------------------|
| Certification Listing | RoHS / FCC / cULus |
|-----------------------|--------------------|

### EQUIPMENT / ACCESSORIES

- Optional flange kit

### Safety advice

- Luminaire lays in standard 15/16" and 9/16" T-grid ceilings

### DOWNLOAD DATA

| Spec Sheets and Product Documents                                                  |                           | Document name                                |
|------------------------------------------------------------------------------------|---------------------------|----------------------------------------------|
|  | Installation Guide        | SYLVANIA ValueLED Volumetric Troffer         |
|  | Product Family Spec Sheet | ValueLED Lumen Selectable Volumetric Troffer |

| Spec Sheets and Product Documents                                                |                           | Document name                                            |
|----------------------------------------------------------------------------------|---------------------------|----------------------------------------------------------|
|  | Product Family Spec Sheet | ValueLED™ Lumen Selectable Volumetric Troffer- Cut Sheet |

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.