





LED recessed luminaire for machines



Product-Nr.	153110-12
EAN:	4260556625485
Model:	FIELDLED EVO Integrated, M12 rear-side

Order number:	153110-12
Model:	FIELDLED EVO Integrated, M12 rear-side

Type:	LED recessed luminaire for machines
Illuminant:	SMD LED
Power consumption:	~39 W
Lamp luminous flux:	6000 lm
Lamp luminous efficiency:	155 lm/W
Light distribution:	Direct

Light colour:	5700K 3-step MacAdam
---------------	----------------------

Colour rendering (Ra):	>85
------------------------	-----

Supply voltage:	24V DC ± 10%
-----------------	--------------

Connection (connector):	M12 A-coded, rear side
-------------------------	------------------------

Degree of protection:	IP67/IP69K
-----------------------	------------

Class of protection:	III
----------------------	-----

Glare control:	Microprisms
----------------	-------------

Beam angle (optics):	100°
----------------------	------

Operating temperature:	-30 °C - +60 °C (-22 °F - 140 °F)
------------------------	-----------------------------------

Storage temperature:	-30 °C - +80 °C (-22 °F - 176 °F)
----------------------	-----------------------------------

Lamps lifetime:	> 100,000 h (L80/B10)
-----------------	-----------------------

Vibration resistance:	At 10 to 55 Hz (amplitude 0.35 mm (~0,01"))
-----------------------	---

Shock resistance:	Up to 50 g (~2 oz)
-------------------	--------------------

Housing material:	aluminium
-------------------	-----------

Cover material:	ESG (toughened tempered glass), shatterproof
-----------------	--

Height [B] x Width [C]:	30 mm x 96 mm (~1.18" x ~3.78"), frame: 5.6 mm x 132 mm (~0.22" x ~5.2")
-------------------------	--

Length [A]:	540 mm (~21,26")
-------------	------------------

Weight (net):	2200 g (~78 oz)
---------------	-----------------

Gross weight:	2550 g (~90 oz)
---------------	-----------------

Risk group (DIN EN 62471):	Free group
----------------------------	------------

Markings:	CE, UKCA, ETL Listed (5003529)
-----------	--------------------------------

Dimmable:	Optional via accessories
-----------	--------------------------

Made in:	Germany
----------	---------