



2' Highbay


Applications:

- Recessed Downlighting
- New/Remodel Construction
- Residential/Commercial Lighting

Product Information:

- 0-10V dimmable integrated driver
- Optional internally-mounted motion sensor
- High voltage (300-480V) driver available






Watt Selection



Knockouts



Motion Sensor



Accessories



Frosted Lens

-  60/80/110 Watt
-  15950 Lumens
-  120-277V Dimmable
-  Integrated LED
-  IP67 Rated
-  120-277V

RETAIL READY STAND OUT PACKAGING

11.5"



Packaging subject to size change
based on product size



HIGHBAY

NW-HB-L-110-2F-50K

LUMENS	60W - 8700 80W - 11600 110W - 15950
WATTAGE	60/80/110W
VOLTAGE	120-277V
TRIM	WH-White
COLOR TEMP	5000K
LIFE HOURS	50,000
CRI	80
DIMMABLE	Yes



HIGHBAY

NW-HB-L-165-2F-50K

LUMENS	125W - 18125 150W - 21750 165W - 23925
WATTAGE	125/150/165W
VOLTAGE	120-277V
TRIM	WH-White
COLOR TEMP	5000K
LIFE HOURS	50,000
CRI	80
DIMMABLE	Yes

