



MAX001V - T

 175 x 115 x H47 mm
6.88 x 3.22 x H1.61 inch

 157 x 82 x H41 mm
6.18 x 3.22 x H1.61 inch

 12 + 29 mm
0.47 + 1.14 inch

 0,14 kg / 0.30 lb

 -10 / 80 °C / 14 / 176° F

 Capacità / Capacity
0.527 lt



 Stampaggio: ad iniezione
Process: Injection molding

 Materiale / Materials
POLIPROPILENE/POLYPROPYLENE
NYLON (Serrature / Latches)



Shipping & Logistic info

12 pz. per cartone
12 pcs. x carton



1,95 Kg per cartone
4.30 lb gross weight



IP67
RATING

- Guarnizione ermetica / Watertight seal around lid
- Valvola automatica di pressurizzazione / Automatic pressure release valve
- Sistema di impilabilità / Stackable interlocking system
- Resistenza agli urti / Thick body material



SCREEN PRINTING & CUSTOM LABEL
SERIGRAFIA & ETICHETTA CUSTOM



CUSTOMIZED FOAM INLAY
INTERNI IN SPUGNA FUSTELLATA



LASER MARKING OR ENGRAVING
INCISIONE O MARCATURA LASER



CUSTOM COLOUR
COLORI CUSTOM