



ULR-IP54-16F-HO-27K
ULR-IP54-16F-HO-30K
ULR-IP54-16F-HO-35K
ULR-IP54-16F-HO-40K
ULR-IP54-16F-HO-50K

24V DAMP LOCATION HIGH OUTPUT LED RIBBON

Ideal for undercabinet, soffit, display cases and toe kick lighting.

ELECTRICAL SPECIFICATIONS:

- Voltage: 24VDC (LED driver required)
- Wattage: 4.4W per ft.
- Max Run: 20ft.
- Efficacy: 75~79LM/W per ft.

HOUSING SPECIFICATIONS:

- Cutting increment: Every 4 inches
- 3M double sided tape(9474LE) is preinstalled
- Operating temperature: -4°F - 104°F
- IP rating: IP54

CERTIFICATIONS: UL



DIMENSIONS:

16.4'(L) x 0.4"(W)

MODEL	WATTS PER FT.	VOLTAGE	LUMENS PER FT.	COLOR TEMP	REEL LENGTH	MAX RUN
ULR-IP54-16F-HO-27K	4.4W	24VDC	310LM	2700K	16.4FT.	20FT.
ULR-IP54-16F-HO-30K	4.4W	24VDC	310LM	3000K	16.4FT.	20FT.
ULR-IP54-16F-HO-40K	4.4W	24VDC	330LM	4000K	16.4FT.	20FT.
ULR-IP54-16F-HO-50K	4.4W	24VDC	350LM	5000K	16.4FT.	20FT.

OPTIONAL ACCESSORIES:



ULR-IN-HO-COUP-6I-WR
ULR-IN-HO-COUP-3F-WR



ULR-IN-HO-COUP-NO-WR



ULR-IN-HO-CONN-6I-WR
ULR-IN-HO-CONN-3F-WR
ULR-IN-HO-CONN-6I-PT
ULR-IN-HO-CONN-3F-PT

MODEL	DESCRIPTION
ULR-IP54-HO-COUP-6I-WR	Coupling to connect 2 high output ribbons, 6"
ULR-IP54-HO-COUP-3F-WR	Coupling to connect 2 high output ribbons, 3'
ULR-IP54-HO-COUP-NO-WR	Coupling to connect 2 high output ribbons, no wire
ULR-IP54-HO-CONN-6I-WR	Power feed cable, 1side ribbon connector, 1 side female socket to driver
ULR-IP54-HO-CONN-3F-WR	Power feed cable, 1side ribbon connector, 1 side female socket to driver
ULR-IP54-HO-CONN-6I-PT	Power feed cable, 1side ribbon connector, 1 side open end
ULR-IP54-HO-CONN-3F-PT	Power feed cable, 1side ribbon connector, 1 side open end

LIGHTING SPECIFICATIONS:

- Dimming: Dimmable using a magnetic driver
- LED: SMD2835 chip spaced 5/8" on center, 19 per foot, 0.23 wats each chip
- LED Type: SMD2835
- Total lumens: 310~350LM per ft.
- Color temperature: 2700K/3000K/3500K/4000K/5000K
- Color rendering index: 90
- Beam Angle: 120°

WARRANTY: 5 years

