



Master MAC-24WOSC 24" High Velocity Oscillating Wall Fan 3900 CFM, 1/3 HP, 120 Volt



- Perfect for the garage, barn, patio or workshop
- All-metal construction for durability
- Direct-drive motor with high airflow, up to 3900 CFM
- Oscillating fan head for directional airflow control
- Wall mount included
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading 24" High Velocity Oscillating Wall Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting all-metal construction. Plus, the tilt-angle head lets you direct the airflow wherever it is most convenient. Whether you're in the barn, relaxing on the patio, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. *Master – built for power.*



Features and Benefits

- Great for your home, garage, barn, or workshop
- All-metal construction for durability
- Direct-drive motor with airflow up to 3900 CFM
- 1/3 HP industrial motor
- Oscillating fan head for directional airflow control
- All-metal safety guard
- Wall mount included
- 3 variable speed settings for user preference
- Balanced blades for optimal airflow
- 1-year limited warranty

Key Specs

Model Number	MAC-24WOSC
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	40
Air Flow (CFM)	3900 / 3500 /2900
Motor Size (HP)	1/3

Variable Speed	Yes
Volts	120
Amps	2.1
Product Dimensions (L x W x H) (in.)	26 x 11 x 26

