

GRIPPS®

ANSI/ISEA
121-2023
COMPLIANT

H010402 GRIPPLOCK CABLE MKII 3MM X 120MM

Building on GRIPPS®'s original trusted design, the Gripplock Cable MKII features an ultra-low-profile locking head to reduce bulk and an increased certified load rating of 2.5kg / 5.5lb.

Crafted with a core band of aircraft-grade steel, it allows you to instantly create a permanent, heavy-duty connection point using your tool's existing hang-holes or slots. Capable of fitting through 4mm diameter holes, the MKII is 2mm smaller in diameter than its predecessor.

Installation remains completely effortless. Simply thread the cable through your tool, lock the heads together, and secure your equipment in seconds—no additional thread-locking compound required. Stronger, sleeker, and exceptionally reliable, the Gripplock Cable MKII makes retrofitting tools safer and easier than ever.

Available in packs of 5.



2.5 KG **5.5** LB

MAX LOAD:




New Collarless Design:
—4 mm / 0.16 in diameter




ENGINEERED FOR DROP PREVENTION

gripps.com

KEY FEATURES




1




Feed the smaller end through a hole in the tool.

2



Clip the two ends together to create a permanent connection point.



Your Griplock Cable is now ready to connect with a suitable GRIPPS® tether.

SPECIFICATIONS

SKU	MAX LOAD (TETHER)	MAX LENGTH (TETHER)	LENGTH
H010402-5	2.5 kg 5.5 lb	0.91 m 35.8 in	120 mm 4.72 in

@GRIPPSGLOBAL



#ConquerGravity