

LEDVANCE

THE RIGHT LIGHTING MATTERS

LINEAR HIGH BAY 5A

VALUE
CLASS

SIMPLIFYING YOUR WORK

- DUAL SELECTABLE: Three wattages and two CCTs in the same luminaire.
- V-hooks and 3-foot mounting chains are included
- CONTROLS READY: Compatible with LEDVANCE standalone or networked lighting controls, no wiring required.





LEDVANCE

ORDERING GUIDE

LNHIBA	5A	SXXX	XXX	D	8	SC14	12	WH
PRODUCT NAME	GENERATION	WATTAGE	VOLTAGE	DIMMING	CRI	COLOR TEMPERATURE	DIMENSIONS	COLOR/ FINISH
LNHIBA5A = Linear High Bay	5A = Generation 5A	S165 = 105/135/165W S220 = 175/195/220W S300 = 255/275/300W	UNH = 120-277V HUV = 277-480V	D = 0-10V	80 = >80	SC14 = 4000/5000K	12 = 1'X2'	WH = White

FEATURES

DUAL SELECTABLE

Allows customization based on the application and helps minimize inventory.



CONTROLS

READY

Shipped with pre-wired sensor base; ready to accept optional standalone or networked lighting controls, LEDVANCE LINK™.

INSTALLATION

3' chain and v-hooks included; Optional surface mount brackets, pendant mount brackets, and aircraft cable mounts are available.

HOUSING & LENS

Powder coated white finish and UV stabilized polycarbonate lens provides a robust and durable design.

ACCESSORIES



FIXTURE CONTROLLER W/PIR SENSOR (3.5MM) 62634



CONTROLLER 62630



PIR White: 62664



MICROWAVE White: 65622



SENSOR ADAPTER FOR LEDVANCE LINK™ SENSORS 63652



REMOTE 65623



WIRE GUARD 62906 & 62907



CHAIN MOUNT 60573 & 60574

*Additional accessories can be found on spec sheet.

LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone: 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com

LEDVANCE is a registered trademark. The Bluetooth® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by LEDVANCE LLC is under license. All other trademarks are those of their respective owners. Specifications subject to change without notice.



SCAN TO FOLLOW US
ON SOCIAL MEDIA



Spec Sheet



Install Guide