


INSTRUCTION MANUAL

300 CFM BLOWER FAN

MODEL 20711006-180W-16



SAVE THIS MANUAL FOR FUTURE REFERENCE.

IMPORTANT SAFETY INSTRUCTIONS

WARNING! READ AND SAVE THESE INSTRUCTIONS. Failure to follow all instructions listed below may result in electric shock, fire and/or serious personal injury.

- 1. CONSIDER WORK AREA ENVIRONMENT.** Don't use the fan blower in damp or wet locations. Don't use the fan blower in presence of flammable liquids or gases. Don't restrict the air intake.
- 2. USE SAFETY GLASSES.** Also use face or dust mask if work area is dusty.
- 3. DON'T ABUSE CORD.** Never pull the fan blower by its cord or yank it to disconnect from receptacle. Keep cord away from heat, oil, and sharp edges.
- 4. SECURE FAN BLOWER** if used in an unstable area such as a moving boat, R.V., etc.
- 5. MAINTAIN FAN BLOWER.** Keep blower, motor and blower wheel clean. For safer operation, follow instructions for attaching accessories. Keep handle dry, clean and free from oil, grease and water.
- 6. DISCONNECT FAN BLOWER** when not in use, before servicing, and when attaching accessories.
- 7. NEVER** stick a screwdriver or any other object into the air discharge grill or air intake areas.
- 8. INSPECT FOR DAMAGE** before using the fan blower. Determine before use if it will operate properly. Check for alignment and/or binding of the motor and blower wheel. Inspect cord periodically for damage. Check the switch by turning the fan blower on and off while unit is plugged in.
- 9. REPLACEMENT PARTS.** When servicing, use only genuine parts supplied by the manufacturer for your model.
- 10. WARNING:** To reduce the risk of fire or electric shock, do not use the fan blower with any solid-state speed control device.
- 11. WARNING:** To reduce the risk of electric shock, do not expose the fan blower to rain or water.

12. CAUTION: Automatically Operated Device - To reduce the risk of injury, always disconnect from power supply before servicing or attaching accessories.

TECHNICAL SPECIFICATIONS

Model: 20711006-180W-16
Rated Voltage: 120V~
Rated Frequency: 60Hz
Rated Loads: 12A
Motor Power: 180W
Speed: 3 settings
Air Volume: max. 300 cubic feet per minute
THERMAL PROTECTION

MAINTENANCE

- 1. WARNING:** Make sure that the fan blower is switched off and disconnected from the power supply before starting any cleaning or maintenance procedures.
- 2.** Don't use lacquer thinner or similar solvents to clean the plastic parts.
- 3.** Don't use steel wool, wire brush, abrasive pads or cleaners to clean the fan blower.
- 4.** To reduce the risk of electric shock, all repairs must be done by qualified electricians.