

LED PAR30 LAMP

Model No. EP30-11W5040cecs-2

LED **EP30-11W5040cecs-2** delivers superior brightness, valuable energy savings, long lasting performance and true color perception. These short neck PAR30 LED spot bulbs are ideal for task lighting due to its uniform *bright white light (4000K) and replace conventional 75 Watt incandescent light bulbs. Enjoy features such as: Instant on, dimming options, energy efficient, 90+CRI, and damp rated.



75W

REPLACEMENT

11W

11 Watts

4000K

Bright White

**2
PACK**

Twin Pack



90+ CRI



Dimmable



Wet Rated

Electrical Specifications


Model No.	Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	CCT
EP30-11W5040cecs-2	11 W	120V	975 lm	40°	N/A	4000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan	Estimated Yearly Cost
90+	88 lm/W	0.7	0.1 A	E26	25,000 Hrs.	\$ 1.32

Mechanical Specifications

Rating	Operational Temperature	Inner Box QTY.	Master Box QTY.	Dimensions(in.)	UPC Code
Wet Rated	-4F - 104 F	2 pcs	20 pcs	3.74"(Ø) x 3.62"(H)	811174034124

Product Dimensions



Product Photometric Data

