

PRODUCT DATASHEET

WRAP FVL DUAL SELECTABLE 2FT S30W 3CCT 120-347V

WRAP FVL | Wrap luminaire with slim body design and selectable CCT and wattage



Areas of application

- Offices
- Retail
- Closet storage spaces when installed per NEC 410.16 requirements
- Education
- Hallways
- Manufacturing

Product features

- Selectable CCT: 3500/4000/5000K
- Wattage Selectable
- Diffuse acrylic lens provides edge-to-edge illumination
- Pre-wired for field installation of microwave or PIR motion/daylight sensors
- White powder coated metal body
- Toolless lens and light engine removal
- Screw-In LINK™ compatible
- Includes V-hook mounting bracket

TECHNICAL DATA

Additional product data

Ordering Abbreviation	WRAP/FVL/S030UNHD8SC7/24WH
Abbrev. With Packaging Info.	WRAPFVLS030UNHD8SC724WH 4/CS 1/SKU
SKU UPC	0046135641152
NAED	64115
General Description	Wrap, Value Line, selectable wattage, 120-347V, 0-10V dimming, 80+CRI, CCT selectable, 2ft, white
Warranty	5 years

Electrical data

Nominal Wattage	30.00/25.00/20.00/15.00 W
Nominal voltage	120.00...347.00 V
Power factor	≥ 0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	3900/3250/2600/1950 lm
Efficacy	130 lm/W
Color Temperature/CCT	3500/4000/5000 K
Color Rendering Index (CRI)	> 80
Luminaire Type	Wrap

Dimensions & Weight

Length	24.02 in
Width	5.2 in
Height	3.94 in
Product weight	3.2 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Metal
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-40...+50 °C
Maximum Operating Temperature	122 °F
Minimum Operating Temperature	-40 °F
Dimming	Yes

Type of Dimming	0-10V
Mounting	Surface
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	100000
-------------------------	--------

Logistical data

SKU Qty	1
Case Qty	4
Case Length (in)	25.394
Case Width (in)	11.614
Case Depth (in)	9.606
Case Cube (ft)	1.640
Case Weight (lbs)	16.277
SKU UPC	0046135641152
Pallet Qty	96

Certificates & Standards

Certification Listing	RoHS / FCC
-----------------------	------------

Optional accessories

Product image	Product name	UPC
	CABLE MOUNT 10FT	OS63906
	ADAPTER PIN BRACKET L-SHAPE ADJUSTABLE	OS63909
	Standalone PIR Motion sensor 3.5mm Screw-in 19.7ft 12V	OS63908
	CHAIN MOUNT LNHIBA2A/CHAINM	OS60573
	Standalone Microwave Motion Sensor Behind the lens 19.7ft 12V	OS63907

Product image	Product name	UPC
	Standalone Commissioning Remote G2 VAPOR/WRAP/STRIP/PANEL	OS66592
	LINK WIRELESS CONTROLLER 5 KEY BATTERY BLE	OS62636
	LINK CONTROLLER 3.5mm AUX12V BLE	OS62630
	LINK SENSOR PIR 40FT 3.5mm BLE WH	OS62634

EQUIPMENT / ACCESSORIES

- V-hooks

Safety advice

- cULus listed to UL1598 and CSA C22.2 luminaire standards
- 2.5kV surge protection
- Indoor use

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	Wrap FVL Installation Guide
	Product Family Spec Sheet	LEDLUM209 DUAL SELECTABLE WRAP FVL
Photometric and lighting design files		Document name
	IES file (IES)	Wrap FVL IES Files
	IES file (IES)	Wrap FVL IES Files

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.