


JOB NAME:

DATE:

TYPE:

COMMENTS:



LIGHT INFORMATION		DIMENSIONS & WEIGHT		PRODUCT FINISH	
Light Type	Integrated LED	Length (In)	9	Polished Nickel	
CRI	90	Width (In)	5.5	SHADE FINISH	
Delivered Lumens	227	Height (In)	13	Organic Clear Glass	
Color Temperature	3000K	Min Height (In)	24.25	ADDITIONAL INFORMATION	
LED Lifespan (L70)	50000	Max Height (In)	158.25	Power Wire Length (In)	144
Light Direction	Ambient	Weight (Lbs)	2.75	Replaceable LED	Yes
Dimming Method	Triac/Elv	INSTALLATION		CERTIFICATIONS & COMPLIANCE	
Current Type	DC	Mounting Type	J-Box		
Input Voltage	120	Rating	Dry		
Total Wattage	5	Hanging Support Type	Aircraft Cable		