

Seamless Protection For Your Most Critical Environments

Scientific Products
and Solutions





▶ 1 OUR SOLUTIONS

- 2 Kimtech™ Brand
- 4 Are You Dressed For Success?™
- 6 Here's What Success Looks Like
- 8 The RightCycle Program
- 10 APEX

▶ 11 PROTECTIVE APPAREL

- 14 Kimtech™ Sterile Cleanroom Apparel
- 16 Kimtech™ Non-Sterile Cleanroom Apparel
- 23 Additional Products & Accessories
- 26 Kimtech™ Kimguard™ Sequential Sterilization Wrap

▶ 27 GLOVES

- 30 Kimtech™ Sterile Cleanroom Gloves
- 32 Kimtech™ Non-Sterile Cleanroom Gloves
- 38 Kimberly-Clark™ Exam Gloves
- 42 KleenGuard™ and Jackson Safety® Gloves

▶ 43 MASKS

- 46 Kimtech™ Sterile Cleanroom Masks
- 47 Kimtech™ Cleanroom Masks
- 49 Kimberly-Clark™ Lab Masks

▶ 51 WIPERS

- 52 Kimtech Pure™ Wipers
- 54 Kimtech Science™ Wipers
- 55 Kimtech Science™ Bench Top Protector
- 56 Kimtech™ Wipers
- 57 WypAll® Wipers

▶ 59 EYEWEAR

- 60 Safety Glasses
- 63 Smith & Wesson® Eyewear
- 64 Goggle Protection

Protection for People & Processes

Kimberly-Clark Professional understands the challenges you face in protecting your process from contamination and your people from harm. We also understand how you strive to maintain the highest laboratory and cleanroom standards, while meeting your sustainability goals. We have solutions that can minimize contamination and risk while increasing productivity and reducing waste. Let us show you how.





Protection: When and Where it Counts

When it comes to protection, you can't cut corners. You need reliable, trusted solutions that will deliver the highest level of assurance — seamlessly.

Kimtech™ Brand solutions provide sterile and clean-processed apparel options that will close the gaps in contamination, effectively and efficiently, while delivering comfort to your employees. And that's not all. The Kimtech™ Brand offers innovative gowning technologies, sterile and non-sterile glove products and task-engineered wipers that deliver precision performance for all your lab and cleanroom needs.

Scientifically proven. Intuitively designed. Reliable.

For protection against known and unknown risks, put your trust in the **Kimtech™** Brand.



If your garments
are compromised,
your process could be too.

Are You
Dressed
For Success?™



Contamination is a People Problem.

To avoid cleanroom contamination, we have to look at its source: PEOPLE. They are the largest contributor.

What stands between you and the risk of contamination? **Your choice of garment.**

Selecting the right garment can reduce the contamination risk dramatically.

The Good News: We Make It Simple.

Being **Dressed For Success™** means choosing a garment that can control contamination and gives you the assurance to do your best work.

Contamination is bad for business, especially for an industry where purity is paramount.

Before you get dressed, turn to the experts in sterile garments — **Kimtech™ Sterile Single-Use Apparel** for seamless protection when and where it counts.

There are big differences between Kimtech™ Sterile Single-Use Apparel and Laundered Garments:

› SINGLE-USE GARMENTS

Kimtech™ sterile single-use garments are engineered to reduce contamination risk, offering significantly higher Bacterial Filtration Efficiency (BFE) ratings than laundered reusable apparel. And they're sterile every time — **guaranteed.**



Bacterial Filtration Efficiency (BFE)



Strong barrier for fine particles and liquids

› LAUNDERED GARMENTS

Laundered garments typically contain a single layer of woven polyester-blend fabric, which may degrade after multiple laundering and sterilization cycles — leading to BFE declines of more than 25% after an average of five washes.¹



Bacterial Filtration Efficiency (BFE)



Fabric degradation at the submicron level — enough to allow bacteria to penetrate

› For more information, visit www.kimtech.com/dress-for-success

¹ Kimberly-Clark Test Study

Here's What Success Looks Like



▶ Our garments close the gaps in contamination and offer cloth-like comfort through a 100% polypropylene breathable SMS (Spunbond Meltblown Spunbond) fabric.

CONTAMINATION CONTROL FEATURES:

Advanced Clean-Don™ Technology

Lowers contamination risk and makes sterile donning easier — minimizing the chances of workers touching the outside of garments or garments touching the floor

Each Garment Sealed in Multi-Layer Packaging

To guarantee sterility

Secure Fit to Reduce the Risk of Particles Escaping

And a gap guard for additional protection

Snap Technology on Arms and Legs

Built-in snaps automatically release as the garment is put on — lowering the risk of it touching the floor

Inside-Out Fold

Visible blue line along the inside of the garment signals the proper place to hold while gowning and helps workers avoid touching the outside of the garment

Built-in Thumb Loops

Keep garment sleeves from rolling back and exposing the arm or wrist

Protects the Shoelace Area

Closing a potential contamination gap

Plus:



Recyclable via
The RightCycle Program

Divert these previously hard-to-recycle items from your waste stream

What You Need

FOR ISO 5 THROUGH ISO 8 CLEANROOM ENVIRONMENTS

Contain submicron particles, from head to toe, with seamless protection and comfort for ISO 3 or higher cleanrooms.

ISO
5

GRADE A

Sterile filtration, filling & stoppering, lyophilization

- Kimtech™ A5 Cleanroom Apparel, clean processed with Clean-Don™ Technology (see pages 14-17)
- Kimtech™ M5 Cleanroom Face Masks (see page 47)
- Kimtech™ G3 White Nitrile Gloves & Kimtech™ G3 Latex† Gloves (see pages 32-34)

ISO
6

GRADE B

Activities in areas directly surrounding Grade A zone

- Kimtech™ A6 Liquid Splash Protection Coverall with Hood (see page 18)
- Kimtech™ M6 Cleanroom Face Masks (see page 48)
- Kimtech™ G3 White Nitrile Gloves & Kimtech™ G3 Latex† Gloves (see pages 32-34)

ISO
7

GRADE C

Drug compounding, compression, coating

- Kimtech™ A7 Certified Liquid Barrier Gown (see page 19)
- Kimtech™ M7 Veils (see page 48)
- Kimtech™ G3 NXT™ Nitrile Gloves & Kimtech™ G3 Blue Nitrile Gloves (see pages 32-34)

ISO
8

GRADE D

Material staging, labeling and packaging, laboratory

- Kimtech™ A8 Cleanroom Apparel (see pages 20-22)
- Kimtech™ G3 NXT™ Nitrile Gloves & Kimtech™ G3 Blue Nitrile Gloves (see pages 32-34)



* CAUTION: This product contains natural rubber latex which may cause allergic reactions.



The RightCycle Program

Giving Gloves and Garments New Life

600 tons & counting
Waste diverted since 2011

Sustainability matters to you and to us. That's why we created The RightCycle Program, the first large-scale recycling program for non-hazardous lab, cleanroom and industrial waste. Since 2011, we've helped hundreds of customers divert more than 600 metric tons of waste. We can do the same for you by turning your used gloves and garments into flowerpots, patio furniture and other useful products.


At Kimberly-Clark Professional, we're always working to reduce the environmental impact of our products. Reducing our dependence on the world's natural resources, leaves more for the future — for our children, for the planet and for our businesses. We strive to help customers like you reach your zero waste-to-landfill goals. The RightCycle Program is part of this commitment and one very important way for us to work together, one ton of waste at a time.



Apparel and gloves are worn in your facility.



Used products are collected and shipped to our recycling centers.



Used products are sorted and processed into plastic pellets.



Materials are molded into new plastic products and durable goods.



“For me, the biggest appeal about RightCycle is that it’s the start of an EPR, an Extended Producer Responsibility, for a material that we don’t often think about. Gloves are a high-volume, fast-moving commodity used by almost every industry. Once people start getting good at recycling primary commodities, such as paper and plastic, we’re going to have to move to secondary commodities. Gloves bring you to that next level.”

— Shantanu Pai
Assistant Sustainability Researcher,
Illinois Sustainable Technology Center (ISTC)



Look for this symbol to see
which products are eligible for
The RightCycle Program.

For more information, visit: www.kimtech.com/rightcycle

APEX Makes it Happen

When you're transitioning to a new brand of products, you want the changeover to be seamless and worry-free. That's where APEX comes in. It's our promise to you to make the conversion to Kimtech™ Brand products as successful as possible.

APEX is a complimentary training program that effectively engages employees, ensuring protection of the scientific process while enhancing efficiency and performance. Expert consultants work with employees on everything from aseptic technique and best practices to standard operating procedures (SOP) review and physical gown and glove training.

APEX is an essential component of our solutions and another example of what makes Kimberly-Clark Professional so exceptional.

APEX

“APEX is invaluable.
It helps with ‘big change’
for customers.”

- Kimberly-Clark Professional distributor



KIMTECH™

Protective Apparel

Kimtech™ Brand apparel provides seamless protection when and where it matters most — closing the gaps in your protection. As a global leader in lab and cleanroom PPE, Kimberly-Clark Professional products work together to enhance comfort, compliance and productivity.



With innovative features such as Clean-Don™ Technology and built-in thumb loops, our apparel provides protection for the scientific process and peace of mind for workers. Whether you need sterile or non-sterile apparel, the Kimtech™ Brand has got you covered. And that is not all — our apparel and accessories are recyclable via The RightCycle Program.



Symbols Key



Sterile



Recommended for ISO Class 5 or higher cleanroom



Recommended for ISO Class 6, 7, 8 or higher cleanroom



RightCycle by Kimberly-Clark Professional™



Recommended for ISO Class 7, 8 or higher cleanroom



Recommended for ISO Class 8 or higher cleanroom

Find Your Fit

What type of apparel suits you best? These easy-to-use selection charts will help you choose the right products for your workers and your environment.

Category	ISO**	Ideal For	Suggested Use	Performance		
				Best	Better	Good
A5 Sterile			Compounding, Mixing, Filling, Cleaning	●		
A5 Non-Sterile		Cleanroom environments	Non-Sterile Compounding, Mixing, Filling, Cleaning			
	ISO 5	ISO Class 5 Aseptic Cleanroom GRADE A (Former FED-STD-209E; Class 100)		●		
	ISO 6,7,8	ISO Class 6, 7, 8 Bioburden control areas GRADE B/C/D (Former FED-STD-209E; Class 1,000, 10,000, 100,000)				
A6 Non-Sterile		Cleanroom environments	Non-Sterile Pharmaceutical Manufacturing, Bio-Medical Research, Pharmaceutical Compounding, Biotechnology		●	
	ISO 6,7,8	ISO Class 6, 7, 8 Bioburden control areas GRADE B/C/D (Former FED-STD-209E; Class 1,000, 10,000, 100,000)				
A7 Non-Sterile		Cleanroom environments	Non-Sterile Laboratory, Testing, Compounding Preparation Areas		●	
	ISO 7,8	ISO Class 7, 8 Bioburden control areas GRADE B/C/D (Former FED-STD-209E; Class 1,000, 10,000, 100,000)				
A8 Non-Sterile		Cleanroom environments	Packaging and Distribution Areas Non-Sterile Production			●
	ISO 8	ISO Class 8 Bioburden control areas GRADE B/C/D (Former FED-STD-209E; Class 1,000, 10,000, 100,000)				

** ISO compatibility is dependent on the equipment capabilities within your cleanroom.

MINIMAL GOWNING REQUIREMENTS:	Bouffant Cap	Hood	Beard Cover	Face Mask	Lab Coat/ Gown	Coverall	Shoe Cover	Boots	Gloves	Safety Glasses	Goggles
ISO Class 5 (Class 100)	●	●	●	●		●	●	●	●		●
ISO Class 6 (Class 1,000)	●	●	●	●		●	●	●	●		●
ISO Class 7 (Class 10,000)	●		●	●	●	●	●		●	●	
ISO Class 8 (Class 100,000)	●		●		●	●	●		●	●	

Cleanroom Classifications		
ISO Class	ISO Class Limits ²	FS209 Class Limits ³
ISO 3	35	1
ISO 4	352	10
ISO 5	3,520	100
ISO 6	35,200	1,000
ISO 7	352,000	10,000
ISO 8	3,520,000	100,000
ISO 9	35,200,000	—

² [particles / m3 of air] for particles equal to and larger than 0.5 microns

³ [particles / ft3 of air] for particles equal to and larger than 0.5 microns

Sterile Cleanroom Apparel

Also known as Kimtech Pure™ Brand

Kimtech™ A5 Sterile Cleanroom Apparel

Clean Processed with Clean-Don™ Technology

ISO 5

S




▶ PRODUCT FEATURES

- **Highly visible blue line** along the inside of the garment signals the proper place to grasp while gowning, helping workers to avoid touching the outside of the garment
- **Cloth-like comfort** is delivered by the SMS (Spunbond Meltblown Spunbond) material
- **Built-in thumb loops** keep garment sleeves from rolling back and exposing arm or wrist
- **Innovative inside-out fold** pattern presents the inside of the garment as the package is opened, reducing the risk of touching and contaminating the outside of the coverall
- **Patented telescoped arms and legs with snap technology** feature built-in snaps that gather up legs and arms to lower the risk of touching the floor, then automatically release as garment is put on



Kimtech™ Apparel SMS Fabric

Outer Layers – Cloth-like, yet tough and abrasion-resistant spunbond polypropylene



Middle Layers – Intricate web of microfibers that filter out many water-based liquids and dry particulates

TYPICAL USES

(ISO 5-8
Cleanroom Environments)

- Compounding
 - Mixing
 - Filling
 - Cleaning

A5 Sterile Integrated Hoods

- Oval head design to accommodate different hairstyles and head shapes
- Optimized viewing to limit skin exposure around forehead and cheeks
- Integrated hood and mask to close gaps in protection

A5 Sterile Elasticized Hoods

- Stretch fit elastic hood and opening
- Tunneled overseams to prevent particle shedding
- Clean-Don™ Technology ties for easy donning and a more secure fit

A5 Sterile Boot Covers

- Side grasp ties for secure fit
- Vinyl edge to reduce slipping and liquid penetration
- 3 sizes available (S/M, L/XL, Universal)

A5 Sterile Sleeve Protectors

- Blue-line donning signal feature
- Thumb loops keep sleeves from rolling back and exposing arm or wrist



Kimtech™ A5 Sterile Cleanroom Apparel⁴ ⁴ Gamma Irradiated SAL:10⁻⁶

Code	Description	Size	Total/Case
Coverall			
88800	Coverall, Sterile	S	25
88801	Coverall, Sterile	M	25
88802	Coverall, Sterile	L	25
88803	Coverall, Sterile	XL	25
88804	Coverall, Sterile	2XL	25
88805	Coverall, Sterile	3XL	25
88806	Coverall, Sterile	4XL	25
12917	Coverall, Sterile	5XL	25
12914	Coverall, Sterile	6XL-8XL	25
Hood			
40616	Elasticized Hood, Sterile	Universal	100
47677	Integrated Hood and Mask, Sterile	XL	75
36072	Integrated Hood and Mask, Sterile	Universal	75
25797	Hood with Ties, Sterile	Universal	100
88807	Hood, Sterile	Universal	100
Sleeve Protector			
36077	Sleeve Protector, Sterile	18" length	200
89791	Cleanroom Packaged Sleeves, Sterile, extra long, Blue (EtO sterilized)	Universal 23.5" length	100
Boots			
31683	Boots w/ Grasp Ties and Vinyl Edge, Sterile	S/M	100 Pairs
31697	Boots w/ Grasp Ties and Vinyl Edge, Sterile	L/XL	100 Pairs
31696	Boots w/ Grasp Ties and Vinyl Edge, Sterile	Universal	100 Pairs
12922	Boots, w/ Ties, Vinyl, Sterile	S/M	100 Pairs
12920	Boots, w/ Ties, Vinyl, Sterile	XL/2XL	100 Pairs
88808	Boots, w/ Ties, Vinyl, Sterile	Universal	100 Pairs

Non-Sterile Cleanroom Apparel

Also known as Kimtech Pure™ Brand

Kimtech™ A4 Sleeve Protectors

▶ PRODUCT FEATURES

- Blue-line donning signal feature
- Thumb loops keep sleeves from rolling back and exposing arm or wrist

Code	Description	Size	Total/Case
49815	Sleeve Protector	18"	200
49816	Sleeve Protector	21"	200




Kimtech™ A5 Cleanroom Apparel

Clean Processed with Clean-Don™ Technology



▶ PRODUCT FEATURES

- **Cloth-like comfort** is delivered by the SMS (Spunbond Meltblown Spunbond) material
- **High neck collar** to control contamination risk
- **Elastic waist band** for a proper fit
- **Built-in thumb loops** keep garment sleeves from rolling back and exposing arm or wrist
- **Nine sizes available** (Small-8XL)
- **Individual and bulk pack options**



A5 Integrated Hood & Mask

- Oval head design to accommodate different hairstyles and head shapes
- Optimized viewing to limit skin exposure around forehead and cheeks
- Integrated hood and mask to close gaps in protection

A5 Boot Covers

- Ties for secure fit
- Vinyl sole



Kimtech™ A5 Cleanroom Apparel, Non-Sterile



Individually Packed Code	Bulk Packed Code	Description	Size	Total/Case
Coverall				
88842	49831	Coverall	S	25
88843	49832	Coverall	M	25
88844	49833	Coverall	L	25
88845	49834	Coverall	XL	25
88846	49835	Coverall	2XL	25
88847	49836	Coverall	3XL	25
88848	49837	Coverall	4XL	25
12916	49838	Coverall	5XL	25
12915	49841	Coverall	6XL-8XL	25



Hood				
49828		Integrated Hood and Mask	Universal	75
25796		Hood with Ties	Universal	100
88849		Hood	Universal	100



Boots				
12921		Boots with Ties	S/M	200
12919		Boots with Ties	L/XL	200
88850		Boots with Ties	Universal	200

Non-Sterile Cleanroom Apparel

Also known as Kimtech Pure™ Brand

Kimtech™ A6 Liquid Splash Protection Coverall with Hood



▶ PRODUCT FEATURES

- High-performance laminated film for the front panel, hood, arms and legs
- Lightweight, breathable filter material for the back panel to keep workers safe and cool
- Suitable for ISO 7 and 8/Grade C & D cleanrooms
- 94% Bacterial Filtration Efficiency (BFE)
- Built-in thumb loops and elastic cuffs
- Innovative origami-inspired fold design to reduce gowning time

APPLICATIONS

- Non-Sterile Pharmaceutical Manufacturing
- Bio-Medical Research
- Pharmaceutical Compounding
- Biotechnology



Bulk Packed Code	Description	Size	Total/Case
47681	Coverall, White	S	25
47682	Coverall, White	M	25
47683	Coverall, White	L	25
47684	Coverall, White	XL	25
47685	Coverall, White	2XL	25
47686	Coverall, White	3XL	25
47687	Coverall, White	4XL	25

Kimtech™ A7 Certified Liquid Barrier Gown

ISO
6,7,8

▶ PRODUCT FEATURES

- Seamless front and closed back
- Enhanced liquid barrier protection — fabric tested per ASTM F1670, F1671 and F739-12 for permeation of chemotherapy drugs and hormones
- Easy don-and-doff design to reduce contamination risk and prevent chemicals from getting on clothing or skin
- Thumb loops to maintain glove and garment interface
- Low lint to minimize contamination
- Meets USP <800> guidelines by providing seamless protection against hazardous drugs



Code	Description	Size	Total/Case
47992	Gown, Blue	S/M	100
47993	Gown, Blue	L/XL	100
47994	Gown, Blue	2XL	100

10 bags of 10; 100 per case

Kimtech™ A7 Cleanroom Lab Coat

ISO
7,8



▶ PRODUCT FEATURES

- Enhanced chemical and biological protection
- Thumb loops to maintain glove and garment interface
- Low lint to reduce contamination risk

Bulk Packed Code	Description	Size	Total/Case
47651	Lab Coat with Thumb Loops	S	30
47652	Lab Coat with Thumb Loops	M	30
47653	Lab Coat with Thumb Loops	L	30
47654	Lab Coat with Thumb Loops	XL	30
47655	Lab Coat with Thumb Loops	2XL	30
47656	Lab Coat with Thumb Loops	4XL	30
47657	Lab Coat with Thumb Loops	6XL	30

High mandarin collar — to reduce the risk of contamination

Advanced Barrier Fabric for better liquid and dry particle protection

Elastic wrist and thumb loops for full wrist coverage



Non-Sterile Cleanroom Apparel

Also known as Kimtech Pure™ Brand

Kimtech™ A7 Ankle High Shoe Covers




▶ PRODUCT FEATURES

- Protects the shoelace and ankle areas not addressed by traditional shoe covers
- Delivers a higher barrier of liquid protection⁵ and superior grip
- Thread color helps to identify the size (Universal & L/XL)

Two elastic bands above and below the ankle for enhanced fit and coverage

30% more material added to cover the ankle vs. a standard shoe cover

Vinyl anti-skid soles for better grip

 Key features have been highlighted for illustration purposes only.

Bulk Packed Code	Description	Thread Size Indicator	Size	Total/Case
47972	Ankle High Shoe Cover with Vinyl Sole	White	Universal	300
47973	Ankle High Shoe Cover with Vinyl Sole	Black	L/XL	300

Kimtech™ A8 Cleanroom Apparel



▶ PRODUCT FEATURES

- A comfortable, lightweight innovative fabric that moves with the worker
- Built-in thumb loops to protect people and processes
- High neck collar to control contamination risk
- Double bagged, packaged for the cleanroom

APPLICATIONS

- Non-Sterile Pharmaceutical Manufacturing
- Bio-Medical Research
- Pharmaceutical Compounding
- Biotechnology

Bulk Packed Code	Description	Size	Total/Case
47951	Coverall	S	25
47952	Coverall	M	25
47953	Coverall	L	25
47954	Coverall	XL	25
47955	Coverall	2XL	25
47956	Coverall	3XL	25
47957	Coverall	4XL	25




⁵As compared to SMS

Kimtech™ A8 Certified Lab Coats & Jackets



▶ PRODUCT FEATURES

- Light fluid protection
- Protective 3-layer SMS fabric
- All coats and jacket feature soft knitted cuffs
- Available with extra protection fabric with blood strikethrough resistance



Kimtech™ A8 Lab Coat — mid-calf length

Bulk Packed Code	Color	Collar Type	Reinforced Pockets/Snaps	Size	Total/Case
Kimtech™ A8 Certified Lab Coat (Formerly known as Lab Coat – Basic™)					
10120	White	Traditional	2/4	S	25
10121	White	Traditional	2/4	M	25
10122	White	Traditional	2/4	L	25
10123	White	Traditional	2/4	XL	25
10124	White	Traditional	2/4	2XL	25




Kimtech™ A8 Certified Lab Coat

(Formerly known as Lab Coat – Basic Plus™, Neck Loop for hanging)


10030	Blue	Knit	3/5	S	25
10031	Blue	Knit	3/5	M	25
10032	Blue	Knit	3/5	L	25
10033	Blue	Knit	3/5	XL	25
10034	Blue	Knit	3/5	2XL	25
51905	Blue	Knit	3/5	3/4XL	20
10020	White	Knit	3/5	S	25
10021	White	Knit	3/5	M	25
10022	White	Knit	3/5	L	25
10023	White	Knit	3/5	XL	25
10024	White	Knit	3/5	2XL	25

Kimtech™ A8 Lab Coat + Extra Protection — mid-calf length



Bulk Packed Code	Color	Collar Type	Reinforced Pockets/Snaps	Size	Total/Case
Kimtech™ A8 Certified Lab Coat + Extra Protection (Formerly known as Lab Coat – Universal Precautions, Back Vent, Neck Loop for hanging)					
10045	Blue	Traditional	3/6	S	25
10046	Blue	Traditional	3/6	M	25
10047	Blue	Traditional	3/6	L	25
10048	Blue	Traditional	3/6	XL	25
10049	Blue	Traditional	3/6	2XL	10
10040	White	Traditional	3/6	S	25
10041	White	Traditional	3/6	M	25
10042	White	Traditional	3/6	L	25
10043	White	Traditional	3/6	XL	25
10044	White	Traditional	3/6	2XL	10

Kimtech™ A8 Lab Jacket + Extra Protection — hip length



Bulk Packed Code	Color	Collar Type	Reinforced Pockets/Snaps	Size	Total/Case
Kimtech™ A8 Certified Lab Jacket + Extra Protection (Formerly known as Lab Coat – Universal Precautions, Neck Loop for hanging)					
10069	White	Knit	3/5	S	25
10071	White	Knit	3/5	M	25
10072	White	Knit	3/5	L	25
10073	White	Knit	3/5	XL	25

▶ LAB COAT SELECTION

Select based on collar preference, style preference. All are for light fluid protection. For heavier fluid protection select A7 lab coats.

Non-Sterile Cleanroom Apparel

Formerly Kimberly-Clark™ Brand

Kimtech™ A8 Shoe Covers with Unitrax



▶ PRODUCT FEATURES

- Dry particle and fluid protection
- Extra grip
- Low linting, Category 1, Helmke Drum Test
- Packed for cleanroom



Code	Description	Color	Size	Eaches/ Bags	Total/Case
39370	Shoe Cover w/seamless bottom	White	S/M	100/3	300
39372	Shoe Cover w/seamless bottom	White	L/XL	100/3	300
39371	Shoe Cover w/seamless bottom	White	Universal	100/3	300

Kimtech™ A8 Certified Shoe Covers with Traction Strips



Formerly Kimberly-Clark™ Ankle Guard* and Kimberly-Clark™ X-tra Traction*

▶ PRODUCT FEATURES

- Light splash protection
- Interior has cloth-like feel against the skin



Code	Description	Color	Height	Size	Eaches/ Carton	Eaches/Case
69252	Shoe Cover	Blue	Ankle	Universal	100/3	300
69254	Shoe Cover	Blue	Ankle	XL	80/3	240
69253	Ankle-High Shoe Cover	Blue	Mid-Calf	Universal	90/3	270
69353	Ankle-High Shoe Cover	Blue	Mid-Calf	XL	90/3	270

Adhesive traction strips
to help prevent slips



KleenGuard™ A70 Chemical Spray Protection Smock & Apron

▶ PRODUCT FEATURES

A70 Smock

- Bound seams and neck
- Elastic wrist and shoulder for proper fit
- Back neck snaps

A70 Apron

- Bound seams
- Bound neck and ties
- One size fits all



Code	Description	Color	Size	Total/Case
09829	Smock – Back Opening	Yellow	44"	25
09830	Smock – Back Opening	Yellow	52"	25
97790	Apron	Yellow	29" x 44"	100

KleenGuard™ A80 Chemical Permeation & Jet Liquid Protection Coveralls

▶ PRODUCT FEATURES

- Made of Saranex® 23-P Film laminated to a durable fabric which provides a soft cloth-like feel against the skin
- Taped, sealable storm flap and taped seams
- Seamless front provides more protection in the primary exposure area
- Patented Reflex™ Design is 7-1/2 times less likely to rip out than ANSI minimums — provides 12% more chest room and 6% longer body length
- Level B/C Suits



Zipper front, storm flap, elastic wrists, ankles & respirator-fit hood



Code	Color	Size	Total/Case
45643	White	L	12
45644	White	XL	12
45645	White	2XL	12
45646	White	3XL	10
45647	White	4XL	10

Zipper front, storm flap, elastic wrists, ankles & respirator-fit hood & boots



Code	Color	Size	Total/Case
45663	White	L	12
45664	White	XL	12
45665	White	2XL	12
45666	White	3XL	10
45667	White	4XL	10

Procedure Gowns

▶ PRODUCT FEATURES

Procedure Gowns♦

- Protective 3-layer SMS fabric with light to moderate fluid protection
- Velcro® Brand neck closure
- Tie waist, full back and knit cuff

Isolation Cover Gowns♦

- Protective 3-layer SMS fabric with light to moderate fluid protection
- Tape-tab neck closure
- Tie waist and elastic cuff

Impervious Comfort Gowns♦

- Impervious film laminate
- Fluid protection in front
- Knit cuff with perforated open back



Procedure Gown



Isolation Cover Gown



Impervious Comfort Gowns



Code	Color	Size	Eaches/ Bags	Total/Case
Procedure Gowns♦				
69025	Blue	Universal	10/6	60
69028	Blue	XL	10/6	60
Isolation Cover Gowns♦				
69979	Yellow	L	10/10	100
69988	Yellow	XL	10/10	100
69981	Blue	Universal	10/10	100
Impervious Comfort Gowns♦				
69600	Blue	Universal	10/10	100
69601	Blue	2XL	10/10	100

♦ Packaged by Halyard Health, Inc.

Surgical Gowns

S

▶ PRODUCT FEATURES

Non-Reinforced Sterile Surgical Gowns♦

- Low to moderate fluid protection
- Adjustable neckline — hook & loop
- With towel
- Double bagged

Ultra™ Sterile Surgical Gowns♦

- Provides AAMI Level 3 liquid barrier protection in front area
- Low to moderate fluid protection
- Adjustable neckline — hook & loop
- Knit cuffs
- With towel
- Double bagged



Non-Reinforced Surgical Gown



Ultra™ Sterile Surgical Gown



Code	Color	Size	Neck Binding	Fold	Sleeves	Total/Case
Non-Reinforced Sterile Surgical Gowns♦						
90018	Blue	L	Yellow	Book	Set-in	36
90048	Blue	XL	Yellow	Book	Set-in	32
99284	Blue	L	White	Book	Raglan	20
99285	Blue	XL	White	Book	Raglan	20
90012	Blue	L	Yellow	Drop	Raglan	36
90042	Blue	XL	Yellow	Drop	Raglan	34
Ultra™ Sterile Surgical Gowns♦						
95101	Blue	S	Yellow	Book	Raglan	34
95111	Blue	L	Yellow	Book	Raglan	32
95121	Blue	XL	Yellow	Book	Raglan	30
95131	Blue	2XL	Yellow	Book	Raglan	28

♦ Packaged by Halyard Health, Inc.


Bouffant Caps

▶ PRODUCT FEATURES


KleenGuard™ Bouffant Caps

- Dry particle protection
- Not made with natural rubber latex
- Packed for cleanroom

Code	Color	Size	Eaches/Bags	Total/Case
36850	White	Medium - 21"	100/10	1,000
36860	White	Large - 24"	100/10	1,000



Kimtech™ Kimguard™ Sequential Sterilization Wrap♦



▶ PRODUCT FEATURES

- Available in six grades of wrap fabric – from KC100 to KC600 – to offer precisely the right protection for your sterilization needs. Choosing is easy; the higher the number, the stronger the wrap
- Pre-vacuum steam and EO compatible
- Enhanced microbial barrier
- Low lint

Select the grade that meets your need

KC100	0-3 lbs. suggested wrapped package content weight
KC200	3-6 lbs. suggested wrapped package content weight
KC300	6-9 lbs. suggested wrapped package content weight
KC400	9-13 lbs. suggested wrapped package content weight
KC500	13-17 lbs. suggested wrapped package content weight
KC600	17-25 lbs. suggested wrapped package content weight

KC100

Code	Size	Sheets per case
10709♦	9" x 9"/22 cm x 22 cm	1,000
10712	12" x 12"/30 cm x 30 cm	1,000
10715♦	15" x 15"/38 cm x 38 cm	1,000
10718♦	18" x 18"/45 cm x 45 cm	1,000
10720♦	20" x 20"/50 cm x 50 cm	1,000
10724	24" x 24"/60 cm x 60 cm	500
10730	30" x 30"/76 cm x 76 cm	300
10736	36" x 36"/91 cm x 91 cm	300
10740	40" x 40"/101 cm x 101 cm	250
10745	45" x 45"/114 cm x 114 cm	250
10748	48" x 48"/121 cm x 121 cm	250
10754	54" x 54"/137 cm x 137 cm	100
10772	54" x 72"/137 cm x 182 cm	100

KC200

Code	Size	Sheets per case
68012♦	12" x 12"/30 cm x 30 cm	1,000
68018♦	18" x 18"/45 cm x 45 cm	1,000
68024♦	24" x 24"/60 cm x 60 cm	500
68030	30" x 30"/76 cm x 76 cm	300
68036	36" x 36"/91 cm x 91 cm	300
68040♦	40" x 40"/101 cm x 101 cm	250
68048	48" x 48"/121 cm x 121 cm	100
68054♦	54" x 54"/137 cm x 137 cm	100
68072♦	54" x 72"/137 cm x 182 cm	100

KC300

Code	Size	Sheets per case
10818♦	18" x 18"/45 cm x 45 cm	1,000
10824♦	24" x 24"/60 cm x 60 cm	500
10830♦	30" x 30"/76 cm x 76 cm	300
10836	36" x 36"/91 cm x 91 cm	300
10840♦	40" x 40"/101 cm x 101 cm	250
10845♦	45" x 45"/114 cm x 114 cm	100
10848♦	48" x 48"/121 cm x 121 cm	100

KC400

Code	Size	Sheets per case
68218	18" x 18"/45 cm x 45 cm	600
68224♦	24" x 24"/60 cm x 60 cm	250
68230	30" x 30"/76 cm x 76 cm	200
68236	36" x 36"/91 cm x 91 cm	150
68245♦	45" x 45"/114 cm x 114 cm	100
68248	48" x 48"/121 cm x 121 cm	50
68254♦	54" x 54"/137 cm x 137 cm	50
68272♦	54" x 72"/137 cm x 182 cm	50

KC500

Code	Size	Sheets per case
68118♦	18" x 18"/45 cm x 45 cm	600
68124♦	24" x 24"/60 cm x 60 cm	250
68130	30" x 30"/76 cm x 76 cm	250
68136♦	36" x 36"/91 cm x 91 cm	150
68145♦	45" x 45"/114 cm x 114 cm	100
68148♦	48" x 48"/121 cm x 121 cm	50
68154♦	54" x 54"/137 cm x 137 cm	50
68190♦	54" x 90"/137 cm x 228 cm	50
68160	60" x 60"/152 cm x 152 cm	50

KC600

Code	Size	Sheets per case
68636	36" x 36"/91 cm x 91 cm	144
68640♦	40" x 40"/101 cm x 101 cm	96
68645♦	45" x 45"/114 cm x 114 cm	96
68648♦	48" x 48"/121 cm x 121 cm	48
68654♦	54" x 54"/137 cm x 137 cm	48
68672♦	54" x 72"/137 cm x 182 cm	48

♦ Packaged by Halyard Health, Inc.



KIMTECH™

Gloves

Kimtech™ Brand gloves protect your process and your employees from known and unknown risks while delivering comfort, dexterity, quality and the assurance to do your best work. They work hand in hand with other head-to-toe solutions from Kimberly-Clark Professional — the global leader in lab and cleanroom PPE and wiping products.

Which Glove is Right for You?

Choose from a wide variety of cleanroom and laboratory glove offerings including a true original: our Purple Nitrile™ Exam Glove, *the glove of choice in labs and the most recognizable glove in the market.*

Cleanroom & Exam Glove Selection Guide

Category	Suggested Use	Performance			
		Best	Better	Good	
Sterile Gloves					↑ Protection Level
G3 White Nitrile	Parenteral Drug Manufacturing; Ophthalmic Manufacturing; Biotech; Aseptic processing	●			
G3 Latex†	Parenteral Drug Manufacturing; Ophthalmic Manufacturing; Biotech; Aseptic processing	●			
G3 Sterling™ Nitrile	Parenteral Drug Manufacturing; Ophthalmic Manufacturing; Biotech; Aseptic processing		●		
G5 Latex†	Parenteral Drug Manufacturing; Ophthalmic Manufacturing; Biotech; Aseptic processing			●	
Non-Sterile Gloves					↑ Protection Level
G3 White Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Electronics	●			
G3 NXT™ Nitrile	Pharmaceutical; Biotech; Semiconductor; Applications where double donning is necessary	●			
G3 Blue Nitrile	Pharmaceutical; Biotech; Semiconductor; Applications where double donning is necessary	●			
G3 Latex†	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage	●			
G3 EvT Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage		●		
G3 Sterling™ Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage		●		
G5 White Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage		●		
G5 Blue Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage		●		
G5 Sterling™ Nitrile	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage		●		
G5 Latex†	Pharmaceutical; Biotech; Semiconductor; Medical device; Disk Drive; Data Storage			●	
G5 Vinyl Co-Polymer	Semiconductor; Medical device; Disk Drive; Data Storage; Electronics			●	
Exam Gloves					↑ Protection Level
Purple Nitrile™	Higher-risk applications within life sciences: pharmaceutical & biomedical research, forensic science, non-sterile drug manufacturing, hazardous drug compounding, chemotherapy, EMS, petrochemical, chemical processing, electronics, BSL 1 & 2 lab research	●			
Blue Nitrile	Protection against moderate to high exposure to fluids or chemicals: pharmaceutical & biomedical research, chemical processing, petrochemical, BSL 1 & 2 lab research, medical device, forensic science research, food processing, electronics, janitorial	●			
Spring Green Nitrile	For general laboratory use in life sciences, university labs, medical device, forensic science, chemical processing, petrochemical, food processing, janitorial		●		
Forest Green Nitrile	For general laboratory use in life sciences, university labs, medical device, forensic science, chemical processing, petrochemical, food processing, janitorial		●		
Sterling™ Nitrile	For general laboratory use in life sciences, university labs, medical device, forensic science, chemical processing, petrochemical, food processing, janitorial		●		
PFE-Xtra & PFE Latex†	For general laboratory use in life sciences, university labs, medical device, forensic science, janitorial		●		
Lavender™ Nitrile	For use in lower-risk laboratory applications: pharmaceutical, biomedical, medical device research, petrochemical, electronics, janitorial			●	
Comfort Latex†	For use in lower-risk laboratory applications: pharmaceutical, biomedical, medical device research, petrochemical, electronics, janitorial			●	

† CAUTION: This product contains natural rubber latex which may cause allergic reactions.

Advantages of Kimtech™ Gloves


Acceptable Quality Level (AQL)

- Refers to the probability of having defective gloves within a lot
- The lower the AQL number, the lower the probability of defective gloves
- Kimtech™ Gloves exceed ASTM standards for freedom from pinholes and critical defects (*ASTM = AQL 2.5; Kimtech™ Gloves = AQL 1.5 or better*).
- A low AQL for pinholes is important — the lower the number of pinholes, the greater the level of barrier protection



The Importance of Trend & Technical Data^{†††}

- Demonstrate consistent product quality over time
- Trend data indicating particle counts and extractable levels are available for all Kimtech™ G3 Latex[†] and Nitrile Gloves



■ Monthly Particle Average (Particles larger than 0.5 microns)

■ Upper Limit Specification

Example based on historical Critical Nitrile Data

^{†††} Tested according to the procedure as described in IEST-RP-CC005.3: Gloves and Finger Cots Used in Cleanrooms and Other Controlled Environments

[†] **CAUTION:** This product contains natural rubber latex which may cause allergic reactions.

Symbols Key



RightCycle by Kimberly-Clark Professional™



Double Bagged with Case Liner



Acceptable Quality Level



Recommended for ISO Class 3 or higher cleanroom



Sterile



Recommended for ISO Class 5 or higher cleanroom



Sterile Cleanroom Gloves

Formerly Kimtech Pure™ Brand


Kimtech™ G3 Sterile White Nitrile Gloves

Highest personal and process protection in the sterile range



PRODUCT FEATURES

- Gamma sterilized (10⁻⁴)
- Packaged for aseptic donning (walleted and pouched in polyethylene)
- Suitable for double donning
- Low endotoxins: typical <5, max ≤20 EU/glove
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets USP <800> guidelines
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Particles: typical 700, max ≤950 at >0.5 um/cm²
- Not made with natural rubber latex
- Textured fingertips with beaded cuff for easy donning
- Hand-specific pairs
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	6.0	6.5	7.0	7.5	8.0	8.5	9.0	10.0	Gloves/Bag	Total/Case
Kimtech™ G3 Sterile White Nitrile Gloves, 12" Hand-Specific Pairs	White	56888	56889	56890	56891	56892	56893	56894	56887	20/10	200 pairs


Kimtech™ G3 Sterile Sterling™ Nitrile Gloves

Innovation combines protection, comfort and tactile sensitivity



PRODUCT FEATURES

- Gamma sterilized (10⁻⁴)
- Packaged for aseptic donning (walleted and pouched in polyethylene)
- Suitable for double donning
- Low endotoxins: typical <5, max ≤20 EU/glove
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets USP <800> guidelines
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Particles: typical 750, max ≤1,200 at >0.5 um/cm²
- Not made with natural rubber latex
- Textured fingertips with beaded cuff for easy donning
- Hand-specific pairs
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	6.0	6.5	7.0	7.5	8.0	8.5	9.0	10.0	Gloves/Bag	Total/Case
Kimtech™ G3 Sterile Sterling™ Nitrile Gloves, 12" Hand-Specific Pairs	Sterling	11821	11822	11823	11824	11825	11826	11827	11828	30/10	300 pairs

Kimtech™ G3 Sterile Latex† Gloves

High-quality latex† gloves with good comfort and dexterity




▶ PRODUCT FEATURES

- Gamma sterilized (10^{-6})
- Packaged for aseptic donning (walleted and pouched in polyethylene)
- Suitable for double donning
- Low endotoxins: typical <5 , max ≤ 20 EU/glove
- Particles: typical 800, max $\leq 1,500$ at >0.5 $\mu\text{m}/\text{cm}^2$
- Natural rubber latex† with low residual protein content
- Fully textured with beaded cuff for easy donning
- Hand-specific pairs

8.6 mil thickness

Available in 12" length



Packaged in a Class 100 Cleanroom

Description	Color	6.0	6.5	7.0	7.5	8.0	8.5	9.0	10.0	Total/Case
Kimtech™ G3 Sterile Latex† Gloves, 12" Hand-Specific Pairs	Natural	56843	56844	56845	56846	56847	56848	56849	56842	200 pairs

Kimtech™ G5 Sterile Latex† Gloves

Quality sterile latex† gloves at a value price

▶ PRODUCT FEATURES

- Gamma sterilized (10^{-6})
- Packaged for aseptic donning (walleted and pouched in polyethylene)
- Suitable for double donning
- Particles: max $\leq 2,000$ at >0.5 $\mu\text{m}/\text{cm}^2$
- Natural rubber latex† with low residual protein content
- Fully textured with beaded cuff for easy donning
- Hand-specific pairs


DID YOU KNOW?

Though you can't see it happening, every minute of the day we lose about 30,000 to 40,000 dead skin cells off the surface of our skin.



8.6 mil thickness

Available in 12" length



Packaged in a Class 100 Cleanroom

Description	Color	6.0	6.5	7.0	7.5	8.0	8.5	9.0	10.0	Total/Case
Kimtech™ G5 Sterile Latex† Gloves, 12" Hand-Specific Pairs	Natural	56851	56852	56853	56854	56855	56856	56857	56850	200 pairs

† CAUTION: This product contains natural rubber latex which may cause allergic reactions.

Non-Sterile Cleanroom Gloves

Formerly Kimtech Pure™ Brand


Kimtech™ G3 White Nitrile Gloves

Highest personal and process protection in the critical (G3) glove range



PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Strong, consistent grip
- Beaded cuff for easy donning
- Particles: typical 600, max ≤ 950 at $>0.5 \mu\text{m}/\text{cm}^2$
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets USP <800> guidelines
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G3 White Nitrile Gloves, 12" Ambi	White	56880	56881	56882	56883	56884	56886	100/10	1,000


Kimtech™ G3 NXT™ Nitrile Gloves

Provides great personal and process protection with ability to double don



PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Particles: typical 650, max ≤ 950 at $>0.5 \mu\text{m}/\text{cm}^2$
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets USP <800> guidelines
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G3 NXT™ Nitrile Gloves, 12" Ambi	White	62990	62991	62992	62993	62995	62994	100/10	1,000


Kimtech™ G3 EvT Nitrile Gloves

Quality gloves ideal for semiconductor and touch panel applications



▶ PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Strong, consistent grip
- Beaded cuff for easy donning
- Particles: typical 600, max ≤ 950 at $>0.5 \mu\text{m}/\text{cm}^2$
- Meets U.S. FDA regulations for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	XL	2XL	Gloves/Bag	Bags/Case	Total/Case
Kimtech™ G3 EvT Nitrile Gloves, 12" Ambi	White	38700	38701	38702	38703	38704	38705	250	6 (XS-L) 5 (XL-2XL)	1,500 1,250


Kimtech™ G3 Sterling™ Nitrile Gloves

Nitrile protection with sensitivity of latex, cleaned to meet the needs of the critical cleanroom environment



▶ PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Strong, consistent grip
- Beaded cuff for easy donning
- Comfortable fit, excellent dexterity, and tactile sensitivity
- Particles: typical 800, max $\leq 1,200$ at $>0.5 \mu\text{m}/\text{cm}^2$
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G3 Sterling™ Nitrile Gloves, 12" Ambi	Sterling	99234	99235	99236	99237	99238	99239	250/6	1,500

Non-Sterile Cleanroom Gloves

Formerly Kimtech Pure™ Brand


Kimtech™ G3 Blue Nitrile Gloves

Color differentiation for your critical cleanroom needs



PRODUCT FEATURES

- Ambidextrous with smooth fingertips
- Beaded cuff for easy donning
- Bisque finish
- Suitable for double donning
- Particles: typical 600, max ≤ 800 at $>0.5 \mu\text{m}/\text{cm}^2$
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G3 Blue Nitrile Gloves, 12" Ambi	Blue	56875	56876	56877	56878	—	56879	100/10	1,000


Kimtech™ G3 Latex† Gloves

Provides comfort, dexterity and maximum flexibility



PRODUCT FEATURES

- Natural rubber latex† with low residual protein content
- Textured palms and fingertips
- Beaded cuff for easy donning
- Particles: typical 700, max $\leq 1,500$ at $>0.5 \mu\text{m}/\text{cm}^2$



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case		
Kimtech™ G3 Latex† Gloves, 12" Ambi	Natural	—	56813	56814	56815	—	56816	100/10	1,000		
		6.0	6.5	7.0	7.5	8.0	8.5			9.0	10.0
Kimtech™ G3 Latex† Gloves, 12" Hand-Specific Pairs	Natural	56835	56836	56837	56838	56839	56840	56841	56834	50/4	200 pairs
Kimtech™ G3 Latex† Gloves, 12" Hand-Specific Multi-Pack	Natural	56827	56828	56829	56830	56831	56832	56833	56825	50/4	200 pairs

† CAUTION: This product contains natural rubber latex which may cause allergic reactions.


Kimtech™ G5 White Nitrile Gloves



Highest personal and process protection in the critical (G5) glove range

▶ PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Strong, consistent grip
- Beaded cuff for easy donning
- Particles: ≤ 950 at $>0.5 \text{ um/cm}^2$
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G5 White Nitrile Gloves, 10" Ambi	White	56863	56864	56865	56866	56867	56868	100/10	1,000


Kimtech™ G5 Blue Nitrile Gloves



Color differentiation for your controlled cleanroom needs

▶ PRODUCT FEATURES

- Ambidextrous with smooth fingertips
- Beaded cuff for easy donning
- Bisque finish
- Suitable for double donning
- Particles: $\leq 1,700$ at $>0.5 \text{ um/cm}^2$
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G5 Blue Nitrile Gloves, 10" Ambi	Blue	56858	56859	56860	56861	—	56862	100/10	1,000

Non-Sterile Cleanroom Gloves

Formerly Kimtech Pure™ Brand


Kimtech™ G5 Sterling™ Nitrile Gloves

Nitrile protection with sensitivity of latex, cleaned to meet the needs of the critical cleanroom environment



▶ PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Strong, consistent grip
- Beaded cuff for easy donning
- Comfortable fit, excellent dexterity, and tactile sensitivity
- Particles: $\leq 2,000$ at $>0.5 \mu\text{m}/\text{cm}^2$
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	XS	S	M	L	L+	XL	Gloves/Bag	Total/Case
Kimtech™ G5 Sterling™ Nitrile Gloves, 12" Ambi	Sterling	98184	98185	98186	98187	98188	98189	250/6	1,500




Kimtech™ G5 Latex† Gloves



Provides comfort, dexterity and maximum flexibility

▶ PRODUCT FEATURES

- Natural rubber latex† with low residual protein content
- Textured palms and fingertips
- Beaded cuff for easy donning
- Particles: $\leq 3,000$ at $>0.5 \mu\text{m}/\text{cm}^2$



Packaged in a Class 100 Cleanroom

Description	Color	S	M	L	XL	Gloves/Bag	Total/Case
Kimtech™ G5 Latex† Gloves, 12" Ambi	Natural	56809	56810	56811	56812	100/10	1,000
Kimtech™ G5 Latex† Gloves, 10" Ambi	Natural	56805	56806	56807	56808	100/10	1,000

† CAUTION: This product contains natural rubber latex which may cause allergic reactions.


Kimtech™ G5 Vinyl Co-Polymer Gloves



Value-priced gloves for static-sensitive environments

▶ PRODUCT FEATURES

- Ambidextrous with smooth fingertips
- Beaded cuff for easy donning
- Static dissipative in use



Packaged in a Class 100 Cleanroom

Description	Color	S	M	L	XL	Gloves/Bag	Total/Case
Kimtech™ G5 Vinyl Co-Polymer Gloves, 12" Ambi	Clear	61001	61002	61003	61004	100/10	1,000


Purple Nitrile™ Exam Gloves — The Original Purple Nitrile™ Exam Glove



Maximum protection for higher-risk procedures

PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- FDA cleared for use with chemotherapy drugs (*non-sterile only*)
- Tested for use with 29 chemotherapy drugs and 4 hormones, per ASTM D6978-05 (*non-sterile only*)
- Meets USP <800> guidelines
- Purple Nitrile-Xtra™ 12" Gloves meet NFPA standard 1999:2013 for protecting EMS workers against liquid-borne pathogens
- Not made with natural rubber latex
- Static dissipative in use



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
Purple Nitrile-Xtra™ Exam Gloves, 12" Ambi	Purple	55090	50601	50602	50603	50604	50/10	500
Purple Nitrile™ Exam Gloves, 9.5" Ambi	Purple	55080	55081	55082	55083	55084	100/10 XL = 90/10	1,000 XL = 900
Sterile Purple Nitrile™ Exam Gloves, 9.5" Pairs	Purple	—	55091	55092	55093	—	50 pairs/4	200 pairs
Sterile Purple Nitrile™ Exam Gloves, 9.5" Singles	Purple	—	52101	52102	52103	—	100 singles/4	200 pairs


Blue Nitrile Exam Gloves



Protection against moderate to high exposure to fluids or chemicals along with excellent tactile sensitivity

PRODUCT FEATURES

- Ambidextrous
- Beaded cuff for easy donning
- Powder-free
- Smooth Blue Exam Gloves meet U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
Smooth Blue Nitrile Exam Gloves, 9.5" Ambi	Blue	50574	50576	50578	50580	50582	100/10 XL = 90/10	1,000 XL = 900
Textured Blue Nitrile Exam Gloves, 9.5" Ambi	Blue	53100	53101	53102	53103	53104	100/10 XL = 90/10	1,000 XL = 900

Spring Green Nitrile Exam Gloves



Recyclable gloves with ideal thickness for today's laboratory needs

PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- Strong wet and dry grip to reduce potential for slips
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
Spring Green Nitrile Exam Gloves	Spring Green	43437	43438	43439	43440	43441	200/10 XL = 180/10	2,000 XL = 1,800


Forest Green Nitrile Exam Gloves



Provides dexterity, protection and a way to reduce your solid waste stream

PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- Meets Canadian requirements for food-handling applications
- Not made with natural rubber latex
- Static dissipative in use
- Six sizes for optimal fit



Description	Color	XS	S	M	L	XL	2XL	Gloves/Box	Total/Case
Forest Green Nitrile Exam Gloves	Forest Green	43443	43444	43445	43446	43447	43448	200/10 2XL = 180/10	2,000 2XL = 1,800

Sterling™ Nitrile Exam Gloves



Provides the protection of nitrile with the sensitivity of latex for everyday use

PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- FDA cleared for use with chemotherapy drugs (*non-sterile only*)
- Tested for use with 12 chemotherapy drugs and 4 hormones, per ASTM D6978-05 (*non-sterile only*)
- Meets USP <800> guidelines
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Sterling Nitrile-Xtra™ 12" Gloves meet NFPA standard 1999:2013 for protecting EMS workers against liquid-borne pathogens
- Not made with natural rubber latex
- Static dissipative in use



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
Sterling Nitrile-Xtra™ Exam Gloves, 12" Ambi	Sterling	53137	53138	53139	53140	53141	100/10	1,000
Sterling™ Nitrile Exam Gloves, 9.5" Ambi	Sterling	50705	50706	50707	50708	50709	200/10 XL = 170/10	2,000 XL = 1,700
Sterile Sterling™ Nitrile Exam Gloves, 9.5" Ambi (Pairs)	Sterling	—	53130	53131	53132	—	50/4	200 pairs


Lavender™ Nitrile Exam Gloves



Protective, comfortable and more economical than standard nitrile gloves

PRODUCT FEATURES

- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- Comfortable fit, excellent dexterity, and tactile sensitivity
- Not made with natural rubber latex
- Static dissipative in use



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
Lavender™ Nitrile Exam Gloves, 9.5" Ambi	Lavender	52816	52817	52818	52819	52820	250/10 XL = 230/10	2,500 XL = 2,300


PFE-Xtra & PFE Latex[†] Exam Gloves



Provides comfort, dexterity and maximum flexibility

▶ PRODUCT FEATURES

- Natural rubber latex[†] with low residual protein content
- Ambidextrous, fully textured gloves
- Beaded cuff for easy donning
- Powder-free



Description	Color	XS	S	M	L	XL	Gloves/Box	Total/Case
PFE-Xtra Latex[†] Exam Gloves, 12" Ambi	Natural	—	50501	50502	50503	50504	50/10	500
PFE Latex[†] Exam Gloves, 9.5" Ambi	Natural	57110	57220	57330	57440	57550	100/10 XL = 90/10	1,000 XL = 900


Comfort Latex[†] Exam Gloves



Provides comfort, dexterity and maximum flexibility

▶ PRODUCT FEATURES

- Natural rubber latex[†] with low residual protein content
- Ambidextrous with textured fingertips
- Beaded cuff for easy donning
- Powder-free
- Six sizes for optimal fit



Description	Color	XS	S	M	L	XL	2XL	Gloves/Box	Total/Case
Comfort Latex[†] Exam Gloves, 9.5" Ambi	Natural	43431	43432	43433	43434	43435	43436	100/10 2XL = 90/10	1,000 2XL = 900

[†] **CAUTION:** This product contains natural rubber latex which may cause allergic reactions.

KleenGuard™ Thin Mil Gloves



▶ G10 Arctic Blue Nitrile Gloves

- Advanced formulation with enhanced tactile sensitivity
- Touchscreen compatible
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications
- Textured fingertips; powder-free
- Not made with natural rubber latex




Description	Color	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	Gloves/Box	Total/Case
G10 Arctic Blue Nitrile Gloves	Arctic Blue	90095	90096	90097	90098	90099	200 (XL = 180)	2,000 (XL = 1,800)

Jackson Safety® Gloves

▶ G29 Chemical Gloves

- Neoprene blend; silicone-free
- Highest level of dexterity per EN420:2003 standard
- Touchscreen compatible
- Ambidextrous, textured fingertips; powder-free
- Not made with natural rubber latex



▶ G80 Nitrile Chemical-Resistant Gloves

- Cotton flock lined for added comfort
- Textured fingertips enhance grip
- Meets EN374-3: 2003 standard
- Meets U.S. FDA regulations and Canadian requirements for food-handling applications




▶ G35 Inspection Gloves

- 100% white nylon
- Low-linting
- Seamless knit shell
- Ambidextrous
- Not made with silicone
- Colored yarn on cuff



▶ G80 Neoprene/Latex† Chemical-Resistant Gloves

- Palm strengthened for extra protection
- Cotton flock lining
- Anti-slip pattern on fingers for good wet or dry grip
- Meets EN 374-AKL standard
- Touchscreen compatible



Description	Color	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (2XL)	Gloves/Box	Total/Case
G29 Chemical Gloves, 12" Ambi	Blue	49822	49823	49824	49825	49826	49827	50/10	500
G35 Inspection Gloves, 9" Ambi	White Nylon	38716	38717	38718	38719	38720		12 pairs/10	120 pairs
G80 Nitrile Chemical-Resistant Gloves, 13"	Green	—	94445	94446	94447	94448	94449	12 pairs/5	60 pairs
G80 Neoprene/Latex† Chemical-Resistant Gloves, 12"	Blue & Yellow	—	38741	38742	38743	38744	—	12 pairs/5	60 pairs

† CAUTION: This product contains natural rubber latex which may cause allergic reactions.



KIMTECH™

Masks

Our solutions help keep contaminants from getting in or out, providing seamless protection for your people and process and the assurance to do your best work. As a global leader in PPE and wiping solutions for labs and cleanrooms, we offer an array of options that work together to meet your mask, respirator and other PPE needs.






TOP CONTAMINATION SOURCES:

Skin flakes, oils, perspiration and hair can all contribute to cleanroom contamination.⁶

Which Product is Best for You?

These charts will help you determine the best cleanroom and lab masks for use in your environment.

Kimtech™ Cleanroom Masks

Category	Suggested Use	Performance		
		Best	Better	Good
M3 - Sterile 	Pharmaceutical/Biotech	●		
M3 - Clean 	Semiconductor/Disk Drive/ Data Storage/Integrated Circuits	●		
M5 - Clean 	Biotech/Medical Device/Electronics/ Telecommunications		●	
M6 - Clean 	Semiconductor/Disk Drive/ Data Storage/Integrated Circuits		●	
M7 - Clean 	Semiconductor/Disk Drive/ Data Storage/Integrated Circuits			●

Kimberly-Clark™ Lab Masks

Protection Level ↑

Category	Suggested Use	Performance		
		Resistance to penetration by synthetic blood, mmHg pressure	BFE %	PFE %
N95 Respirator with Level 3 Mask	High-risk small airborne contaminants/ respiratory infection control ⁷	160	≥99%	≥99%
Level 3 Masks	Heavy to moderate blood or fluid exposure	160	≥99%	≥99%
Level 2 Masks	Moderate to light blood or fluid exposure	120	≥98%	≥98%
Basic Protection Masks	Short non-fluid exposures	—	≥95% - ≥98%	≥95% - ≥98%

Symbols Key



Sterile



Recommended for ISO Class 3 or higher cleanroom



Recommended for ISO Class 6 or higher cleanroom



Double Bagged with Case Liner



Recommended for ISO Class 5 or higher cleanroom



Recommended for ISO Class 7 or higher cleanroom

⁶ "The Contamination Risks Posed by Laundered Cleanroom Apparel," Kimberly-Clark Professional white paper, 2014

⁷ OSHA, <https://www.osha.gov/Publications/respirators-vs-surgicalmasks-factsheet.html>



3 Steps in Selecting a Face Mask

- 1 Identify the work environment
- 2 Select the style
- 3 Determine the attachment

Simple Donning Steps

- 1 Select your mask
- 2 Pleats point down
- 3 Shiny side out
- 4 Adjust the head attachment
- 5 Pinch the nose wire around the bridge of the nose
- 6 Proceed to your work

Sterile Cleanroom Masks

Formerly Kimtech Pure™ Brand

Kimtech™ M3 Sterile Face Masks



▶ PRODUCT FEATURES

- Fractured polyethylene film outer layer
- BICOSOF fabric inner facing provides comfort and protects filter media



Code	Description	Color	Style	Units/Bag ⁹	Bags/Case	Total/Case
62467	Kimtech™ M3 Certified Sterile Pleat-Style Face Mask	White	7" Soft ties	20	10	200
62470	Kimtech™ M3 Certified Sterile Pleat-Style Face Mask	White	7" Knitted earloops	20	10	200
62494	Kimtech™ M3 Certified Sterile Pleat-Style Face Mask	White	9" Soft ties	20	10	200
62483	Kimtech™ M3 Certified Sterile Pouch-Style Face Mask	White	Individually packaged with two knitted headbands	20	10	200

⁹ Individually packaged



⁹ <http://www.lung.org/about-us/blog/2016/05/sneeze-versus-cough.html>

Kimtech™ M3 Cleanroom Face Masks

ISO
3

DB

▶ PRODUCT FEATURES

- Low-linting polyethylene film outer layer
- BICOSOF fabric inner facing provides comfort



Code	Description	Color	Style	Units/Bag	Bags/Case	Total/Case
62465	Kimtech™ M3 Pleat-Style Face Mask	White	7" Knitted earloops	50	10	500
62466	Kimtech™ M3 Pleat-Style Face Mask	White	7" Soft ties	50	10	500
62484	Kimtech™ M3 Certified Pouch-Style Face Mask	White	Two knitted headbands	50	6	300

Kimtech™ M5 Cleanroom Face Masks

ISO
5

DB

▶ PRODUCT FEATURES

- Three-layer design
- Polyester/cellulose inner/outer facing



Code	Description	Color	Style	Units/Bag	Bags/Case	Total/Case
62692	Kimtech™ M5 Pleat-Style Face Mask	Blue	Earloops	50	10	500
62742	Kimtech™ M5 Pleat-Style Face Mask	Blue	Soft ties	50	6	300

Kimtech™ M6 Cleanroom Face Masks

ISO 6 DB

PRODUCT FEATURES

- BICOSOF fabric inner facing provides comfort
- Two-layer design



Code	Description	Color	Style	Units/Bag	Bags/Case	Total/Case
62477	Kimtech™ M6 Pleat-Style Face Mask	White	Knitted earloops	50	10	500

Kimtech™ M7 Veils

ISO 7 DB

PRODUCT FEATURES

- Provides exceptional breathability
- Constructed of low-linting apertured polyethylene film
- Available with knitted headband or snaps for easy face adjustment
- 13" wide & 15" long



Code	Description	Color	Style	Units/Bag	Bags/Case	Total/Case
62751	Kimtech™ M7 Veil	White	Snaps	50	3	150
62757	Kimtech™ M7 Veil	White	Knitted headbands	50	3	150

Kimberly-Clark™ N95 Respirator and Surgical Masks

▶ PRODUCT FEATURES

- Polyurethane headband
- Two levels of fluid protection per ASTM F2100-11 — moderate (level 2) or heavy (level 3)
- Flat fold pouch-style with large breathing chamber
- Available with safety seal



Code	Description	ASTM Level	Color	Size	Safety Seal	Each/Case	Total/Case
62355	N95 Respirator & Surgical Mask for Fluid Protection	2 (moderate fluid protection)	White	Small	No	50/6	300
62126	N95 Respirator & Surgical Mask for Fluid Protection	2 (moderate fluid protection)	White	Regular	No	50/6	300
46827	Fluidshield™ N95 Respirator & Surgical Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Small	No	35/6	210
46727	Fluidshield™ N95 Respirator & Surgical Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Regular	No	35/6	210
46867	Fluidshield™ N95 Respirator & Surgical Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Small	Yes	35/6	210
46767	Fluidshield™ N95 Respirator & Surgical Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Regular	Yes	35/6	210

Kimberly-Clark™ Procedure and Surgical Masks

▶ PRODUCT FEATURES

- ASTM F2100-11 levels of protection
- Procedure (earloop) or surgical masks (ties)

Procedure Masks

Code	Description	ASTM Level	Color	Style	Type	Each/Case	Total/Case
47090	Procedure Mask	None	White	Pleated	Earloop	50/10	500
47080	Procedure Mask	None	Blue	Pleated	Earloop	50/10	500
47117	Procedure Mask	None	Yellow	Pleated	Earloop	50/10	500
62356♦	The Lite One™ Procedure Mask	None	Blue	Pleated	Earloop	50/10	500
62115♦	Fluidshield™ Procedure Mask	2 (moderate fluid protection)	Blue	Pleated	Earloop	50/10	500
47107	Fluidshield™ Procedure Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Pleated	Earloop	40/10	400
32856♦	Child's Size Disney® Mask			Pleated	Earloop	75/10	750/pkg

♦ Packaged by Halyard Health, Inc.

Lab Masks

Surgical Masks

Code	Description	ASTM Level	Color	Style	Type	Each/Carton	Total/Case
48201◆	Surgical Mask	None	Blue	Pleated	Ties	50/6	300
47500	Soft Touch II™ Surgical Mask	None	Blue	Pleated	Horizontal Ties	50/6	300
48100	The Lite One™ Surgical Mask	None	Blue	Pleated	Ties	50/6	300
37525◆	Duckbill Surgical Mask	None	Green	Pouch	Ties	50/6	300
48207	Fluidshield™ Surgical Mask for Heavy Fluid Protection	3 (heavy fluid protection)	Orange	Pleated	Ties	50/6	300

Cone Masks

Code	Description	ASTM Level	Color	Style	Type	Each/Carton	Total/Case
00152◆	Standard Cone Mask	None	Blue	Cone	Headband	50/6	300

◆ Packaged by Halyard Health, Inc.

Kimberly-Clark™ Fluidshield™ Masks with Visors

PRODUCT FEATURES

- ASTM F2100-11 level 3 for heavy fluid protection
- Pleat-style procedure (earloop) or surgical masks (ties)
- Fog resistant
- Foam band



Code	Description	Visor	Color	Style	Type	Each/Carton	Total/Case
47137	Mask with Visor	Regular	Orange	Procedure	Earloop	25/4	100
47147	Mask with Wraparound Visor	Wraparound	Orange	Procedure	Earloop	25/4	100
48237	Mask with Visor	Regular	Orange	Surgical	Ties	25/4	100
48247	Mask with Wraparound Visor	Wraparound	Orange	Surgical	Ties	25/4	100

Kimberly-Clark™ Face Shields

PRODUCT FEATURES

- Equipped with a foam band and headband
- Can be worn with or without glasses or goggles
- Fog resistant



Code	Description	Color	Each/Carton	Total/Case
41204	Face Shield with Full Length Visor	Clear	40/1	40
41205	Face Shield with 3/4 Length Visor	Clear	40/1	40



Wipers

When it comes to precision cleaning in a scientific environment, you need wiping products you can trust. The Kimtech™ Brand's innovative wiping solutions provide the assurance you need to do your best work while protecting critical environments and processes.



The Industry Standard

Over 60 years ago, Kimberly-Clark Professional created Kimwipes® Wipers, the first delicate-task wiper for lab environments. It remains No. 1 today. From the industry standard for labs and research facilities to sterile pre-saturated cleanroom wipers, the Kimtech™ Brand continues to deliver high-performance wiping solutions. These, combined with our head-to-toe PPE, deliver seamless protection when and where it counts.

Symbols Key



Sterile



Recommended for ISO Class 4 or higher cleanroom



Recommended for ISO Class 5 or higher cleanroom



Double Bagged with Case Liner



Product complies with the Trade Agreements Act



Meets EPA guidelines for minimum post-consumer waste content; towels 40%

Kimtech Pure™ W4 Wipers



PRODUCT FEATURES

- 100% polypropylene
- Thermally bonded; no glues or binders
- Acid-, base- and solvent-resistant
- Straight, clean, knife-cut edges minimize lint



- 100% polypropylene with 70% isopropyl alcohol / 30% deionized water
- Ideal one-step application of alcohol to critical surfaces



Code	Description	Cleanroom Class FS209		Delivery System	Color	Material	Size (W x L)	Bags/Case	Units/Bag	Total/Case
33390	Kimtech Pure™ W4 Critical Task Wipers	10		Flat/Anti-stat Dbl Bag	White	Polypropylene	9" x 9"	5	100	500
33330	Kimtech Pure™ W4 Critical Task Wipers	10		Flat/Anti-stat Dbl Bag	White	Polypropylene	12" x 12"	5	100	500
06070	Kimtech Pure™ W4 Pre-Saturated Alcohol Wipers, 70% IPA	10		Resealable Pouch/Anti-stat Liner Bag	White	Polypropylene	11" x 9"	10	40	400

Kimtech Pure™ W4 Sterile Pre-Saturated Wipers

▶ PRODUCT FEATURES

- 100% polypropylene with 70% isopropyl alcohol / 30% deionized water
- Thermally bonded; no glues or binders
- Acid-, base- and solvent-resistant
- Straight, clean, knife-cut edges minimize lint
- Ideal one-step application of alcohol to critical surfaces



Code	Description	Cleanroom Class FS209	Delivery System	Color	Material	Size (W x L)	Bags/Case	Units/Bag	Total/Case
76490	Kimtech Pure™ W4 PreSat Sterile Wipers	10	Resealable Pouch/ Anti-stat Liner Bag	White	Polypropylene	11" x 9"	10	40	400


Kimtech Pure™ W5 Wipers

▶ PRODUCT FEATURES

- 50% rayon / 50% polyester spunlace blend
- Clothlike feel
- No binders or surfactants, resulting in low extractables

Excellent absorption efficiency and capacity

High liquid absorbency rate



Code	Description	Delivery System	Color	Material	Size (W x L)	Bags/Case	Units/Bag	Total/Case
06179	Kimtech Pure™ W5 Critical Task Wipers	Flat/Anti-stat Dbl Bag	White	Spunlace	9" x 9"	5	100	500

Kimtech Science™ Kimwipes® Wipers

The industry standard for labs and research

Introduced over 60 years ago, Kimtech Science™ Kimwipes® Wipers were the first delicate-task wiper for laboratories and since then have been the market leader for wiping surfaces, parts, instruments and cleaning lenses.

Other products have tried to imitate, but have never matched the original. Don't put your delicate processes at risk!

PRODUCT FEATURES

- Also available in 2-ply and 3-ply for increased absorbency
- Gentle texture
- Low lint and low extractables



Code	Description	Delivery System	Color	Material	Size (W x L)	Boxes/Case	Units/Box	Total/Case
34120	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	1-ply tissue	4.4" x 8.4"	30	280	8,400
34155	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	1-ply tissue	4.4" x 8.4"	60	280	16,800
34133	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	1-ply tissue	11.8" x 11.8"	15	196	2,940
34256	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	1-ply tissue	14.7" x 16.6"	15	140	2,100
34705	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	2-ply tissue	11.8" x 11.8"	15	119	1,785
34721	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	2-ply tissue	14.7" x 16.6"	15	90	1,350
34743	Kimtech Science™ Kimwipes® Delicate Task Wipers	Pop-Up™ Box	White	3-ply tissue	11.8" x 11.8"	15	119	1,785

Kimtech Science™ Precision Wipers

PRODUCT FEATURES

- A value-conscious alternative that offers reliable wiping performance for delicate tasks
- Available in 1-ply or 2-ply
- Low lint and low extractables



Code	Description	Delivery System	Color	Material	Size (W x L)	Boxes/Case	Units/Box	Total/Case
05511	Kimtech Science™ Precision Wipers	Pop-Up™ Box	White	1-ply tissue	4.4" x 8.4"	60	280	16,800
75512	Kimtech Science™ Precision Wipers	Pop-Up™ Box	White	1-ply tissue	11.8" x 11.8"	15	196	2,940
05514	Kimtech Science™ Precision Wipers	Pop-Up™ Box	White	1-ply tissue	14.7" x 16.6"	15	140	2,100
05517	Kimtech Science™ Precision Wipers	Pop-Up™ Box	White	2-ply tissue	14.7" x 16.6"	15	90	1,350

Kimtech Science™ Lens Cleaning Station

▶ PRODUCT FEATURES



- Ideal compact unit for your eye safety program
- Use anywhere safety goggles are worn
- Anti-static, anti-fog; silicone-free cleaning solution removes dirt quickly and easily
- Wipers won't scratch delicate surfaces when used wet

TYPICAL USES

- Labs
- Manufacturing facilities
- Welding operations
- Refineries
- Food processing
- Printing
- Medical/dental offices



Wipers dispense one-at-a-time for ease of use

Code	Description	Delivery System	Color	Material	Size (W x L)	Boxes/Case	Units/Box	Total/Case
34623	Kimtech Science™ Lens Cleaning Station		White	1-ply tissue	4.4" x 8.4"	4	560 wipes & 8 oz. spray	2,240
34644	Kimtech Science™ Lens Cleaning Station		White	1-ply tissue	4.4" x 8.4"	4	1,120 wipes & 16 oz. spray	4,480

Kimtech Science™ Bench Top Protector

▶ PRODUCT FEATURES

- Flat, stable surface helps protect experiments and delicate glassware
- Quickly absorbs spills
- Better wet durability than competitive sheet products
- Slip-resistant polyethylene backing keeps mats in place
- Lies flat and remains flat even after drying



Fluid barrier resists harsh chemicals

Code	Description	Delivery System	Color	Material	Size (W x L)	Wipers/Unit	Units/Case	Total/Case
75460	Kimtech Science™ Bench Top Protector	Sheet	Top layer (white) cellulose fiber; Bottom layer (green) anti-slip polyethylene film	Airlaid/Polyethylene	18" x 19.5"	50	8	400

Kimtech™ Wipers for the WetTask™ Refillable Wet Wiping System

Choose the Kimtech™ Wiper that works best for your task & add the chemical solution you prefer.

▶ PRODUCT FEATURES

- Reduces exposure to chemical vapors & splashes
- Eliminates potential chemical spills
- Clean, fresh wiper every time
- Enclosed system helps to avoid contamination of the wipers and cleaning solution when in use

TYPICAL USES

- Surface preparation
- Surface cleaning, sanitizing, and disinfecting
- Cleaning and removing soil, oil and grease
- Solvent application



3 Easy Steps



Available in two sizes

Code	Chemical Type	Delivery System	Color	Material	Size (W x L)	Qty/Case	Sheets/Roll	Dispenser
06001	Kimtech Prep™ Wipers for Solvents	Roll	White	Hydroknit®	12" x 12.5"	6	60	1 Free Bucket/Case
06211	Kimtech Prep™ Wipers for Disinfectants and Sanitizers		White	Spunlace	12" x 12.5"	6	90	1 Free Bucket/Case
06411	Kimtech Prep™ Wipers for Bleach, Disinfectants and Sanitizers		White	Meltblown	12" x 12.5"	6	90	1 Free Bucket/Case
06471	Kimtech Prep™ Wipers for Bleach, Disinfectants and Sanitizers		White	Meltblown	12" x 12.5"	6	90	No Bucket Included
36101	Kimtech™ Dual Function Wipers with Textured Surface for Bleach, Disinfectants and Sanitizers		Purple/White	Meltblown	12" x 12.5"	6	90	1 Free Bucket/Case
77320	Kimtech Prep™ Wipers for Bleach, Disinfectants and Sanitizers		White	Meltblown	12" x 12.5"	12	35	1 Free Canister/Case
06006	Kimtech Prep™ Wipers for Solvents		White	Hydroknit®	9" x 15"	2	275	09361
09361	Kimtech™ Wipers for the WetTask™ System	Bucket	Blue	N/A	3.5 Gallons	2	N/A	Bucket for 06006

WypAll® L10 Towels — Light-duty, single-use towels

▶ PRODUCT FEATURES

- Strong & durable for general clean-up tasks
- Compostable¹⁰
- Portable dispensers enable you to keep product where you work

Meets EPA guidelines for minimum post-consumer waste content; towels 40%



Code	Description	Delivery System	Color	Material	Size (W x L)	Wipers/Box	Boxes/Case	Dispenser
05320	Utility Wipers	Pop-Up™ Box	White	1-ply paper	9" x 10.25"	125	18	09352, 46091
05322	Utility Wipers	Pop-Up™ Box	White	1-ply paper	12" x 10.25"	125	18	09352, 46091
42346	Light Weight Utility Wipers	Pop-Up™ Box	White	1-ply paper	9" x 10.25"	250	24	09352, 46091
05120	Windshield Wipers	Banded	Blue	2-ply paper	9.3" x 10.25"	140	16	N/A
05123	Windshield Wipers	Banded	Blue	1-ply paper	9.1" x 10.25"	224	10	N/A
01770	Dairy Wipers	Banded	White	1-ply paper	9.3" x 10.25"	200	12	N/A
01772	Dairy Wipers	Pop-Up™ Box	White	1-ply paper	9" x 10.25"	110	18	09352, 46091

WypAll® L30 Towels — Soft, absorbent, medium-duty towels

▶ PRODUCT FEATURES

- Cloth-like feel at a value price
- Soft enough for personal use¹¹
- Compostable¹⁰
- Portable dispensers enable you to keep product where you work



Code	Description	Delivery System	Color	Material	Size (W x L)	Wipers/Box	Boxes/Case	Dispenser
05816	WypAll® L30 Towels	Pop-Up™ Box	White	DRC	16.4" x 9.8"	120	6	09352
05800	WypAll® L30 Towels	Pop-Up™ Box	White	DRC	16.4" x 9.8"	100	8	09352
03086	WypAll® L30 Towels	Pop-Up™ Box	White	DRC	10" x 9.8"	120	10	73900
05812	WypAll® L30 Towels	1/4 Fold	White	DRC	12.5" x 12"	90	12	45888, 09107
05820	WypAll® L30 Towels	Center-Pull	White	DRC	9.8" x 15.2"	300	2	09335
05830	WypAll® L30 Towels	Center-Pull	White	DRC	8" x 15"	150	6	09335
05841	WypAll® L30 Towels	Jumbo Roll	White	DRC	12.4" x 13.3"	950	1	80596, 80579
05843	WypAll® L30 Towels	Small Roll	White	DRC	11" x 10.4"	70	24	N/A

¹⁰ All Kimberly-Clark Professional white L series towels can be aerobically composted in municipal or industrial facilities in the United States and Canada by ASTM D6868-11. Check with your waste hauler to ensure your application and their composting process are compatible.







¹¹ Not for use on compromised skin

WypAll® X60 Cloths — A versatile reusable cloth to replace assorted rags



▶ PRODUCT FEATURES

- Absorbs 2 times more water and oil than rags¹² for faster clean-up
- Tough enough for big jobs — soft enough for face & hands¹¹
- Rinse & reuse — reduces waste & cost
- On average, reduces disposal waste by 78% versus rags
- Clean & consistent cloth every time
- Portable dispensers enable you to keep product where you work

Code	Description	Delivery System	Color	Material	Size (W x L)	Wipers/Box	Boxes/Case	Dispenser
34015	WypAll® X60 Cloths	 Brag™ Box	White	Hydroknit®	12.5" x 16.8"	180	1	73900
34790	WypAll® X60 Cloths	 Pop-Up™ Box	White	Hydroknit®	9.1" x 16.8"	126	10	73900
34865	WypAll® X60 Cloths	 1/4 Fold	White	Hydroknit®	12.5" x 12"	76	12	45888, 09107
34770	WypAll® X60 Cloths		White	Hydroknit®	11" x 23"	100	9	45888, 09107
34900	WypAll® X60 Cloths	 Flat Sheet	White	Hydroknit®	12.5" x 16.8"	150	6	N/A
35401	WypAll® X60 Cloths	 Small Roll	White	Hydroknit®	9.8" x 13.4"	130	12	N/A
35411	WypAll® X60 Cloths		Blue	Hydroknit®	9.8" x 13.4"	130	12	N/A
35421	WypAll® X60 Cloths		White	Hydroknit®	19.8" x 13.4"	130	6	N/A
35431	WypAll® X60 Cloths		Blue	Hydroknit®	19.8" x 13.4"	130	6	N/A
34955	WypAll® X60 Cloths	 Jumbo Roll	White	Hydroknit®	12.5" x 13.4"	1,100	1	80596, 80579
34965	WypAll® X60 Cloths		Blue	Hydroknit®	12.5" x 13.4"	1,100	1	80596, 80579

¹¹ Not for use on compromised skin ¹² Pound for pound, based on one test lot



Eyewear

Kimberly-Clark Professional offers safety eyewear for different work environments and a variety of different tasks. Designed with the wearer's needs and style in mind, our eyewear offers a comprehensive portfolio of eye protection options.

DON'T LET YOUR WORKERS BECOME A STATISTIC
 More than **2,000** people sustain a job-related eye injury every day.¹³

Protection for Different Environments and Tasks

Our eyewear offerings provide workers with choices — such as different colors, sizes and vision assistance — potentially tipping the scale between protection and injury. Why take a chance on anything else? Choose our trusted brands to enhance safety and productivity in your workplace.

Symbols Key

- Z87.1** Meets the optical requirements of the ANSI Z87.1 standards
- D4** Meets the ANSI Z87.1 requirements for dust protection
- UV** Lenses are made of a polycarbonate material that provides 99.9% UVA/UVB/UVC protection
- +** Meets the impact protector requirements of the ANSI Z87.1 standards
- D5** Meets the ANSI Z87.1 requirements for fine dust protection
- TAA** Product complies with the Trade Agreements Act
- D3** Meets the ANSI Z87.1 requirements for liquid splash/droplet protection
- SP** Certified to meet the impact, ignition/flammability, coverage, and optical requirements of the CSA Z94.3 standards
- BASE CURVE 10** Number denotes the base curve of the eyewear; a higher base curve provides more wraparound protection and peripheral vision, and can reduce the need for side shields

Element® Safety Eyewear — Visitor safety glasses



PRODUCT FEATURES

- Lightweight, popular styling with an economical price
- Metal-free design with screwless hinges

Code	Lens	Coating	Frame	Pairs/Box
25627	Clear	Uncoated	Clear	12
29094	Amber	Uncoated	Black	12
33072	Light Blue	Uncoated	Light Blue	12
25638	Indoor/Outdoor	Uncoated	Black	12
25631	Smoke	Uncoated	Black	12
29110	Blue Mirror	Mirror	Black	12



¹³ National Institute of Occupational Safety and Health (NIOSH)
<https://www.cdc.gov/niosh/topics/eye/default.html>

Nemesis™ Safety Eyewear — Stylish comfort. Lasting protection.



▶ PRODUCT FEATURES

- Sporty, flexible, and lightweight design for comfort and compliance
- Patented Flex-Dry™ nosepiece designed for comfort with enhanced flexibility and integrated ridges to divert sweat
- Hardcoated lenses for scratch resistance and longer life



Nemesis™ Small Eyewear: Sporty eyewear that fits a smaller, slimmer head without adjustments

Code	Lens	Coating	Frame	Gravity Feed	Pairs/Box
25676	○ Clear		● Black	●	12
25679	○ Clear	Anti-Fog	● Black		12
25659	● Amber		● Black		12
25685	○ Indoor/Outdoor		● Black		12
25688	● Smoke Mirror	Mirror	● Black	●	12
19639	○ Light Blue		● Blue		12
47378	○ Clear	Anti-Fog	● Red	●	12
47388	○ Clear	Anti-Fog	● Silver	●	12
47383	● Smoke	Anti-Fog	● Silver	●	12
47384	○ Clear	Anti-Fog	● Metallic Blue	●	12
47387	● Smoke	Anti-Fog	● Metallic Blue	●	12
47417	● Polarized Smoke		● Camo	●	12


Nemesis™ Small Safety Eyewear

38474	○ Clear		● Black w/Black Tips		12
38478	○ Clear	Anti-Fog	● Black w/Pink Tips		12

Every pair includes a neck cord for reduced risk of damage when not being worn



Comfort, Style and Durability



While other eyewear snaps under a little bit of stress, the Nemesis™ Eyewear can handle the pressure.¹⁴

¹⁴ Applies to Nemesis™, Nemesis™ Polarized, Nemesis™ VL, Nemesis™ CSA, Nemesis™ with Rx Inserts, and Nemesis™ Rx Readers Safety Glasses

Nemesis™ CSA Safety Eyewear — CSA certified



▶ PRODUCT FEATURES

- Sporty, flexible, lightweight design that is certified to meet the requirements of CSA Z94.3
- Patented Flex-Dry™ nosepiece designed for comfort with enhanced flexibility and integrated ridges to channel away sweat
- Hardcoated lenses for scratch resistance and longer life

Every pair includes a neck cord for reduced risk of damage when not being worn



Code	Lens	Coating	Frame	Gravity Feed	Pairs/Box
20378	○ Clear		● Black	●	12
20379	○ Clear	Anti-Fog	● Black	●	12
20381	○ Indoor/Outdoor		● Black	●	12
20380	● Smoke Mirror		● Black	●	12

Nemesis™ Rx Readers Safety Eyewear



▶ PRODUCT FEATURES

- Sporty, flexible, lightweight eyewear with integrated diopters for vision assistance
- Patented Flex-Dry™ nosepiece designed for comfort with enhanced flexibility and integrated ridges to divert sweat
- Hardcoated lenses for scratch resistance and longer life

Note: Styles marked with ■ are not CSA certified



Every pair includes a neck cord for reduced risk of damage when not being worn

Code	Lens	Strength	Frame	Gravity Feed	Pairs/Box
28618	○ Clear	+1.0	● Black	●	6
28621	○ Clear	+1.5	● Black	●	6
28624	○ Clear	+2.0	● Black	●	6
28627	○ Clear	+2.5	● Black	●	6
28630	○ Clear	+3.0	● Black	●	6
22516 ■	● Smoke	+1.5	● Black		6
22518 ■	● Smoke	+2.0	● Black		6
22519 ■	● Smoke	+2.5	● Black		6



Smith & Wesson® Caliber™ Safety Eyewear



PRODUCT FEATURES

- Frameless sunglass design with contoured flexible rubber temples offer long-term comfort; designed not to pinch or put pressure on the user's head
- Thin, flexible nosepiece has built-in airflow holes for flexibility and comfort
- Hardcoated lenses for scratch resistance and longer life



Hinge stops prevent temple tips from scratching lenses for increased longevity

Code	Lens	Coating	Frame	Gravity Feed	Pairs/Box
23006	○ Clear	Anti-Fog	● Black	●	12
23008	○ Indoor/Outdoor	Anti-Fog	● Black	●	12
23007	○ Smoke	Anti-Fog	● Black	●	12
23010	○ Brown	Anti-Fog	● Brown	●	12

Smith & Wesson® Magnum® 3G Safety Eyewear



PRODUCT FEATURES

- Safety eyewear with a frameless sunglass design
- Extendable temples offer three different temple lengths for a customized fit
- Self-adjusting nose pad with rubber fingers designed to prevent glasses from slipping down the nose
- Hinge stops prevent temple tips from scratching lenses for increased longevity
- Hardcoated lenses for scratch resistance and longer life



The same frameless sunglass design of Magnum® 3G, but in a smaller frame size for smaller, slimmer heads

Code	Lens	Coating	Frame	Pairs/Box
19799	○ Clear		● Black	12
19794	○ Clear	Anti-Fog	● Black	12
19796	○ Copper Blue Shield		● Black	12
19823	○ Smoke		● Black	12
19831	○ Indoor/Outdoor		○ Metallic Gray	12

Magnum® 3G Mini Safety Eyewear

Code	Lens	Frame	Pairs/Box
19822	○ Clear	● Black	12


Monogoggle™ 202 Particle Protection Safety Goggles



PRODUCT FEATURES

- Two-piece goggle frame with a separate soft, cushioning nosepiece for enhanced fit and comfort
- Unventilated design provides protection from fine dust particles
- Fits over most prescription eyeglasses

Code	Lens	Coating	Frame	Pairs/Box
16666	○ Clear	—	● Green	36
16667	○ Clear	Anti-Fog	● Green	36




Monogoggle™ VPC Splash Protection Safety Goggles



PRODUCT FEATURES

- Splash protection goggles in the same two-piece goggle frame as the Monogoggle™ 202 and 211, but with a larger lens for enhanced fit and comfort with larger prescription eyeglasses
- Indirect ventilation like the Monogoggle™ 211 style, but with two additional baffled ports to increase airflow and minimize condensation and fogging, while protecting from splashes
- Wider nosepiece to fit over most half-mask respirators
- Fits over most prescription eyeglasses

Code	Lens	Coating	Frame	Pairs/Box
16361	○ Clear	Anti-Fog	● Bronze	36



Shield™ Safety Goggles



PRODUCT FEATURES

- Monogoggle™ XTR goggles integrated into a face shield to provide full eye and face protection from liquids without the hassle of primary eye protection underneath a face shield
- Curved face shield conforms to the shape of the face for added protection
- Fits over most prescription eyeglasses

Code	Lens	Coating	Frame	Pairs/Box
18629	○ Clear	Anti-Fog	● Blue	6



Monogoggle™ 211 Splash Protection Safety Goggles



▶ PRODUCT FEATURES

- Economical splash protection with a soft, pliable frame for enhanced fit and comfort
- Button vents offer indirect ventilation while providing protection from splashes
- Fits over most prescription eyeglasses



Headband buckles are located towards the rear of the goggle frame to limit interference with peripheral vision

Code	Lens	Coating	Frame	Pairs/Box
14384	○ Clear		● Green	36
14387	○ Clear	Anti-Fog	● Green	36
16668	○ Clear (with Foam)	Anti-Fog	● Green	36
16669	○ Clear (Respiratory)	Anti-Fog	● Green	36
16670	○ Clear	Anti-Fog	● Smoke	36

Revolution™ OTG Splash Protection Safety Goggles



▶ PRODUCT FEATURES

- Splash protection in a sleek, sporty design with a curved lens for enhanced field of vision
- Patented cross vent technology keeps air flowing in and moisture out to prevent fogging
- Soft, pliable frame gasket for enhanced fit and comfort
- Fits over most prescription eyeglasses



Code	Lens	Coating	Frame	Pairs/Box
14399	○ Clear	Anti-Fog	● Blue	30
14402	● Amber	Anti-Fog	● Blue	30
14401	● Smoke	Anti-Fog	● Blue	30
18483	○ Clear	Anti-Fog	● Black	30

Choose Kimberly-Clark Professional Products for All Your Needs in Critical Environments

Kimberly-Clark Professional offers you convenience, reliability and technical expertise in a single source for apparel, masks, gloves, wipers and eyewear for critical environments.

Certified Quality Documentation:

For Certificates of Conformance, Certificates of Analysis and Certificates of Irradiation, visit www.kimtech.com/certificates or e-mail kimtech@kcc.com.



▶ ⚠ WARNINGS: Improper use or failure to heed warnings may result in serious injury or death.

Do not use respirators for sandblasting or to protect against asbestos, lead-based paint, pesticides, oil aerosols[§], vapors or gases. Do not wear respirators when conditions prevent a good facial seal. It is important to fit check the respirator each time it is worn.

[§] Except R95 or P95



Visit our website at www.kimtech.com

OR contact us at **800-255-6401**

Technical Help: kimtech@kcc.com | **888-346-4652**

Our Guarantee

Your total satisfaction means everything to us. If, for any reason, our products do not meet your expectations, Kimberly-Clark will reimburse you[†] for your initial purchase, via FREE product, for up to \$1,000. For more information on Kimberly-Clark Professional, visit us online at www.KCProfessional.com. [†] Guarantee extended to consuming end-user accounts only.

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

©/TM Trademarks of Kimberly-Clark Worldwide, Inc. Marques déposées de Kimberly-Clark Worldwide, Inc. The Daisy Design is a trademark of Kimberly-Clark Worldwide, Inc. Saranex® is a registered trademark of the Dow Chemical Company. VELCRO® is a registered trademark of Velcro BVB. The color Purple, Purple Nitrile™, Purple Nitrile-Xtra™, the color Gray, Sterling™, the color Lavender, Lavender™, the color Orange, Fluidshield™, The Lite One™, Soft Touch II™ and Ultra™ are trademarks of Halyard Health or its affiliates and used under license. SMITH & WESSON® and Magnum® are trademarks owned by Smith & Wesson Corp and used under license. ©KCIWW. 1745YK-01 7/18