

## Save with Printer Starter Kits



| Catalog #                                              | Kit Contents                                                                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>BMP41 DataComm Starter Kit</b><br>(BMP41-KIT-VD)    | 1 - BMP41 Label Printer Standard Package (BMP41-KIT)<br>1 - BMP41 Hard Case (BMP41-HC)<br>1 - 1.0 in. black on white B-427 cartridge (M-51-427)<br>1 - 0.475 in. black on white B-412 cartridge (MC-475-412)<br>1 - 1.0 in. black on yellow B-595 cartridge (MC1-1000-595-YL-BK)<br>1 - 1.0 in. black on white B-595 cartridge (MC1-1000-595-WT-BK)                                                             |
| <b>BMP41 Electrical Starter Kit</b><br>(BMP41-KIT-EL)  | 1 - BMP41 Label Printer Standard Package (BMP41-KIT)<br>1 - BMP41 Hard Case (BMP41-HC)<br>1 - 1.0 in. black on white B-427 cartridge (M-143-427)<br>1 - 1.0 in. black on white B-498 cartridge (M-48-498)<br>1 - 0.75 in. black on white B-342 cartridge (M-187-075-342)<br>1 - 1.0 in. black on orange B-595 cartridge (MC1-1000-595-OR-BK)<br>1 - 1.0 in. black on white B-595 cartridge (MC1-1000-595-WT-BK) |
| <b>BMP41 Facility ID Starter Kit</b><br>(BMP41-KIT-GI) | 1 - BMP41 Label Printer Standard Package (BMP41-KIT)<br>1 - 1.0 in. black on yellow B-595 cartridge (MC1-1000-595-YL-BK)<br>1 - 1.0 in. red on white B-595 cartridge (MC1-1000-595-WT-RD)<br>1 - 1.0 in. white on green B-595 cartridge (MC1-1000-595-GN-WT)<br>1 - 1.0 in. black on white B-595 cartridge (MC1-1000-595-WT-BK)<br>1 - 1.0 in. black on white B-483 cartridge (M-60-483)                        |

\*Printer ships with BMP41 rechargeable battery pack, MC1-1000-595-WT-BK cartridge, USB cable, AC adapter, product CD, printer drivers CD, quick start guide and 2-year warranty.

## Indoor and Outdoor Vinyl for Safety, Facility and Lean 5S (B-595)

Continuous vinyl material is ideal for lean 5S labels, pipe markers, equipment and production area identification. These labels offer excellent resistance to oils, detergents, dirt, grime and many solvents. Permanent adhesive, very pliable, good for rough surfaces and outdoor use. 8-10 years average outdoor durability.\* Temp. range: -40° F to 180° F (-40° C to 82° C). UL recognized.



Figure 33



| Fits Printers | Figure  | Catalog #          | B#    | Material | Color    | Label Width A<br>Inch (mm) | Roll Length B<br>Feet (m) | Labels<br>Per Roll | Ribbon in<br>Cartridge |
|---------------|---------|--------------------|-------|----------|----------|----------------------------|---------------------------|--------------------|------------------------|
| BMP41, 51, 53 | Fig. 33 | MC-375-595-WT-BK   | B-595 | Vinyl    | BK on WT | 0.375 (9.5)                | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-WT-BK   | B-595 | Vinyl    | BK on WT | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-WT-BK   | B-595 | Vinyl    | BK on WT | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-WT-BK | B-595 | Vinyl    | BK on WT | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-375-595-YL-BK   | B-595 | Vinyl    | BK on YL | 0.375 (9.5)                | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-YL-BK   | B-595 | Vinyl    | BK on YL | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-YL-BK   | B-595 | Vinyl    | BK on YL | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-YL-BK | B-595 | Vinyl    | BK on YL | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-OR-BK   | B-595 | Vinyl    | BK on OR | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-OR-BK   | B-595 | Vinyl    | BK on OR | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-OR-BK | B-595 | Vinyl    | BK on OR | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-BL-WT   | B-595 | Vinyl    | WT on BL | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-BL-WT   | B-595 | Vinyl    | WT on BL | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-BL-WT | B-595 | Vinyl    | WT on BL | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-375-595-RD-WT   | B-595 | Vinyl    | WT on RD | 0.375 (9.5)                | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-RD-WT   | B-595 | Vinyl    | WT on RD | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-RD-WT   | B-595 | Vinyl    | WT on RD | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-RD-WT | B-595 | Vinyl    | WT on RD | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-GN-WT   | B-595 | Vinyl    | WT on GN | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-GN-WT   | B-595 | Vinyl    | WT on GN | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-GN-WT | B-595 | Vinyl    | WT on GN | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-WT-RD   | B-595 | Vinyl    | RD on WT | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-WT-RD   | B-595 | Vinyl    | RD on WT | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-WT-RD | B-595 | Vinyl    | RD on WT | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-BK-WT   | B-595 | Vinyl    | WT on BK | 0.500 (12.7)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-BK-WT   | B-595 | Vinyl    | WT on BK | 0.750 (19.1)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-BK-WT | B-595 | Vinyl    | WT on BK | 1.000 (25.4)               | 25 (7.6)                  | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-CL-BK   | B-595 | Vinyl    | BK on CL | 0.500 (12.7)               | 20 (6.09)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-CL-BK   | B-595 | Vinyl    | BK on CL | 0.750 (19.1)               | 20 (6.09)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-CL-BK | B-595 | Vinyl    | BK on CL | 1.000 (25.4)               | 20 (6.09)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-CL-WT   | B-595 | Vinyl    | WT on CL | 0.500 (12.7)               | 20 (6.09)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-CL-WT   | B-595 | Vinyl    | WT on CL | 0.750 (19.1)               | 20 (6.09)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-CL-WT | B-595 | Vinyl    | WT on CL | 1.000 (25.4)               | 20 (6.09)                 | 1 roll (cont.)     | R4400                  |

\* Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques and material color. The 8 to 10 year outdoor durability applies to the vinyl label stock only; ribbon durability will vary.

## Indoor and Outdoor Vinyl for Safety, Facility and Lean 5S (B-595)

Continuous vinyl material is ideal for lean 5S labels, pipe markers, equipment and production area identification. These labels offer excellent resistance to oils, detergents, dirt, grime and many solvents. Permanent adhesive, very pliable, good for rough surfaces and outdoor use. 8-10 years average outdoor durability.\* Temp. range: -40° F to 180° F (-40° C to 82° C). UL recognized.



Figure 33



| Fits Printers | Figure  | Catalog #          | B#    | Material | Color           | Label Width A<br>Inch (mm) | Roll Length B<br>Feet (m) | Labels<br>Per Roll | Ribbon in<br>Cartridge |
|---------------|---------|--------------------|-------|----------|-----------------|----------------------------|---------------------------|--------------------|------------------------|
| BMP51, 53     | Fig. 33 | MC-250-595-WT-BK   | B-595 | Vinyl    | Black on White  | 0.250 (6.35)               | 25 (7.62)                 | 1 roll (cont.)     | R10000                 |
| BMP41, 51, 53 | Fig. 33 | MC-375-595-WT-BK   | B-595 | Vinyl    | Black on White  | 0.375 (9.5)                | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-WT-BK   | B-595 | Vinyl    | Black on White  | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-WT-BK   | B-595 | Vinyl    | Black on White  | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-WT-BK | B-595 | Vinyl    | Black on White  | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-WT-BK  | B-595 | Vinyl    | Black on White  | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP51, 53     | Fig. 33 | MC-250-595-YL-BK   | B-595 | Vinyl    | Black on Yellow | 0.250 (6.35)               | 25 (7.62)                 | 1 roll (cont.)     | R10000                 |
| BMP41, 51, 53 | Fig. 33 | MC-375-595-YL-BK   | B-595 | Vinyl    | Black on Yellow | 0.375 (9.5)                | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-YL-BK   | B-595 | Vinyl    | Black on Yellow | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-YL-BK   | B-595 | Vinyl    | Black on Yellow | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-YL-BK | B-595 | Vinyl    | Black on Yellow | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-YL-BK  | B-595 | Vinyl    | Black on Yellow | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-OR-BK   | B-595 | Vinyl    | Black on Orange | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-OR-BK   | B-595 | Vinyl    | Black on Orange | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-OR-BK | B-595 | Vinyl    | Black on Orange | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-OR-BK  | B-595 | Vinyl    | Black on Orange | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-BL-WT   | B-595 | Vinyl    | White on Blue   | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-BL-WT   | B-595 | Vinyl    | White on Blue   | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-BL-WT | B-595 | Vinyl    | White on Blue   | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-BL-WT  | B-595 | Vinyl    | White on Blue   | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-375-595-RD-WT   | B-595 | Vinyl    | White on Red    | 0.375 (9.5)                | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-RD-WT   | B-595 | Vinyl    | White on Red    | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-RD-WT   | B-595 | Vinyl    | White on Red    | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-RD-WT | B-595 | Vinyl    | White on Red    | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-RD-WT  | B-595 | Vinyl    | White on Red    | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-GN-WT   | B-595 | Vinyl    | White on Green  | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-GN-WT   | B-595 | Vinyl    | White on Green  | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-GN-WT | B-595 | Vinyl    | White on Green  | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-GN-WT  | B-595 | Vinyl    | White on Green  | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-WT-RD   | B-595 | Vinyl    | Red on White    | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-WT-RD   | B-595 | Vinyl    | Red on White    | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-WT-RD | B-595 | Vinyl    | Red on White    | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-WT-RD  | B-595 | Vinyl    | Red on White    | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-CL-BK   | B-595 | Vinyl    | Black on Clear  | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-CL-BK   | B-595 | Vinyl    | Black on Clear  | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-CL-BK | B-595 | Vinyl    | Black on Clear  | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-CL-BK  | B-595 | Vinyl    | Black on Clear  | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-500-595-CL-WT   | B-595 | Vinyl    | White on Clear  | 0.500 (12.70)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC-750-595-CL-WT   | B-595 | Vinyl    | White on Clear  | 0.750 (19.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP41, 51, 53 | Fig. 33 | MC1-1000-595-CL-WT | B-595 | Vinyl    | White on Clear  | 1.000 (25.40)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |
| BMP51, 53     | Fig. 33 | MC-1500-595-CL-WT  | B-595 | Vinyl    | White on Clear  | 1.500 (38.10)              | 25 (7.62)                 | 1 roll (cont.)     | R4400                  |

\* Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques and material color. The 8-10 year outdoor durability applies to the vinyl label stock only; ribbon durability will vary.

## Inside-Panel Component Labels for Electrical, Automation and Data Centers (B-422, B-428, B-483, B-499 and B-595)

Variety of durable materials ideal for marking backer boards, DIN rail, relays, PLCs, switches and solenoids. Create serial or rating plates with barcodes, graphics and more with a flexible high-tack adhesive for easy and long-lasting adhesion.

- **B-422 Polyester Material:** Permanent adhesive, good for powder-coated and textured surfaces. Best on flat surfaces. Temp. range: -40° F to 212° F (-40° C to 100° C). UL recognized.
- **B-428 Metalized Polyester Material:** Permanent adhesive, silver finish. Temp. range: -40° F to 176° F (-40° C to 80° C). UL recognized.
- **B-483 Polyester Material:** Permanent adhesive for powder-coated and textured surfaces. Best on flat surfaces Temp. range: -40° F to 248° F (-40° C to 120° C). UL recognized.
- **B-499 Nylon Cloth Material:** Permanent adhesive. Pliable for rough or smooth surfaces. Temp. range: -94° F to 194° F (-70° C to 90° C). UL recognized.
- **B-595 Indoor / Outdoor Vinyl Material:** Permanent adhesive, very pliable, good for rough surfaces and outdoor use, wide range of colors. Temp. range: -40° F to 180° F (-40° C to 82° C). UL recognized.




Figure 2



Figure 33




Figure 46 (with border)

| Fits Printers                             | Figure  | Catalog #          | B#    | Material            | Color           | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Labels<br>Per Roll | Ribbon in<br>Cartridge |
|-------------------------------------------|---------|--------------------|-------|---------------------|-----------------|----------------------------|-----------------------------|--------------------|------------------------|
| <b>B-422 Gloss Polyester</b>              |         |                    |       |                     |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 33 | MC-375-422         | B-422 | Gloss Polyester     | Black on White  | 0.375 (9.5)                | 25 ft. (7.6 m)              | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC-475-422         | B-422 | Gloss Polyester     | Black on White  | 0.475 (12.1)               | 25 ft. (7.6 m)              | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC-500-422         | B-422 | Gloss Polyester     | Black on White  | 0.500 (12.7)               | 25 ft. (7.6 m)              | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-7-422            | B-422 | Gloss Polyester     | Black on White  | 0.500 (12.70)              | 0.500 (12.70)               | 280                | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-89-422           | B-422 | Gloss Polyester     | Black on White  | 0.500 (12.70)              | 1.500 (38.10)               | 360                | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-47-422           | B-422 | Gloss Polyester     | Black on White  | 1.000 (25.40)              | 0.500 (12.70)               | 360                | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-49-422           | B-422 | Gloss Polyester     | Black on White  | 1.000 (25.40)              | 1.000 (25.40)               | 200                | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-422       | B-422 | Gloss Polyester     | Black on White  | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-90-422           | B-422 | Gloss Polyester     | Black on White  | 1.500 (38.10)              | 0.750 (19.05)               | 200                | R6000                  |
| <b>B-428 Metalized Polyester</b>          |         |                    |       |                     |                 |                            |                             |                    |                        |
| BMP51, 53                                 | Fig. 2  | M-29-428           | B-428 | Metalized Polyester | Light Gray      | 0.500 (12.70)              | 1.500 (38.10)               | 360                | R4300                  |
| BMP51, 53                                 | Fig. 2  | M-30-428           | B-428 | Metalized Polyester | Light Gray      | 0.750 (19.05)              | 1.500 (38.10)               | 260                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-47-428           | B-428 | Metalized Polyester | Light Gray      | 1.000 (25.40)              | 0.500 (12.70)               | 360                | R4300                  |
| BMP41, 51, 53                             | Fig. 46 | M-92-428-BB        | B-428 | Metalized Polyester | Light Gray      | 1.130 (28.70)              | 0.500 (12.70)               | 360                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-60-428           | B-428 | Metalized Polyester | Light Gray      | 2.000 (50.80)              | 1.000 (25.40)               | 80                 | R4300                  |
| <b>B-483 Ultra-Aggressive Polyester</b>   |         |                    |       |                     |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 2  | M-47-483           | B-483 | Polyester           | Black on White  | 1.000 (25.4)               | 0.500 (12.7)                | 480                | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-61-483           | B-483 | Polyester           | Black on White  | 2.000 (50.80)              | 0.500 (12.70)               | 80                 | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-60-483           | B-483 | Polyester           | Black on White  | 2.000 (50.80)              | 1.000 (25.40)               | 80                 | R6000                  |
| <b>B-499 Nylon Cloth</b>                  |         |                    |       |                     |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 2  | M-131-499          | B-499 | Nylon Cloth         | Black on White  | 0.500 (12.7)               | 1.000 (25.40)               | 180                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-11-499           | B-499 | Nylon Cloth         | Black on White  | 0.500 (12.70)              | 0.750 (19.05)               | 220                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-84-499           | B-499 | Nylon Cloth         | Black on White  | 0.900 (22.86)              | 0.500 (12.70)               | 200                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-128-499          | B-499 | Nylon Cloth         | Black on White  | 1.000 (25.40)              | 1.900 (48.3)                | 100                | R4300                  |
| BMP51, 53                                 | Fig. 2  | M-132-499          | B-499 | Nylon Cloth         | Black on White  | 1.500 (38.10)              | 1.250 (31.75)               | 160                | R4300                  |
| <b>B-595 Indoor / Outdoor Vinyl Tape*</b> |         |                    |       |                     |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 33 | MC-500-595-WT-BK   | B-595 | Vinyl               | Black on White  | 0.500 (12.70)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-595-WT-BK | B-595 | Vinyl               | Black on White  | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC-500-595-YL-BK   | B-595 | Vinyl               | Black on Yellow | 0.500 (12.70)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-595-YL-BK | B-595 | Vinyl               | Black on Yellow | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC-500-595-OR-BK   | B-595 | Vinyl               | Black on Orange | 0.500 (12.70)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-595-OR-BK | B-595 | Vinyl               | Black on Orange | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |

\* For additional vinyl label colors, refer to the B-595 indoor / outdoor grade facility and safety labels on page 116.

## Bin, Storage and General Industrial Labels (B-483, B-499 and B-595)

Several materials with an aggressive adhesive for use in commercial and industrial applications.

- **B-483 Polyester Material:** Permanent adhesive for powder-coated and textured surfaces. Best on flat surfaces Temp. range: -40° F to 248° F (-40° C to 120° C). UL recognized.
- **B-499 Nylon Cloth Material:** Permanent adhesive. Pliable for rough or smooth surfaces. Temp. range: -94° F to 194° F (-70° C to 90° C). UL recognized.
- **B-595 Indoor / Outdoor Vinyl Material:** Permanent adhesive, very pliable, good for rough surfaces and outdoor use. Temp. range: -40° F to 180° F (-40° C to 82° C). UL recognized.




Figure 2



Figure 33

| Fits Printers                             | Figure  | Catalog #          | B#    | Material    | Color           | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Labels<br>Per Roll | Ribbon in<br>Cartridge |
|-------------------------------------------|---------|--------------------|-------|-------------|-----------------|----------------------------|-----------------------------|--------------------|------------------------|
| <b>B-483 Ultra-Aggressive Polyester</b>   |         |                    |       |             |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 2  | M-47-483           | B-483 | Polyester   | Black on White  | 1.000 (25.4)               | 0.500 (12.7)                | 360                | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-61-483           | B-483 | Polyester   | Black on White  | 2.000 (50.80)              | 0.500 (12.70)               | 80                 | R6000                  |
| BMP41, 51, 53                             | Fig. 2  | M-60-483           | B-483 | Polyester   | Black on White  | 2.000 (50.80)              | 1.000 (25.40)               | 80                 | R6000                  |
| <b>B-499 Nylon Cloth</b>                  |         |                    |       |             |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 2  | M-11-499           | B-499 | Nylon Cloth | Black on White  | 0.500 (12.70)              | 0.750 (19.05)               | 220                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-84-499           | B-499 | Nylon Cloth | Black on White  | 0.900 (22.86)              | 0.500 (12.70)               | 200                | R4300                  |
| BMP41, 51, 53                             | Fig. 2  | M-128-499          | B-499 | Nylon Cloth | Black on White  | 1.000 (25.40)              | 1.900 (48.3)                | 100                | R4300                  |
| BMP51, 53                                 | Fig. 2  | M-132-499          | B-499 | Nylon Cloth | Black on White  | 1.500 (38.10)              | 1.250 (31.75)               | 160                | R4300                  |
| <b>B-595 Indoor / Outdoor Vinyl Tape*</b> |         |                    |       |             |                 |                            |                             |                    |                        |
| BMP41, 51, 53                             | Fig. 33 | MC-750-595-WT-BK   | B-595 | Vinyl       | Black on White  | 0.750 (19.10)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-595-WT-BK | B-595 | Vinyl       | Black on White  | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP51, 53                                 | Fig. 33 | MC-1500-595-WT-BK  | B-595 | Vinyl       | Black on White  | 1.500 (38.10)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC-750-595-YL-BK   | B-595 | Vinyl       | Black on Yellow | 0.750 (19.10)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP41, 51, 53                             | Fig. 33 | MC1-1000-595-YL-BK | B-595 | Vinyl       | Black on Yellow | 1.000 (25.40)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |
| BMP51, 53                                 | Fig. 33 | MC-1500-595-YL-BK  | B-595 | Vinyl       | Black on Yellow | 1.500 (38.10)              | 25 ft. (7.62 m)             | 1 roll (cont.)     | R6000                  |

\* For additional vinyl label colors, refer to the B-595 indoor / outdoor grade facility and safety labels on page 116.

## Tamper-Indicating Vinyl Labels (B-351)

Destructible vinyl material prohibits one piece removal of label to indicate if the label has been tampered with.




Figure 2



| Fits Printers | Figure | Catalog # | B#    | Material | Color          | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Labels<br>Per Roll | Ribbon in<br>Cartridge |
|---------------|--------|-----------|-------|----------|----------------|----------------------------|-----------------------------|--------------------|------------------------|
| BMP51, 53     | Fig. 2 | M-17-351  | B-351 | Vinyl    | Black on White | 0.500 (12.70)              | 1.000 (25.40)               | 360                | R6000                  |
| BMP51, 53     | Fig. 2 | M-20-351  | B-351 | Vinyl    | Black on White | 2.000 (50.80)              | 1.000 (25.40)               | 160                | R6000                  |

## Water Dissolvable Paper Labels (B-403)

Paper material completely dissolves in warm water within 30 seconds, leaving no adhesive residue.




Figure 33



| Fits Printers | Figure  | Catalog #   | B#    | Material          | Color          | Label Width A<br>Inch (mm) | Roll Length B<br>Feet (m) | Labels<br>Per Roll | Rec. Ribbon |
|---------------|---------|-------------|-------|-------------------|----------------|----------------------------|---------------------------|--------------------|-------------|
| BMP51, 53     | Fig. 33 | MC-750-403  | B-403 | Dissolvable Paper | Black on White | 0.750 (19.05)              | 25 (7.62)                 | 1 roll (cont.)     | R4300       |
| BMP51, 53     | Fig. 33 | MC-1500-403 | B-403 | Dissolvable Paper | Black on White | 1.500 (38.1)               | 25 (7.62)                 | 1 roll (cont.)     | R4300       |