GAST MFG, INC.& JUN-AIR
A Unit of IDEX Corporation
Post Office Box 97
Benton Harbor, Michigan 49022 U.S.A.
Ph: 269/926-6171
Fax: 269/925-8288


PART NUMBER
RTD1089

REV.
B

TECHNICAL DATA SHEET

ITEM NO.	MODEL NO.	AMPS	HP	kW	NET WT. lbs.	NET WT. kg	VOLT	FREQ.
1206330	2x120R-40MQ6	20/16	4	3.0	373	169	230	60/50 Hz

NOTES:
1. PRESSURE SWITCH SET TO CUT-IN AT 87 PSI & CUT-OUT AT 116 PSI.
2. PRODUCT PERFORMANCE MAY VERY ±10% IN STANDARD PRODUCTION.
3. TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
4. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
5. FOR INDOOR USE ONLY




SOUND LEVEL 69 db(A) /1m

NORMAL AMBIENT 5-40 °C / 40-104 °F

RELATIVE HUMIDITY 20-80% NON CONDENSING

ENVIRONMENT CLEAN / DUST FREE

PRODUCT PERFORMANCE:



PRODUCT DIMENSIONS:

