



**MCR
SAFETY**

96731

Memphis

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

The next generation of gloves requires the next generation in manufacturing. MCR Safety's state-of-the-art manufacturing facility produces premium NXG® brand gloves with advanced coatings, utilizes 21st-century manufacturing efficiencies, and does so with environmentally friendly production methods. Our NXG® styles are well suited for Multi-Industrial applications that require high dexterity and comfort and are manufactured on seamless knit liners that are flat dipped to reproduce the natural curved shape of the hand. As a result, workers benefit from less hand fatigue and greater productivity while performing detailed tasks to heavy duty jobs. The 96731 features a seamless 13 gauge gray nylon shell and blue latex coated palm and fingertips that will enhance gripping power. If you are looking for the best work gloves, be sure to check out MCR Safety's NXG® options! To learn more, [visit our NXG® landing page here.](#)



FEATURES:

- 13 gauge gray nylon shell
- Blue foam latex coated palm and fingertips
- Good dexterity, comfort and fit

APPLICATIONS:

Bakeries, Agriculture, Assembly Line Production, Automotive ,
Carpentry, Farming, Furniture industry, Janitorial

TECHNICAL DATA FOR: 96731

Series	Memphis	EN 388: CE Score - Abrasion	3
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	13 Gauge	ANSI Puncture	2
Material	Nylon Polyester	ANSI Abrasion	3
Made In	China		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved




MCR
SAFETY

96731

Memphis

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
96731M	Medium	9.90	3.74	2.7	16.968 lb.	1.414
96731S	Small	9.40	3.50	2.50	15.504 lb.	1.292
96731L	Large	10.2	4.02	2.7	17.952 lb.	1.496
96731XL	X - Large	10.70	4.25	2.90	19.296 lb.	1.608

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved