EXTRAFLEX® PLUS+

14-400
SPECIFICATION SHEET

TOUCH SCREEN



ANSI/ISEA 105

A4
6 5

EN388

4444D

SPECIFICATIONS:

- **Liner Materials:** 18g Black Extraflex® Plus A4 Liner
- **Coating Materials:** Black HCT® MicroFoam Nitrile
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XS-2X

Armor Guys Reference Number: 14-400

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	2X
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	6DZ	6DZ	6DZ	6DZ	6DZ	6DZ
CASE WEIGHT	15.29 lbs	16.61 lbs	17.05 lbs	18.81 lbs	19.25 lbs	20.35 lbs

PERFORMANCE LEVEL:

EN388: 4444D – EN Level 4 Cut Resistance

ABRASION	0	1	2	3	4	5	X
CUT	0	1	2	3	4	5	X
TEAR	0	1	2	3	4	5	X
PUNCTURE	0	1	2	3	4	5	X
CUT TDM TEST	A	B	C	D	E	F	

ATTRIBUTES:

- 18g Black Extraflex® Plus A4 Liner
- Black HCT® MicroFoam Nitrile Palm Coating

FEATURES:

- Silicone free
- Reinforced thumb crotch for extended wear
- Touchscreen compatible
- MicroFoam coating ensures excellent oil grip

APPLICATIONS:

- Automotive manufacturing
- Metal stamping
- Construction
- Sheet metal handling
- Steel processing

CATEGORY:

- **Extraflex® Plus**

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:

HCT
Hybrid Coating Technology

ARMOR GUYS