SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

67-117 - Red (Mirror) Edge Lit LED Exit Sign; 3.14 Watt; Dual Face; 120/277 Volts; Silver Finish

GENERAL

Company	NUVO
EA Height	8.66
EA Width	4.72
EA Length	16.34
Bulb Included	Integrated
Material	Aluminum
Fixture Type	Exit Sign
Includes	Mounting hardware and accessories
Product Notes	Aluminum, Acrylic Panel, 4.8V AA300mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C; Lumens/Illuminance: 61 cd/m2 average; Letter Height: 6 in.; Letter Stroke: 0.75 in.
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 3KV
CCT Selectable	No
Wattage Selectable	No
Finish Family	Silver
Additional Info	Input Wattage: 3.14W; Output Wattage: 0.5W; Energy Used in Maintenance Mode: 3.14W
Amps	0.026/0.011A
Has Camera	No
IOT Enabled	No
Lens Finish	Mirrored
Lens Material	Acrylic
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

Dimmable	Non-Dimmable
Operating Frequency	60Hz
Operating Temp	+50F to +104F (+10C to +40C)
Volts	120V/277V
Watts	3.14W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	SILVER
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Recessed Ceiling/Wall

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923670268
Case Cube	1.3851
Case Height	9.45
Case Length	14.96
Case Quantity	3
Case UPC	10045923670265
Case Weight	17.2
Case Width	16.93
EA Cube	0.3865
EA Height	8.66
EA Length	16.34
EA Quantity	1
EA Weight	5.62
EA Width	4.72
Pack Type	Box
Web Height	11.0
Web Length	4.0
Web Width	15.75

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	ULus - Certified, ULus - Listed
California Ban	Lawful for sale
DLC Approved	No
Title 20	Yes
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026