Project / Job Name:

Location:

Fixture Type:

Notes:

65-1251 - 25/20/15 Watt LED Flood Light; 3K/4K/5K CCT; NEMA 4; Black Finish; 120-347 Volt

GENERAL

Company	NUVO
EA Height	5.2
EA Width	5.2
EA Length	8.03
Bulb Included	Integrated
Material	Die-cast Aluminum
Fixture Type	Flood Light
Product Notes	Default Wattage: 25W; 4Vx4H/5Vx5H/6Vx6H Beam Selectable
Status	Active
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	<20%
Wire Color	Black
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Black
Amps	0.210-0.070/0.170-0.060/0.130-0.040A
Mounting Diameter	4.5
Integrated Features	Integrated Photocell
Lens Material	Polycarbonate (PC)
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	150W-200W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	40/60/75
Color Temp	Soft White to Natural Light
CRI	70+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40F to +113F (-40C to +45C)
HID Equivalent	100W-150W
Lumens	3000L/2400L/1800L
Volts	120V-347V
Watts	25W/20W/15W
Max Lumens	3000L

PHYSICAL

Lamp Base	Integrated
Finish	BLACK
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923413513
Case Cube	2.3462
Case Height	11.22
Case Length	21.65
Case Quantity	16
Case UPC	10045923413510
Case Weight	26.75
Case Width	16.69
EA Cube	0.1257
EA Height	5.2
EA Length	8.03
EA Quantity	1
EA Weight	1.98
EA Width	5.2
Web Height	4.92
Web Length	7.71
Web Width	4.82

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-0SG3L3
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026