RoHS COMPLIANT

REVISION INFORMATION		
Rev.	Rev. Date	Brief Description

PID # :	48213	48214	48215	48216	48217	48218
LENGTH (L)	3.3ft(39.4”)	6.6ft(78.7”)	9.8ft(118”)	16.4ft(196.9”)	32.8ft(393.7”)	49.2ft(590.6”)



Length Tolerance:
+50mm/-0(Length<1M);
+100mm/-0(1M≤Length≤10M);
+1%/-0(Length>10M).

Performance:
1. Insertion Loss: ≤0.5dB.
2. Return Loss: ≥26dB.
3. Polarity: Type A

PID	Description
48213	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 1m
48214	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 2m
48215	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 3m
48216	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 5m
48217	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 10m
48218	Monoprice Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua 15m

NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT
		12C MTP/UPC Female, Standard Loss MM Connector / Aqua Housing: Black Boot	2	
		OD:3.0mm,Multimode 50/125 OM4,12F,Fiber Optic Cable OFNP Color:Aqua	1	

MONOPRICE

DESCRIPTION :
Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-12 UPC Female to MTP®-12 UPC Female 12-Fiber OFNP Type A Aqua

PID # : 48213, 48214, 48215, 48216, 48217, 48218

DATE :

UNIT : IN / FT

FILE NAME: