General duty switches

Plug fuse and special application types

Features

- Compact size
- Visible blade, double-break switching action
- Quick-make, quick-break operating mechanism
- Highly visible ON/OFF indicators
- Padlock-off handle feature
- Door padlock provision
- Bondable neutral (where indicated)
- Lugs suitable for copper or aluminum wire
- 30A cartridge fuse switches rated 100,000 AC with Class R fuses



Ampere rating	Indoor - Type 1 Catalog number	Ship. Wt. (lbs) Pkg. of 10	Outdoor - Type 3R Catalog number	Ship. wgt.*[1]	Horsepower rating [1] 1-Phase, 2-Wire Std.	Max
120/240 Volt Fusible (Plug Fuse Type) 10,000 AIC Max						
1-Pole and Solid Neutral [2]						**120 Volt – 1-Phase, 2-Wire**
30	LF111N	31	LF111NR	35	½	2
2-Pole and No Neutral						**120/240V – 1-Phase, 2-Wire**
30	—	—	Use 2-Pole and solid neutral			
2-Pole and Solid Neutral [2]						**120/240V – 1-Phase, 2-Wire**
30	LF211N	37	LF211NR	35	1 ½	3
240 Volt Non-Fusible						
2-Pole Special Application Switch		**1 or 2-Pole – No Fuse**				**240 Volt – 1-Phase, 2-Wire**
30	—	—	LNF221R [5]	35	1.5	3
60	—	—	LNF222RA[3]	30	—	10
60	—	—	LNF222RL[5]	40	3	10

Selection Information – Fused/Non-fused pullouts

Ampere rating	Number of poles	Number of blades	Number of fuses	Catalog number	Ship. Wt. (lbs) Pkg. of 10	Dimensions (inches) Height	Width	Depth
Fused Pullout – 1-Phase, 2-Wire[3] 10,000 AIC Max								**240 Volts AC**
30 [6]	2	2	2	WF2030	21 [7]	9 1/8	5 5/32	3 7/16
60 [4]	2	2	2	WF2060	5	9 1/8	5 5/32	3 7/16
Non-Fused Pullout – 1-Phase, 2-Wire [4]								**240 Volts AC**
60	2	2	—	WN2060	15 [7]	7 3/8	5 5/32	3 7/16

1) Dual horsepower ratings:
Std. – applies when non-time delay plug fuses are installed.
Max – applies when time-delay plug fuses are installed.
2) Has service entrance label.
UL Listed as "Enclosed Switches" (suitable for use as service equipment where indicated) under File #E4776.
(NEMA) — Type G.D.
Federal Spec. — W-S-865C — type LD or type NDS
3) Bottom cable entry and exit only. No hub provision supplied. Ground lug is included and factory installed.
4) Max. horsepower rating – 10.
5) Legacy style, oversize enclosure. Ground lug is included and factory installed.
6) Max. horsepower rating – 3.
7) Package of 6.