Recessed luminaire TUBELED_40 II Integrated, 395 mm x 74 mm x 3 mm (15,55“ x 2,91“ x 0,12“)

LED recessed luminaire

Product-Nr.	151110-01
EAN:	4260556623955
Model:	TUBELED_40 II Integrated



TUBELED_40 II Integrated 151110-01
TUBELED_40 II Integrated RGB-W 151190-01

Order number:	151110-01
Model:	TUBELED_40 II Integrated
Type:	LED recessed luminaire
Illuminant:	SMD LED
Power consumption:	~16,4 W
Lamp luminous flux:	2838 lm
Lamp luminous efficiency:	~173 lm/W
Light distribution:	Light Forming Technolology
Light colour:	5700K 3-step MacAdam
Colour rendering (Ra):	>85
Supply voltage:	24V DC ± 10%
Connection (connector):	M12 A-coded
Degree of protection:	IP67/IP69K
Class of protection:	III
Glare control:	diffused safety glass
Beam angle (optics):	100°
Operating temperature:	-30 °C - +60 °C (-22 °F - 140 °F)
Storage temperature:	-30 °C - +80 °C (-22 °F - 176 °F)
Lamps lifetime:	> 100,000 h (L80/B10)
Vibration resistance:	At 10 to 55 Hz (amplitude 0.35 mm (~0,01“))
Shock resistance:	Up to 50 g (~2 oz)
Housing material:	Aluminium
Cover material:	tempered glass, 4 mm (0,16“)
Height [B] x Width [C]:	32 mm x 74 mm (~1.26" x ~2.91"), aperture 3 mm (~0.12") built-up
Length [A]:	395 mm (~15,55“)
Weight (net):	700 g (~25 oz)
Gross weight:	950 g (~34 oz)
Risk group (DIN EN 62471):	Free group
Markings:	CE, UKCA, ETL Listed (5003529), D mark
Dimmable:	Optional via accessories
Made in:	Germany

LED2WORK GmbH | Stuttgarter Straße 13 A | 75179 Pforzheim | Germany
T: +49 7231 44920-00 | info@led2work.com | www.led2work.com |
Shop.led2work.com