



KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT

DESCRIPTION

2' x 2' Backlit LED Panel Light | 30W | 120-277V Input | 0-10V Dimming



10 YEAR LIMITED WARRANTY

PRODUCT FEATURES

- Aluminum frame featuring stepped-edge design detail and gloss white paint for improved aesthetics
- Backlit style design; fits standard T-grid ceilings
- Suitable for recessed- or surface-mount (with optional accessories)*
- Construction features precise optical lenses over each individual LED, offering optimal light diffusion and consistent surface illumination, with no risk of yellowing over product lifetime
- LED chip lifetime: L70 >100,000 hours @ 25°C/77°F ambient fixture temperature
- Suitable for damp locations
- Powered by Keystone 0-10V dimmable LED driver with built-in junction box
- Compatible with Keystone SmartSafe LED emergency backup
- Over 50% energy savings compared to traditional fluorescent troffers
- Operating temperature range: -20°C/-4°F to 40°C/104°F
- Available with Keystone's Smart Loop Bluetooth™ mesh wireless system, with features such as high-end trim, grouping, occupancy/vacancy sensing, and scheduling.

** For use in non-fire rated installations only*

PERFORMANCE SPECIFICATIONS DETAILED

Catalog Number	Selectable Wattage	Selectable CCT	Lumens	Efficacy	Input Voltage	CRI	Power Factor	UGR	Lifetime
KT-BPLED30-22-835-VDIM-P /G2	30W	3500K	3,750	125 lm/W	120-277V	>80	>0.9	<19	50,000hrs
KT-BPLED30-22-840-VDIM-P /G2	30W	4000K	3,750	125 lm/W	120-277V	>80	>0.9	<19	50,000hrs
KT-BPLED30-22-850-VDIM-P /G2	30W	5000K	3,750	135 lm/W	120-277V	>80	>0.9	<19	50,000hrs




KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT


PHOTOMETRIC SPECIFICATIONS (KT-BPLED30-22-8XX-VDIM-P /G2)

ISOCANDELA PLOT




- Cd: 1,154, 90%
 - Cd: 961, 75%
 - Cd: 769, 60%
 - Cd: 641, 50%
 - Cd: 513, 40%
 - Cd: 385, 30%
 - Cd: 256, 20%
 - Cd: 128, 10%
- Point of Max Cd: 1,281.9

POLAR CANDELA DISTRIBUTION



- -90° H
- -45° H
- -67.5° H
- -0° H
- -22.5° H

ILLUMINANCE AT A DISTANCE



ZONAL LUMEN SUMMARY


Zone	Lumens	% Luminaire
0-30	1,001.3	26.9%
0-40	1,646.7	44.2%
0-60	2,933.8	78.7%
60-90	792.5	21.3%
70-100	326.7	8.8%
90-120	0.0	0%
0-90	3,726.2	100%
90-180	0.0	0%
0-180	3,726.3	100%

KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT

PHYSICAL SPECIFICATIONS

KT-BPLED30-22-8XX-VDIM-P /G2




KT-BPLED30-24-8XX-VDIM-P /G2	
L (Length)	23.74"
W (Width)	23.74"
H (Height)	1.37"

WEIGHT

Catalog Number	Fixture Weight	Carton Weight
KT-BPLED30-22-8XX-VDIM-P /G2	6.20 lbs	12.40 lbs

EXPLODED VIEW CONSTRUCTION FEATURES



KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT

ACCESSORIES

SENSORS/CONTROLLERS

Factory-Installable OR Field-Installable (field-installable purchased separately)

✓	Suffix*	Catalog Number	Description	UPC	Easy Code
	/FC1-PIR	KTSL-FC1-UV-KO-PIR	Bluetooth mesh wireless fixture controller for SmartLoop system with remote mount PIR motion sensor with daylight harvesting and high-end trim; 120-277V; 3A max load with 0-10V dimming	843654129259	MGZ-59



Smart Loop PIR Sensor
KTSL-FC1-UV-KO-PIR

Note: Keystone SmartLoop is a DLC Qualified Network Lighting Control solution, offering advanced functions such as complete wireless control, zoning, high-end trim, occupancy/vacancy sensing, scene setting, and scheduling. To learn more about SmartLoop, please visit <http://www.keystonetech.com/smartloop>.

* For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).

CORD SETS

Factory-Installable OR Field-Installable (field-installable purchased separately)

✓	Suffix*	Catalog Number	Description	UPC	Easy Code
	/515P-6	KT-CS-515P-6-18/3	Cord set for high bay; 125V NEMA 5-15P; straight blade plug; 6' SJTOW cable; 18/3 wire	843654140124	UKH-26
	/NP-10	KT-CS-NP-10-16/3	Cord for high bays; no plug; inners 1/2" strip on both ends; 10' SJTOW cable; 16/3 wire	843654140193	YOH-90
	/NP-6	KT-CS-NP-6-16/3	Cord for high bays; no plug; inners 1/2" strip on both ends; 6' SJTOW cable; 16/3 wire	843654140216	HUB-73
	/NP-15	KT-CS-NP-15-16/3	Cord for high bays; no plug; inners 1/2" strip on both ends; 15' SJTOW cable; 16/3 wire	843654140209	EYD-18
	/MC13	KT-MC-NP-1-18/3	Metal clad cable for fixtures, No Plug, 1' long, 18/3 wire (L,N,G)	843654139777	AYT-71
	/MC63	KT-MC-NP-6-18/3	Metal clad cable for fixtures. No Plug, 6' long, 18/3 wire (L,N,G)	843654134505	EYP-82
	/MC65	KT-MC-NP-6-18/5	Metal clad cable for fixtures. No Plug, 6' long, 18/5 wire (L,N,G, LV)	843654134512	CBU-56
	/MC66	KT-MC-NP-6-18/6	Metal clad cable for fixtures. No Plug, 6' long, 18/6 wire (L,S,N,G, LV)	843654164229	KFF-99

* For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).
Note: For cord sets not listed here, please contact your Keystone sales rep.

(Accessories continued on next page)



KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT

ACCESSORIES (continued)

EMERGENCY BACKUP

Factory-Installable OR Field-Installable (field-installable purchased separately)

✓	Suffix*	Catalog Number	Description	UPC	Easy Code
	/EM5 [†]	KT-EMRG-LED-5C-500-EN /DF	5W, 500 lumen Smart Safe emergency backup with dual flex cables	843654132433	RAR-74
	/EM12 [†]	KT-EMRG-LED-12C-1200-EN /DF	12W, 1200 lumen Smart Safe emergency backup with dual flex cables	890949019900	YCV-23




5W, 500 lumen Battery Backup
KT-EMRG-LED-5C-500-EN /DF

12W, 1200 lumen Battery Backup
KT-EMRG-LED-12C-1200-EN /DF

* For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).
[†] Factory installation of emergency backup units will automatically include any relevant mounting bracket.

Field-Installable / Field-Use ONLY (purchased separately)

Catalog Number	Description	UPC	Easy Code
KT-BPLED-EM-22/4-KIT	Emergency LED backup mounting bracket kit for LED high bay fixtures	843654128047	EIG-03



Emergency Backup Mounting Bracket
KT-BPLED-EM-22/4-KIT

(Accessories continued on next page)

KT-BPLED30-22-8XX-VDIM-P /G2


BACKLIT LED PANEL LIGHT

ACCESSORIES (continued)

MOUNTS AND BRACKETS

Factory-Installable OR Field-Installable (field-installable purchased separately)

✓	Suffix*	Catalog Number	Description	UPC	Easy Code
	/JBOX	KT-BPLED-JBOX-2	Larger J-Box add-on for LED backlit panels	843654128245	BMV-31



* For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).

Field-Installable / Field-Use ONLY (purchased separately)


Catalog Number	Description	UPC	Easy Code
KT-BPLED-SM-24-KIT /G2	Surface Mount kit for 2 x 4 backlit panels	843654134543	CGY-52



STEP-DOWN TRANSFORMERS

Factory-Installable OR Field-Installable (field-installable purchased separately)

✓	Suffix*	Catalog Number	Description	UPC	Easy Code
	/480†‡	KTAT-250-480-277 /SF	Fully enclosed, single flex step-down transformer for LED high bay fixtures (250VA or lower)	843654102931	XIM-17



* For factory installation of accessory, add suffix to fixture part number (see ordering examples and instructions on last page of spec sheet).

† Factory installation of step-down transformer units will automatically include any relevant mounting bracket.

‡ Step-down transformers cannot be ordered in conjunction with standard SJTOW cord set options (contact Keystone sales rep for available custom options if needed).



KT-BPLED30-22-8XX-VDIM-P /G2

BACKLIT LED PANEL LIGHT

ORDERING INFORMATION

Catalog Number	Carton QTY	UPC	Easy Code
KT-BPLED30-22-835-VDIM-P /G2	2	843654146744	YPF-06
KT-BPLED30-22-840-VDIM-P /G2	2	843654146751	GDW-55
KT-BPLED30-22-850-VDIM-P /G2	2	843654146768	YYH-12

CATALOG NUMBER BREAKDOWN

KT-BPLED30-22-8XX-VDIM-P /G2

1	2	3	4	5	6	7	8	9	10
---	---	---	---	---	---	---	---	---	----

- | | |
|---|---|
| <ul style="list-style-type: none"> 1 Keystone Technologies 2 Backlit Panel Light LED Fixture 3 Wattage 4 2' x 2' Nominal Size 5 80 CRI | <ul style="list-style-type: none"> 6 Color Temperature 7 0-10V Dimming 8 Premium DLC 9 Second Generation 10 Additional Ordering Options (See details and examples below) |
|---|---|


10 Additional Ordering Options

(blank)	No sensor included
/FC1-PIR	Occupancy sensor included

ORDERING EXAMPLES


FIXTURE WITH MULTIPLE FACTORY-INSTALLED ACCESSORIES*

KT-BPLED30-22-840-VDIM-P /G2/FC1-PIR/L715P-6/EM5/JBOX




FIXTURE WITH MULTIPLE FACTORY-INSTALLED ACCESSORIES*

KT-BPLED30-22-840-VDIM-P /G2/FC1-PIR/EM5/JBOX/480




FIXTURE WITH TWO FACTORY-INSTALLED ACCESSORIES*

KT-BPLED30-22-840-VDIM-P /G2/FC1-PIR/JBOX




FIXTURE WITH SINGLE FACTORY-INSTALLED ACCESSORY

KT-BPLED30-22-840-VDIM-P /G2/FC1-PIR



FIXTURE WITH NO FACTORY-INSTALLED ACCESSORIES

KT-BPLED30-22-840-VDIM-P /G2



KEYSTONE FIXTURE

Catalog Number
KT-BPLED30-22-840-VDIM-P /G2

SENSORS

✓ Suffix	Catalog Number
✓ /FC1-PIR	KTSL-FC1-UV-KO-PIR

CORD SETS

✓ Suffix	Catalog Number
✓ /L715P-6	KT-CS-L715P-6-16/3

EMERGENCY BACKUP

✓ Suffix	Catalog Number
✓ /EM5	KT-EMRG-LED-5C-500-EN /DF

MOUNTS AND BRACKETS

✓ Suffix	Catalog Number
✓ /JBOX	KT-BPLED-JBOX-2

STEP-DOWN TRANSFORMERS

✓ Suffix	Catalog Number
✓ /480	KTAT-250-480-277 /SF

* When ordering more than one factory-installed accessory, use multiple suffixes as shown in the ordering examples above.
 Note: All accessories can also be ordered separately for field installation using just their regular Catalog Number, UPC, or Easy Code.

Note: Step-down transformers cannot be ordered in conjunction with standard SJTOW cord set options (contact Keystone sales rep for available custom options if needed).