



EAN:	4013288228857	Size:	157x11x11 mm
Part number:	05006542001	Weight:	30 g
Article number:	Kraftform Kompakt VDE 67 iS TiE	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE interchangeable blade for TORX® screws
- Reduced shaft diameter and integrated insulation protection
- Insulated, individually tested as per IEC 60900
- 9 mm hex drive with with entry chamfer
- Black Point tip for enhanced corrosion protection and an exact fit
- Take it easy tool finder: colour coding by profile and laser-engraved size indication
- Hexagonal anti-roll feature against rolling away

VDE blade for the Kraftform Kompakt handle/interchangeable blade system. Lightning-fast blade changes without special tools. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Reduced blade diameter with integrated protective insulation, low-lying screw and spring elements can be easily reached and operated. The Wera Black Point tip offers fitting accuracy and optimised corrosion protection. With Take it easy tool finder: colour coding by profile and laser-engraved size indication. The hexagon anti-roll protection avoids blades from rolling away unintentionally.



Web link
<https://www.wera.de/en/05006542001>

Wera - Kraftform Kompakt VDE 67 iS TiE
05006542001 - 4013288228857

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Individually tested



Testing the tool for dielectric strength at 10,000 volt gives the user the peace of mind that their tool has been tested for its most important property, insulation. Wera VDE tools are subjected to this test piece by piece which guarantees safe working at up to 1,000 volt.

Kraftform Kompakt VDE blades




The 157 mm length blades are suitable for Wera Kraftform bitholding screwdrivers 7400 VDE, 837 i RA, 827 T i and 817 VDE.

The handle/blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

VDE interchangeable blade with reduced shaft diameter (iS)




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Take it easy




The Kraftform Kompakt VDE blades are equipped with the Take it easy tool finder. Colour coding by profile and laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Fast turning



The palm of your hand is comfortably supported on the rounded shape of the rear end of the blades. This allows quick spinning of the blade and accelerates the screwdriving process.

Further versions in this product family:

				
05006540001	TX 15		157	6 3/16"
05006541001	TX 20		157	6 3/16"
05006542001	TX 25		157	6 3/16"

Web link

<https://www.wera.de/en/05006542001>

Wera - Kraftform Kompakt VDE 67 iS TiE
05006542001 - 4013288228857

Wera Werkzeuge GmbH
Korzer Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Web link

<https://www.wera.de/en/05006542001>

Wera - Kraftform Kompakt VDE 67 iS TiE
05006542001 - 4013288228857

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de