Project / Job Name:

Location:

Fixture Type:

Notes:

65-718 - LED Security Light; Dual Head; Bronze Finish; 4000K

GENERAL

Company	NUVO
EA Height	10.04
EA Width	6.89
EA Length	9.45
Bulb Included	Integrated
Extends (in)	8.8
Material	Die-cast Aluminum
Fixture Type	Security Lighting
Product Notes	Adjustable Angle from 0 to 90 degrees
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Bronze
Amps	0.200-0.072A
Has Camera	No
IOT Enabled	No
Lens Finish	Frost
Lens Material	Glass
Photo Cell	No Photocell
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	125W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	4000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	50
Color Temp	Cool White
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-22F to +122F (-30C to +50C)
HID Equivalent	70W
Lumens	1900L
Volts	120V-277V
Watts	20W
Connection	Direct Wired

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Ceiling/Wall

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923629563
Case Cube	2.571
Case Height	11.02
Case Length	39.37
Case Quantity	5
Case UPC	10045923629560
Case Weight	12.68
Case Width	10.24
EA Cube	0.3783
EA Height	10.04
EA Length	9.45
EA Quantity	1
EA Weight	2.54
EA Width	6.89
Pack Type	Color Box
Web Height	4.54
Web Width	8.16

COMPLIANCE

ADA Compliant	No
CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026