RoHS COMPLIANT

REVISION INFORMATION		
Rev.	Rev. Date	Brief Description

PID # :	47916	47917	47918
LENGTH (L)	3ft (36”)	4ft (48”)	6ft (72”)







PIN Assignment





NOTES:

1. Test Condition:
   (1) 100% OPEN & SHORT TEST;
   (2) Insulation Resistance: DC300V 5MΩ(Min) ;
   (3) Conducter Resistance: 5Ω/Max.
   (4) Hi-Pot:DC 300V/0.1s.
2. The product is ROHS compliant.
3. HDTV-DVD TEST:4K@60HZ
4. Prop 65

NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT
7	SHELL	HDMI Shell, aluminium alloy, Gray, with “IIIP & HDMI 4K” LOGO	2	PCS
6	DUST CAP	HDMI Dust Cap, transparent	2	PCS
5	OVER MODEL	45P Black PVC	20	g
4	COPPER FOIL	Copper foil, W4.5*L30MM (for connector)	2	PCS
3	INTERNAL MODEL	PE	10	g
2	CONNECTOR	HDMI 2.0V AM connector, gold plated, with shielding case	2	PCS
1	CABLE	HDMI UL20276 CABLE 34AWG[(7/0.06TC+FPE0.5)*2C+1/0.16TC+HDPE0.3+AL+MYLAR]*5P+(7/0.06TC+HDPE0.45)*4C+AL+D+B96#/0.12AL-MG+CL2 Black PVC OD=4.8±0.2mm	1	PCS

MONOPRICE

DESCRIPTION :
Monoprice™ 4K Certified High Speed Slim HDMI Cable - 4K60Hz, 18Gbps, HDR, CL2 Rated, Gold-Plated, Black

PID # : 47916, 47917, 47918

DATE : 2025/05/13	UNIT : IN/MM/FT	FILE NAME: 47916-47918_tech_drawing