Project / Job Name:

Location:

Fixture Type:

Notes:

**67-512** - Running Man Green Combo Exit Sign/Emergency Light; 120/347V; 90min backup; Single/Dual Face; Universal Mounting; Thermoplastic; Remote-Capable; White Finish

## GENERAL

| | |
|---|---|
| Company | SATCO |
| EA Height | 9.29 |
| EA Width | 2.56 |
| EA Length | 13.86 |
| Bulb Included | Integrated |
| Extends (in) | 2.58 |
| Material | Thermo Plastic |
| Fixture Type | Exit Sign |
| Product Notes | Ni-MH Battery; 90 minute discharge time; Remote Compatible; 24 Hour Recharge Time |
| Status | Active |
| Style | Utility |
| Total Harmonic Distortion | 35%-45% |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | White |
| Additional Info | Remote Capable Power Rating: 3.6V/4W |
| Amps | 0.060/0.021A |
| Has Camera | No |
| IOT Enabled | No |
| Lens Finish | Clear |
| Lens Material | Polycarbonate (PC) |
| Power Factor | 0.8 |
| SDS Class | LED_Fixture |
| Sloped Ceiling Compatible | No |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 5700K |
| Dimmable | Non-Dimmable |
| CRI | 80+ |
| Operating Frequency | 50/60Hz |
| Operating Temp | +50F to +104F (+10C to +40C) |
| Lumens | 150L |
| Volts | 120V/347V |
| Watts | 7.2W |
| Battery Chemistry | Ni-MH |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | WHITE |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Mounting Procedure | Universal |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 2-Years |

## PACKAGING

| | |
|---|---|
| UPC | 045923675607 |
| Case Cube | 1.3663 |
| Case Height | 10.04 |
| Case Length | 16.14 |
| Case Quantity | 6 |
| Case UPC | 10045923675604 |
| Case Weight | 25.42 |
| Case Width | 14.57 |
| EA Cube | 0.1908 |
| EA Height | 9.29 |
| EA Length | 13.86 |
| EA Quantity | 1 |
| EA Weight | 3.75 |
| EA Width | 2.56 |
| Pack Type | Box |

## COMPLIANCE

| | |
|---|---|
| CA Prop 65 | Lead |
| IP Rating | IP40 |
| Location Rating | Damp |
| ROHS Compliant | Yes |
| Safety Listing | CSA - Listed |
| California Ban | Non-Compliant |
| Title 20 | No |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026