

Designed for handheld tools and high durability.

TEGERA® PRO 9205

Learn more

EXTRA PROTECTION FOR PALM AND KNUCKLES

This synthetic leather glove has extra protection for the knuckles and a padded inner hand which makes it perfect for working with handheld tools. The Macrothan®+ provides both durability and breathability for extra comfort.

CHARACTERISTICS

- Flexible
- Durable
- Perfect fit
- Very breathable
- Extra comfortable

FUNCTIONS

- Chrome free
- Reinforced index finger
- Reinforced palm
- Reinforced seams
- Reinforced fingertips
- Reinforced fingers and thumb
- Padded palm
- Pre-curved fingers
- Specially designed thumb
- Knuckle protection
- Ergonomically shaped
- Reflector
- Soft
- Specially designed details

MACROTHAN®+

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Chrome allergy, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Dark environments, Dry environments, Dirty environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, HVAC installation, Construction, Soil preparation, Engineering, Transport work, Machine driving, Warehouse work, Airport work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Accommodation and food service (HoReCa), Facility management services, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Mining and quarrying, Warehousing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Heavy duty gloves
CATEGORY Cat. II
COLLECTION Pro
PALM MATERIAL Macrothan®
BACK MATERIAL Polyester
LINING Unlined
LENGTH 200-240 mm
DEXTERITY 5
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hook with hangtag
FASTENING Elasticated 360°
OUTER MATERIAL SPECIFICATION Polyurethane, Polyester

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2132X

EN 407:2020 (No flame protection) X1XXXX

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
7	S	9205-7	7392626012462
8	M	9205-8	7392626012479
9	L	9205-9	7392626012486
10	XL	9205-10	7392626012493
11	XXL	9205-11	7392626012509

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.