EXTRAFLEX® PLUS+

14-300
SPECIFICATION SHEET

TOUCH SCREEN



ANSI/ISEA 105

A3
4 4

EN388

4X42C

SPECIFICATIONS:

- **Liner Materials:** 18g Blue Extraflex® Plus A3 Liner
- **Coating Materials:** Black HCT® MicroFoam Nitrile
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XS-2X

Armor Guys Reference Number: 14-300

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	2X
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	6DZ	6DZ	6DZ	6DZ	6DZ	6DZ
CASE WEIGHT	15.07 lbs	16.39 lbs	16.83 lbs	18.59 lbs	19.03 lbs	20.13 lbs

PERFORMANCE LEVEL:

EN388: 4X42C

ABRASION	0	1	2	3	**4**	5	X
CUT	0	1	2	3	4	5	**X**
TEAR	0	1	2	3	**4**	5	X
PUNCTURE	0	1	**2**	3	4	5	X
CUT TDM TEST	A	B	**C**	D	E	F	

ATTRIBUTES:

- 18g Blue Extraflex® Plus A3 Liner
- Black HCT® MicroFoam Nitrile Palm Coating

FEATURES:

- Silicone free
- Reinforced thumb crotch for extended wear
- Touchscreen compatible
- MicroFoam coating ensures excellent oil grip

APPLICATIONS:

- Automotive manufacturing
- Light manufacturing
- Sheet metal handling
- Metal stamping
- Construction

CATEGORY:

- **Extraflex® Plus**

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:

HCT
Hybrid Coating Technology

ARMOR GUYS