



TEGERA® PRO 9105

Learn more

DESIGNED FOR MAXIMUM FIT

This synthetic leather glove has a hook and loop closure for a more secure fit. The palm material is Microthan® for extra durability and the back material is nylon. It is suitable for fine assembly work in dry and slightly oily environments where a good grip and dexterity is essential.

CHARACTERISTICS

- Durable
- Excellent grip
- Extremely good fingertip sensitivity
- Extra flexible
- Perfect fit
- Extra comfortable

FUNCTIONS

- Ergonomically shaped
- Reflector
- Chrome free
- Reinforced index finger
- Reinforced seams
- Specially designed details
- Reinforced fingertips
- Pre-curved fingers
- Specially designed thumb

MICROTHAN®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Dark environments, Dry environments, Clean environments, Dirty environments, Slippery environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Installation work, Machine operating, HVAC installation, Machine driving, Warehouse work, Airport work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Glass, ceramics and construction materials, Metal manufacturing and fabrication, Transport equipment manufacturing, Agriculture, forestry and fishing, Facility management services, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Electronics manufacturing, Mining and quarrying, Warehousing, Pulp and paper, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Precision work gloves
CATEGORY Cat. II
COLLECTION Pro
PALM MATERIAL Microthan®
BACK MATERIAL Polyester
LINING Unlined
LENGTH 216-253 mm
DEXTERITY 5
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hook with hangtag
FASTENING Hook-and-loop
OUTER MATERIAL SPECIFICATION Polyurethane, Nylon, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC
EN 388:2016+A1:2018 1111X

ANSI 2 ABR

FEATURES

Precision work

SIZE		ARTICLE NUMBER	EAN
5	XXS	9105-5	7392626033139
6	XS	9105-6	7392626012097
7	S	9105-7	7392626012110
8	M	9105-8	7392626012127
9	L	9105-9	7392626012134
10	XL	9105-10	7392626012141
11	XXL	9105-11	7392626012158
12	3XL	9105-12	7392626025332
13	4XL	9105-13	7392626031999

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.