



EAN:	4013288095428	Size:	70x25x5 mm
Part number:	05027206001	Weight:	10 g
Article number:	950 BM	Country of origin:	CZ
		Customs tariff number:	82041100

- L-keys for hexagonal socket screws
- Hexagonal socket wrench with Hex-Plus advantage for a longer screw life
- Laser-engraved and thereby wear-resistant size markings
- BlackLaser for high corrosion protection and long service life
- Metric

High quality L-keys for hexagonal socket screws. Hex-Plus offers a larger contact surface within the screw head. This reduces the notching effects to a minimum and almost completely eliminates the risk of destroying the screw recess. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. Wear-resistant size markings for rapid accessing.

Web link
<https://www.wera.de/en/05027206001>

Wera - 950 BM
05027206001 - 4013288095428

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

L-Keys



We questioned the classic L-key design, since all too often the screw head recess is rounded out, meaning screws can no longer be tightened or loosened - and so the user finds the L-key slipping out of the recess. Wera Hex-Plus tools have a larger contact surface in the screw head. The notching effects are reduced and thereby the deformation of the screws. At the same time, as much as 20 % more torque can be applied.

Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Size identification



The size of each L-keys has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

Surface protection



L-keys with BlackLaser surface treatment for outstanding surface protection and long service life. High corrosion protection.

Web link
<https://www.wera.de/en/05027206001>

Wera - 950 BM
 05027206001 - 4013288095428

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Further versions in this product family:

					
	mm	mm	mm	inch	inch
05027201001 ¹⁾	1.5	45	14	1 3/4"	9/16"
05027202001	2.0	50	16	2"	5/8"
05027203001	2.5	56	18	2 7/32"	23/32"
05027204001	3.0	63	20	2 1/2"	25/32"
05027205001	3.5	66	23	2 5/8"	29/32"
05027206001	4.0	70	25	2 3/4"	1"
05027207001	4.5	75	26	3"	1 1/32"
05027208001	5.0	80	28	3 1/8"	1 3/32"
05027209001	6.0	90	32	3 1/2"	1 1/4"
05027210001	7.0	95	34	3 3/4"	1 5/16"
05027211001	8.0	100	36	4"	1 7/16"
05027213001	9.0	106	38	4 11/64"	1 1/2"
05027212001	10.0	112	40	4 7/16"	1 9/16"
05027214001	11.0	120	43	4 23/32"	1 11/16"
05027215001	12.0	125	45	5"	1 49/64"

1) Regular hexagon

Web link

<https://www.wera.de/en/05027206001>

Wera - 950 BM

05027206001 - 4013288095428

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de