marathon®

Inverter (Vector) Duty Motors

Model No: LM33492
Catalog No: LM33492

Inverter (Vector) Duty Motor, 3 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 184TC Frame, TENV

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: LM33492, Catalog No: LM33492 Inverter (Vector) Duty Motor, 3 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 184TC Frame, TENV

Nameplate Specifications

Phase	**3**	Output HP	**3 Hp**
Output KW	**2.2 kW**	Voltage	**230/460 V**
Speed	**1755 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.00**	Frame	**184TC**
Enclosure	**Totally Enclosed Non Ventilated**	Thermal Protection	**Thermostat**
Efficiency	**87.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**8.2/4.1 A**
Power Factor	**78.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**INV**
KVA Code	**N**	Drive End Bearing Size	**6207**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Squirrel Cage Inverter Duty**	Starting Method	**Inverter Only**
Poles	**4**	Rotation	**Selective Clockwise**
Resistance Main	**0 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Aluminum**
Shaft Type	**T**	Overall Length	**15.88 in**
Frame Length	**9.5 in**	Shaft Diameter	**1 1/8 in**
Shaft Extension	**2.75 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 100:1**		

Drawings

Connection Drawing	**005010.20LN**	Outline Drawing	**036143LN-950**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 14/10/2026