



jalas® ZENIT EVO 7178

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2022 S3L, SR, FO, SC

Learn more

MID CUT WITH EXTRA ANKLE SUPPORT

A mid-cut new designed lightweight safety shoe with extra ankle support, knitted textile upper and BOA® Fit System. Outstanding ergonomics, padded Memory foam and water repellency means day-long safety and comfort. An oil resistant RPU outer sole gives outstanding grip and a ventilated inner sole keeps feet cool. Features JALAS® aluminium toe cap, plasma-treated textile puncture protection and double impact protection zones in PORON® XRD®.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption
- Extremely light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Polstered shaft edge
- Ventilating insole
- BOA® Fit System
- Ankle support
- Water repellent
- Ergonomically shaped
- Conforms with IEC 61340-5-1 (ESD)

BOA DIALED IN. PRECISION FIT.

XRD PROTECTION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, All-year use, Environments with risk for outsole penetration, Dry environments, Clean environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Zenit Evo
UPPER MATERIAL Knitted textile
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL RPU outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.22 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2022
S3L, SR, FO, SC

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	7178-35	6408487525377
36	3	4	5	7178-36	6408487525414
37	4	5	6	7178-37	6408487525452
38	5	5.5	6.5	7178-38	6408487525490
39	6	6.5	7.5	7178-39	6408487525537
40	6.5	7.5	8.5	7178-40	6408487525575
41	7	8	9	7178-41	6408487525612
42	8	9	10	7178-42	6408487525650
43	9	9.5	11	7178-43	6408487525698
44	10	10.5	11.5	7178-44	6408487525735
45	10.5	11	12.5	7178-45	6408487525773
46	11	12	13	7178-46	6408487525810
47	12	13	14	7178-47	6408487525858
48	13	13.5	14.5	7178-48	6408487525896

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.