Project / Job Name:

Location:

Fixture Type:

Notes:

67-551 - Running Man Green Combo Edge Lit Exit Sign/Emergency Light; 120-347V; 2HR backup; Single/Dual Face; Premium Flush Recessed Mounting; High Output lamps; Brushed Aluminum Finish

GENERAL

Company	SATCO
EA Height	8.07
EA Width	6.77
EA Length	20.28
Bulb Included	Integrated
Material	Aluminum
Fixture Type	Exit Sign
Product Notes	Ni-Cad Battery; 120 minute discharge time; 24 Hour Recharge Time
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	120%-140%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Metallic
Amps	0.025-0.009A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Acrylic
Power Factor	0.55
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
Operating Frequency	50/60Hz
Operating Temp	+50F to +104F (+10C to +40C)
Lumens	260L
Volts	120V-347V
Watts	3W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	Brushed Aluminum
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Recessed Ceiling/Wall

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923675898
Case Cube	2.1828
Case Height	8.66
Case Length	20.87
Case Quantity	3
Case UPC	10045923675895
Case Weight	26.46
Case Width	20.87
EA Cube	0.6412
EA Height	8.07
EA Length	20.28
EA Quantity	1
EA Weight	7.28
EA Width	6.77
Pack Type	Box
Web Height	10.63
Web Width	19.74

COMPLIANCE

CA Prop 65	Lead
IP Rating	IP40
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	CSAus
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026