



**MCR
SAFETY**

22 Goggles Series

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety's 22 Series Goggles provide a wide, unobstructed field of vision and can be worn with most half-mask respirators. The 2220 features a perforated direct vented transparent PVC body that protects against impact and an elastic strap that is comfortable and flexible. Choose the best safety goggles, choose MCR Safety!



FEATURES:

- PVC body permits a comfortable fit over prescription eyewear
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- Exclusive Duramass® scratch resistant coating
- Adjustable elastic strap is latex free

TECHNICAL DATA FOR: 2220

Series	22	ANSI Z87+ Packaging	Yes White Inner Box
Category	Goggles		
Goggle Type	Direct Vented / Perforated		
Dielectric	Yes		
Scratch Resistant	Yes		
Frame Material	PVC		
Case Pack	144	Case Weight	27.981 lb.
Case Dimensions	15.354 x 13.386 x 25.591	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Goggle Type:
2120	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2220	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2220R	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2225	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

22
Goggles
Series
Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Goggle Type:
2225R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated
2225RB	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated
2230	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2230R	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2230RB	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2235	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2235R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2235RB	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2237	Clear	UV-AF Anti-Fog	Yes	90	Clear	Ventless
2237R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Ventless

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved