WORLD DRYER

WORLD DRYER

eXtremeAir® Series

Comfort and Efficiency are Hand in Hand



The eXtremeAir Series keeps dry times, energy usage, dimensions, and costs to a minimum.

Building owners can choose between the GXT or EXT. While both models blow the competition away in user comfort and energy efficiency, each has a slight edge over the other.

GXT features heat technology and dries hands two seconds faster, while the EXT saves 10 percent more energy between the two options.

Both hand dryers accommodate restrooms limited in space – requiring 43 percent less capacity than traditional models. Sound and speed can be adjusted to fit the environment, as well.

Whether you choose the GXT or EXT, you're making the right choice for restroom users and building efficiency goals.

COST PER 1,000 HAND DRYINGS	
EXT Series	$0.18
GXT Series	$0.42
Paper towels	$26.04

GXT

Fast Dry Time
Dries hands in as little as 10 seconds

Energy Efficieny
Uses up to 80% less energy than conventional hand dryers

Flexible
Adjusts sound and speed with dial

Universal Voltage
Accepts 110-240 V input

Compact Design
Utilizes 43% less space than older models

EXT

Fast Dry Time
Dries hands in as little as 12 seconds

Energy Efficieny
Uses up to 90% less energy than conventional hand dryers

Flexible
Adjusts sound and speed with easy dial adjustment


No Heat Technology
Reduces power consumption and supports multiple dryers on one circuit

Universal Voltage
Accepts 110-240 V input

Compact Design
Utilizes 43% less space than older models

A World of Features (and Difference)

Specifications





eXtremeAir GXT Hand Dryer

COVER MATERIAL/FINSH	ACTIVATION	MOUNTING	110-120 / 208 / 220-240 V	UNIT SIZE (HXWXD) INCH [MM]	SHIPPING SIZE (HXWXD) INCH [MM]	SHIPPING WEIGHT
Brushed S/S	Automatic	Surface	GXT9-SS	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
Steel White	Automatic	Surface	GXT9-M	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
Steel Black	Automatic	Surface	GXT9-BG	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
White ABS	Automatic	Surface	GXT9	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	9 lb / 4.1 kg

eXtremeAir EXT Hand Dryer

COVER MATERIAL/FINSH	ACTIVATION	MOUNTING	110-120 / 208 / 220-240 V	UNIT SIZE (HXWXD) INCH [MM]	SHIPPING SIZE (HXWXD) INCH [MM]	SHIPPING WEIGHT
Brushed S/S	Automatic	Surface	EXT7-SS	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
Steel White	Automatic	Surface	EXT7-M	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
Steel Black	Automatic	Surface	EXT7-BG	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	10 lb / 4.5 kg
White ABS	Automatic	Surface	EXT7	10.1" x 9.4" x 5.6" [257 x 239 x 142]	6.75" x 11.5" x 10.25" [171 x 292 x 260]	9 lb / 4.1 kg

COVER MATERIAL/FINISH	ACCESSORY	MODEL NUMBER	MOUNTING
Brushed S/S	ADA Wall Guard	ADA-WG	Surface
Brushed S/S	Recess Kit	ADA-RK	Recessed
Brushed S/S	Adaptor Plate	AP	Surface

	GXT	EXT
Volts	120-240	120-240
Watts	1500 - 800 (Adjustable)	500-300 (Adjustable)
Hz	60	60



Stainless Steel



Steel White Epoxy



Steel Black Epoxy



White ABS

Choose an eXtremeAir Series design for your restroom environment. World Dryer puts visionary products within arm's reach.

WORLD DRYER CORP. 340 County Line Road, Bensenville, IL 60106, 800.323.0701
Form No. 800-018-2, 11/19

WORLDDRYER.COM