RoHS COMPLIANT

REVISION INFORMATION		
Rev.	Rev. Date	Brief Description



Length Tolerance:
+50mm/-0(Length<1M);
+100mm/-0(1M≤Length≤10M);
+1%/-0(Length>10M).

Performance:
1. Insertion Loss: ≤0.35dB.
2. Return Loss: ≥26dB.
3. Polarity: Type B

PID	Description
48210	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-16 Elite UPC Female to MTP®-16 Elite UPC Female 16-Fiber OFNP Type B Magenta 3m
48211	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-16 Elite UPC Female to MTP®-16 Elite UPC Female 16-Fiber OFNP Type B Magenta 5m
48212	Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-16 Elite UPC Female to MTP®-16 Elite UPC Female 16-Fiber OFNP Type B Magenta 10m

NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT
2		16C MTP/UPC Female Elite MM Connector / Aqua Housing; Black Boot	2	
1		OD:3.0mm, Multimode 50/125 OM4, 16F, Fiber Optic Cable OFNP Color: Erika Violet	1	

MONOPRICE

DESCRIPTION :
Monoprice™ Multi-Mode OM4 Fiber Optic Cable – MTP®-16 Elite UPC Female to MTP®-16 Elite UPC Female 16-Fiber OFNP Type B Magenta

PID # : 48210, 48211, 48212

DATE :

UNIT : M / IN / MM

FILE NAME: