



EAN:	4013288094230	Size:	89x7x7 mm
Part number:	05059489001	Weight:	14 g
Article number:	800/4 Z	Country of origin:	CZ
		Customs tariff number:	82079030

- For slotted screws
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

Tough Wera bits for slotted screws, for universal use. 1/4" hexagonal, suitable for holders as per DIN ISO 1173-F 6.3.

Web link
<https://www.wera.de/en/05059489001>

Wera - 800/4 Z
05059489001 - 4013288094230

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Tough bits



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Web link

<https://www.wera.de/en/05059489001>

Wera - 800/4 Z
05059489001 - 4013288094230

Further versions in this product family:

					
	mm	mm	mm	inch	mm
05059305001	0.5	3.0	50	2"	3.0
05059466001	0.5	3.0	70	2 3/4"	3.0
05059307001	0.5	4.0	50	2"	4.0
05059310001	0.6	3.5	50	2"	3.5
05059472001	0.6	3.5	70	2 3/4"	3.5
05059450001	0.6	3.5	152	6"	3.5
05059315001	0.6	4.5	50	2"	4.5
05059489001	0.6	4.5	89	3 1/2"	4.5
05059320001	0.8	4.0	50	2"	4.0
05059478001	0.8	4.0	70	2 3/4"	4.0
05059480001	0.8	4.0	89	3 1/2"	4.0
05059451001	0.8	4.0	152	6"	4.0
05059325001	0.8	5.5	50	2"	5.5
05059330001	1.0	5.5	50	2"	5.5
05059486001	1.0	5.5	70	2 3/4"	5.5
05059488001	1.0	5.5	89	3 1/2"	5.5
05059452001	1.0	5.5	152	6"	5.5
05059335001	1.0	6.0	50	2"	6.0
05059337001	1.2	6.5	50	2"	6.2
05059492001	1.2	6.5	70	2 3/4"	6.2
05059490001	1.2	6.5	89	3 1/2"	6.2
05059453001	1.2	6.5	152	6"	6.2
05059340001	1.2	8.0	50	2"	8.0
05059496001	1.2	8.0	89	3 1/2"	8.0
05059345001	1.6	8.0	50	2"	8.0
05059500001	1.6	8.0	89	3 1/2"	8.0

Web link

<https://www.wera.de/en/05059489001>

Wera - 800/4 Z

05059489001 - 4013288094230

Wera Werkzeuge GmbH

Körzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de