6" Locking Slide Arm with Short Clevis

Item #7160-1160



This rugged motion attachment easily allows you to move the computer to the desired operating position from either the driver or passenger’s side. The slide arm features Slam and Lock technology that allows you to simply push the computer back to the retracted position and it will automatically lock into place, preventing unwanted movement when the vehicle is in motion. Its lower profile allows the driver to easily see the computer screen, while maintaining their line of sight to the road.

Weight

5.2 lbs. (3.08 kg)

Dimensions

Width: 7.2” (18.4 cm)
Height: 3.9” (9.9 cm)
Length: 9.4” (23.9 cm)

Features

- Entire motion attachment capable of rotating 360 degree with locking every 15 degrees
- Tilt capabilities: 45° forward
- Swivel capabilities: 360°

- The entire arm can rotate around 360° with locking points at every 15°
- Slide motion is up to 5.5 inches (13.97 cm) fore/aft
- To rotate the arm simply pull the front lever out, rotate to desired position and then release the lever
- Heavy duty, spring loaded steel, side pin was tested to 50,000+ cycles
- Can be mounted directly to a flat surface or on any Upper Pole, Center Pole, Low Profile Bracket, GJ console box via Smiley Face or 3-Bolt Hole pattern
- Heavy gauge steel construction for long-term durability
- Black powdercoat finish for maximum
- Limited Lifetime Warranty

Mounting plate hole patterns

- AMPS (4 hole rectangle shaped) - 3 locations, one turned 90 degrees
- NEC (3 hole triangle shaped)
- VESA 75mm
- Gamber-Johnson 2x4