

WFL SERIES RESIDENTIAL LIGHTING

WFL-113-PC-5B-52-MCT-WH-WH
52in 5-BLADE CEILING FAN AND LIGHT

MCT Multi Color Temperature (Selectable)


WESTGATE
THE FUTURE IS HERE...AND IT'S QUITE BRIGHT!

Customer Name: _____

Project Name: _____

Note: _____

Type: _____



16 1/4"(H) x 52"(W)

The WFL Ceiling Fan & Light is the perfect combination of style and functionality for any room. With its sleek and modern design, it adds a touch of elegance to your space while providing efficient cooling and illumination. Key features include:

- **Stylish Design:** The WFL Ceiling Fan & Light boasts a contemporary design that complements various interior styles, from classic to modern.
- **Efficient Cooling:** Enjoy a comfortable environment year-round with powerful fan blades that provide efficient air circulation and cooling.
- **Integrated Lighting:** Illuminate your room with the integrated light fixture, offering both brightness and energy efficiency.
- **Quiet Operation:** Experience quiet and smooth fan operation, perfect for bedrooms, living rooms, and more.

Features

- Metal Housing (White Finish) & Plywood Blades (White Finish)
- 5-Year Warranty
- Polycarbonate Lens

Technical Specifications

Electrical:

- Voltage: 120V AC 50/60Hz
- Wattage: 20
- Power Factor: >0.99
- Efficacy: 85 LPW

Mechanical:

- Metal Housing (White Finish) & Plywood Blades (White Finish)
- Motor: Reversible 3-Speed AC Motor with 80" Lead Wire. Includes (1) 6" Downrod
- Blades: 52" Sweep, 5-Blade Reversible Configurations
- Pull Chain: Two 12" Pull Chains
- Blade Pitch Angle: 13°
- Maximum Ambient Temperature: -4°F to 104°F
- IP20, Suitable For Only
- 5-Year Warranty

Lighting:

- MCT: Multi Color Temperature, The Switch is Inside The Housing
- Dimming: TRIAC Dimmable
- Polycarbonate Lens
- Total Lumens: 1750
- Color Temperatures: 3000K/4000K/5000K
- Color Rendering Index: CRI ≥ 90
- Rated Life: 50,000 Hrs

Fan Performance:

- Fan Diameter: 52"
- Motor Lead Lengths: 17"
- Motor Size: AC 153mm x 18mm
- Electricity Use: 51.27W ~ 12.42W
- AMPS : 0.43 ~ 0.21
- RPM (H/M/L): 218/165/95
- Airflow Efficiency (CFM/W): 113
- Airflow (CFM): High Speed: 4983
- Average Airflow CFM: 3749



Phone: (877) 805-2252 | Fax: (877) 805-2252
www.westgatemfg.com



WG-12202022

Applications:

- The WFL Ceiling Fan & Light is the perfect combination of style and functionality for any room. With its sleek and modern design, it adds a touch of elegance to your space while providing efficient cooling and illumination. Key features include:
- Stylish Design: The WFL Ceiling Fan & Light boasts a contemporary design that complements various interior styles, from classic to modern.
- Efficient Cooling: Enjoy a comfortable environment year-round with powerful fan blades that provide efficient air circulation and cooling.
- Integrated Lighting: Illuminate your room with the integrated light fixture, offering both brightness and energy efficiency.
- Remote Control: Conveniently adjust fan speed, light intensity, and direction with the included remote control.

Performance Table: WFL-113-PC-5B-52-MCT-WH-WH

MODEL NO.	Wattage	Voltage	Lumens	Color Temp.	LPW
WFL-113-PC-5B-52-MCT-WH-WH	20W	120V	1750LM	3000K 4000K 5000K	85

Sample Ordering

Model	Style	Control	No. Blade	Diameter	Color	Temp.	Housing Finish	Blade Finish						
WFL	-	113	-	PC	-	5B	-	52	-	MCT	-	WH	-	WH


Accessories: CEILING FAN EXTENSION DOWNROD



White
(-WH)

Brushed
Nickel
(-BN)

Black
(-BK)



MODEL NO.	DESCRIPTION
WF-DR-12-BN	Ceiling Fan Extension Downrod 12in, Brush Nickel
WF-DR-18-BN	Ceiling Fan Extension Downrod 18in, Brush Nickel
WF-DR-24-BN	Ceiling Fan Extension Downrod 24in, Brush Nickel
WF-DR-36-BN	Ceiling Fan Extension Downrod 36in, Brush Nickel
WF-DR-12-BK	Ceiling Fan Extension Downrod 12in, Black
WF-DR-18-BK	Ceiling Fan Extension Downrod 18in, Black
WF-DR-24-BK	Ceiling Fan Extension Downrod 24in, Black
WF-DR-36-BK	Ceiling Fan Extension Downrod 36in, Black
WF-DR-12-WH	Ceiling Fan Extension Downrod 12in, White
WF-DR-18-WH	Ceiling Fan Extension Downrod 18in, White
WF-DR-24-WH	Ceiling Fan Extension Downrod 24in, White
WF-DR-36-WH	Ceiling Fan Extension Downrod 36in, White

