




EAN:	4013288228376	Size:	275x140x70 mm
Part number:	05136073001	Weight:	1222 g
Article number:	Safe-Torque A 1 SHK Set 1	Country of origin:	CZ
		Customs tariff number:	82041100

- For operations in plumbing, heating and air conditioning, especially for installing shower cubicles and for assembly and maintenance of gas boilers and condensing boilers
- Safe-Torque torque wrench with slip-over release mechanism - the set torque can never be overtightened
- Torque Lock function: The torque function can be deactivated and the tool can then be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation
- For controlled clockwise and counterclockwise torque operation - tightening and loosening with or without torque
- Easy setting and saving of the desired torque value with audible and tactile clicks when reaching the scale values
- After the target torque has been reached, the release angle is only 30°

20-piece set in a robust textile box, especially for HVAC applications. One Safe-Torque A 1 torque wrench with 1/4" square head drive, 2-12 Nm, with slide-over mechanism. Once the set torque has been reached, the tool cannot be overtightened, so that excessive torque cannot be applied. Setting range of 2 to 12 Nm for controlled clockwise and counterclockwise torque operation. Easy setting and saving of the default value: The audible and tactile clicks on reaching the scale values facilitate the safe setting of the desired torque value. With Torque Lock function for use as a standard ratchet without torque function and thus also usable for applications with angles of rotation. Max. breaking torque of the 1/4" square head as per DIN 3122. The return angle of only 5° allows the ratchet to be used even in confined spaces. Included are: Safe-Torque A 1 torque wrench, 1/4" square head, 2-12 Nm, 8 sockets with 1/4" drive, 9 bit sockets (hexagonal socket, TORX®) with 1/4" drive, one short extension.



Web link
<https://www.wera.de/en/05136073001>

Wera - Safe-Torque A 1 SHK Set 1
05136073001 - 4013288228376

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Slide-over mechanism prevents application of excessive torques



Safe-Torque




The Safe-Torque A 1 torque wrench is equipped with a slide-over mechanism. Once the set torque value has been reached, the tool cannot be overtightened, so that excessive torque cannot be applied.

Torque Lock function



The torque function can be deactivated. The Safe-Torque torque wrench can then also be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation.

For clockwise and counterclockwise operation



The Safe-Torque torque wrench is suitable for clockwise and counterclockwise operation with a set torque. When the Torque Lock function is deactivated, tightening and loosening is enabled without torque.

Easy torque setting



Easy setting and saving of the required torque with audible and tactile clicks on reaching the scale values.

Low return angle



The fine-toothed Safe-Torque torque wrench with 72 teeth has a back-pivoting angle of only 5°. The small stroke offers quick and precise working in all installation positions.

Textile belt for sockets/bit sockets



Includes a robust textile belt (Belt) for 9 sockets/bit sockets (1/4"). A smooth rotary mechanism allows a secure hold and easy access of the sockets. With fleece back which keeps the belt hooked inside the textile box. With the extra adhesive hook-and-loop fastener strip, which is also included, the belt can be easily attached to e.g. the wall, shelf, workshop trolley and Wera 2go tool transport system.

Manual and machine sockets



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Set contents:

Safe-Torque A 1 torque wrench with 1/4" square head drive, 2-12 Nm, 1/4" x 2-12 Nm

05075800001 1x 1/4" x 2-12 Nm



8790 HMA Zyklop 1/4" socket, 6 x 23 mm



05003505001	1x 6 x 23 mm
05003506001	1x 7 x 23 mm
05003507001	1x 8 x 23 mm
05003509001	1x 10 x 23 mm
05003511001	1x 12 x 23 mm
05003512001	1x 13 x 23 mm
05003504001	1x 5.5 x 23 mm
05003510001	1x 11 x 23 mm

8767 A HF TORX® Zyklop bit socket with holding function, 1/4" drive, TX 15 x 28 mm



05003363001	1x TX 15 x 28 mm
05003364001	1x TX 20 x 28 mm
05003365001	1x TX 25 x 28 mm
05003369001	1x TX 30 x 28 mm

8740 A HF Zyklop bit socket with holding function, 1/4" drive, 3 x 28 mm



05003332001	1x 3 x 28 mm
05003333001	1x 4 x 28 mm
05003335001	1x 5 x 28 mm
05003337001	1x 6 x 28 mm
05003339001	1x 8 x 28 mm

Belt A (textile belt), 9 location, unloaded, 39 x 238 mm

1x 39 x 238 mm



8794 SA Zyklop extension with free-turning sleeve, short, 1/4", 1/4" x 75 mm

05003525001 1x 1/4" x 75 mm



Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



Web link

<https://www.wera.de/en/05136073001>

Wera - Safe-Torque A 1 SHK Set 1
05136073001 - 4013288228376

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de