Project / Job Name:

Location:

Fixture Type:

Notes:

65-685 - 40 Watt LED Area Light with Photocell; CCT Selectable and Dimmable; Bronze Finish; 120-277 Volts; Ultra Bright Lumens

GENERAL

Company	NUVO
EA Height	7.09
EA Width	11.81
EA Length	16.54
Bulb Included	Integrated
Extends (in)	13.62
Material	Aluminum
Fixture Type	Area Light
Status	Active
Style	Traditional
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	15%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Bronze
Additional Info	Type V Lighting Distribution; Dusk to Dawn Lamp
Amps	0.333-0.144A
Has Camera	No
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Material	Polycarbonate (PC)
Photo Cell	Has Photocell
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	300W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	150x150
Color Temp	Warm to Cool White
CRI	70+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40F to +122F (-40C to +50C)
HID Equivalent	150W
Lumens	5600L-6400L
Volts	120V-277V
Watts	40W
Max Lumens	6400L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Wall/Pipe Arm

ADDITIONAL INFO

Warranty	5-Years
Installation Notes	Suitable for 42-60mm pipe installation

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923656859
Case Cube	1.8389
Case Height	14.96
Case Length	17.13
Case Quantity	2
Case UPC	10045923656856
Case Weight	16.09
Case Width	12.4
EA Cube	0.8015
EA Height	7.09
EA Length	16.54
EA Quantity	1
EA Weight	7.28
EA Width	11.81
Pack Type	Box
Web Height	7.36
Web Width	9.13

COMPLIANCE

ADA Compliant	No
Bug Rating	B2-U3-G1
CA Prop 65	Lead
DLC ID	PLIZI1KXWZDS
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026